

PML-T107 (26X280)R - Pipeline markers



1014241

<https://www.phoenixcontact.com/us/products/1014241>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Pipeline markers, Roll, violet, pre-printed, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2: pre-printed, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

Your advantages

- Stick-on pipeline markers, unmarked
- Suitable for indoor and outdoor use
- Pipeline marking according to DIN 2403
- In combination with the PML-GHS hazardous substances labels, marking which conforms to the Ordinance on Hazardous Substances (GefStoffV) can be applied
- High adhesive strength
- Finely perforated arrowheads enable the arrowheads which are not required to be easily removed
- High temperature resistance
- Group 7 (alkalis)

Commercial data

Item number	1014241
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG21
Product key	BG2611
Catalog page	Page 381 (C-3-2019)
GTIN	4046356784375
Weight per piece (including packing)	492.5 g
Weight per piece (excluding packing)	492 g
Customs tariff number	39199080
Country of origin	DE

PML-T107 (26X280)R - Pipeline markers



1014241

<https://www.phoenixcontact.com/us/products/1014241>

Technical data

Product properties

Type	Rectangle
Product type	System marking
Area of application	Pipeline labels
	Pipeline identification according to DIN 2403

Marking

Number of individual labels	250
Printing	pre-printed

Dimensions

Width	280 mm
Height	26 mm
Length	26 mm
Diameter	0.00 mm

Material specifications

RoHS compliant	yes
Foil strength	50 µm
Adhesive	Acrylic
Color	violet
Material	Polyester

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

PML-T107 (26X280)R - Pipeline markers



1014241

<https://www.phoenixcontact.com/us/products/1014241>

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	2 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

PML-T107 (26X280)R - Pipeline markers



1014241

<https://www.phoenixcontact.com/us/products/1014241>

Classifications

ECLASS

ECLASS-11.0	40200202
ECLASS-12.0	40200202
ECLASS-13.0	40200202

ETIM

ETIM 9.0	EC001777
----------	----------

UNSPSC

UNSPSC 21.0	55121700
-------------	----------

PML-T107 (26X280)R - Pipeline markers



1014241

<https://www.phoenixcontact.com/us/products/1014241>

Accessories

THERMOMARK E.300 D US - Thermal transfer printer

1287033

<https://www.phoenixcontact.com/us/products/1287033>



Thermal transfer printer with internal rewinder for printing all materials in roll format with a print resolution of 300 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

THERMOMARK E.300 US - Thermal transfer printer

1287021

<https://www.phoenixcontact.com/us/products/1287021>



Thermal transfer printer for printing all materials in roll format with a print resolution of 300 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

PML-T107 (26X280)R - Pipeline markers



1014241

<https://www.phoenixcontact.com/us/products/1014241>

THERMOMARK E.600 D US - Thermal transfer printer

1287040

<https://www.phoenixcontact.com/us/products/1287040>



Thermal transfer printer with internal rewinder for printing all materials in roll format with a print resolution of 600 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

THERMOMARK E.600 US - Thermal transfer printer

1287029

<https://www.phoenixcontact.com/us/products/1287029>



Thermal transfer printer for printing all materials in roll format with a print resolution of 600 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

PML-T107 (26X280)R - Pipeline markers



1014241

<https://www.phoenixcontact.com/us/products/1014241>

THERMOMARK ROLL 2.0 - Thermal transfer printer

1085260

<https://www.phoenixcontact.com/us/products/1085260>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

TM-RIBBON 110 WH 101 - Ink ribbon

1099966

<https://www.phoenixcontact.com/us/products/1099966>



Ink ribbon, For THERMOMARK roll printers for printing the product group material off the roll: PML-T..., length: 60 m, roll length: 60 m, width: 110 mm, color: white

PML-T107 (26X280)R - Pipeline markers



1014241

<https://www.phoenixcontact.com/us/products/1014241>

PML-GHS100 (13X13)R - Hazardous substances label

1014289

<https://www.phoenixcontact.com/us/products/1014289>



Hazardous substances label, Roll, red/white, pre-printed, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 500

PML-GHS100 (25X25)R - Hazardous substances label

1014290

<https://www.phoenixcontact.com/us/products/1014290>



Hazardous substances label, Roll, red/white, pre-printed, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 500

PML-T107 (26X280)R - Pipeline markers

1014241

<https://www.phoenixcontact.com/us/products/1014241>



THERMOMARK ROLLMASTER 300 - Thermal transfer printer

0804501

<https://www.phoenixcontact.com/us/products/0804501>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

THERMOMARK ROLLMASTER 600 - Thermal transfer printer

0804663

<https://www.phoenixcontact.com/us/products/0804663>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

PML-T107 (26X280)R - Pipeline markers



1014241

<https://www.phoenixcontact.com/us/products/1014241>

THERMOMARK ROLL - Thermal transfer printer

5146477

<https://www.phoenixcontact.com/us/products/5146477>



Thermal transfer printer, 300 dpi, incl. European power cable, US power cable, and USB cable. DVD with CLIP PROJECT advanced planning and marking software, user manuals in various languages, Windows® printer driver, and firmware. German/English user manual in DIN A5 format, EML (20x8)R roll of labels, white, with 1000 labels, and ink ribbon: 50 m

THERMOMARK X1.2 - Thermal transfer printer

5146231

<https://www.phoenixcontact.com/us/products/5146231>



Thermal transfer printer, weight: 10 kg, length: 0.446 m, width: 242 mm, height: 274 mm, color: gray

PML-T107 (26X280)R - Pipeline markers

1014241

<https://www.phoenixcontact.com/us/products/1014241>

PML-GHS101 (25X25) - Hazardous substances label

1014270

<https://www.phoenixcontact.com/us/products/1014270>



Hazardous substances label, Sheet, red/white, labeled: Explosive, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 4

PML-GHS102 (13X13) - Hazardous substances label

1014271

<https://www.phoenixcontact.com/us/products/1014271>



Hazardous substances label, Sheet, red/white, labeled: Flammable, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 35

PML-T107 (26X280)R - Pipeline markers

1014241

<https://www.phoenixcontact.com/us/products/1014241>

PML-GHS102 (25X25) - Hazardous substances label

1014272

<https://www.phoenixcontact.com/us/products/1014272>



Hazardous substances label, Sheet, red/white, labeled: Flammable, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 4

PML-GHS103 (13X13) - Hazardous substances label

1014273

<https://www.phoenixcontact.com/us/products/1014273>



Hazardous substances label, Sheet, red/white, labeled: Oxidizing, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 35

PML-T107 (26X280)R - Pipeline markers

1014241

<https://www.phoenixcontact.com/us/products/1014241>

PML-GHS103 (25X25) - Hazardous substances label

1014274

<https://www.phoenixcontact.com/us/products/1014274>



Hazardous substances label, Sheet, red/white, labeled: Oxidizing, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 4

PML-GHS104 (13X13) - Hazardous substances label

1014275

<https://www.phoenixcontact.com/us/products/1014275>



Hazardous substances label, Sheet, red/white, labeled: Pressurized gases, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 35

PML-T107 (26X280)R - Pipeline markers

1014241

<https://www.phoenixcontact.com/us/products/1014241>

PML-GHS104 (25X25) - Hazardous substances label

1014276

<https://www.phoenixcontact.com/us/products/1014276>



Hazardous substances label, Sheet, red/white, labeled: Pressurized gases, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 4

PML-GHS105 (13X13) - Hazardous substances label

1014277

<https://www.phoenixcontact.com/us/products/1014277>



Hazardous substances label, Sheet, red/white, labeled: Corrosive, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 35

PML-T107 (26X280)R - Pipeline markers

1014241

<https://www.phoenixcontact.com/us/products/1014241>

PML-GHS105 (25X25) - Hazardous substances label

1014278

<https://www.phoenixcontact.com/us/products/1014278>



Hazardous substances label, Sheet, red/white, labeled: Corrosive, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 4

PML-GHS106 (13X13) - Hazardous substances label

1014279

<https://www.phoenixcontact.com/us/products/1014279>



Hazardous substances label, Sheet, red/white, labeled: Toxic, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 35

PML-T107 (26X280)R - Pipeline markers

1014241

<https://www.phoenixcontact.com/us/products/1014241>

PML-GHS106 (25X25) - Hazardous substances label

1014280

<https://www.phoenixcontact.com/us/products/1014280>



Hazardous substances label, Sheet, red/white, labeled: Toxic, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 9

PML-GHS107 (13X13) - Hazardous substances label

1014281

<https://www.phoenixcontact.com/us/products/1014281>



Hazardous substances label, Sheet, red/white, labeled: Irritant, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 35

PML-T107 (26X280)R - Pipeline markers

1014241

<https://www.phoenixcontact.com/us/products/1014241>

PML-GHS107 (25X25) - Hazardous substances label

1014282

<https://www.phoenixcontact.com/us/products/1014282>



Hazardous substances label, Sheet, red/white, labeled: Irritant, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 9

PML-GHS108 (13X13) - Hazardous substances label

1014283

<https://www.phoenixcontact.com/us/products/1014283>



Hazardous substances label, Sheet, red/white, labeled: Hazardous to health, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 35

PML-T107 (26X280)R - Pipeline markers

1014241

<https://www.phoenixcontact.com/us/products/1014241>

PML-GHS108 (25X25) - Hazardous substances label

1014284

<https://www.phoenixcontact.com/us/products/1014284>



Hazardous substances label, Sheet, red/white, labeled: Hazardous to health, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 9

PML-GHS109 (13X13) - Hazardous substances label

1014285

<https://www.phoenixcontact.com/us/products/1014285>



Hazardous substances label, Sheet, red/white, labeled: Hazardous to the environment, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 35

PML-T107 (26X280)R - Pipeline markers

1014241

<https://www.phoenixcontact.com/us/products/1014241>

PML-GHS109 (25X25) - Hazardous substances label

1014286

<https://www.phoenixcontact.com/us/products/1014286>



Hazardous substances label, Sheet, red/white, labeled: Hazardous to the environment, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 9

US-PML-GHS100 (13X13) - Hazardous substances label

1014287

<https://www.phoenixcontact.com/us/products/1014287>



Hazardous substances label, Card, red/white, pre-printed, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD: Diamond, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 50

PML-T107 (26X280)R - Pipeline markers



1014241

<https://www.phoenixcontact.com/us/products/1014241>

US-PML-GHS100 (25X25) - Hazardous substances label

1014288

<https://www.phoenixcontact.com/us/products/1014288>



Hazardous substances label, Card, red/white, pre-printed, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD: Diamond, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 9

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com