

PAI-4-FIX-5/6 YE - Test adapter



3035977

<https://www.phoenixcontact.com/us/products/3035977>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

4 mm test adapter, for terminal blocks with 5.2 mm and 6.2 mm pitch



Your advantages

- Make contact and latch securely to any point in the function shaft
- Test adapter for accommodating safety test plugs with a 4 mm diameter

Commercial data

Item number	3035977
Packing unit	1 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z3X
Catalog page	Page 105 (C-1-2019)
GTIN	4046356520690
Weight per piece (including packing)	1.4 g
Weight per piece (excluding packing)	1.2 g
Customs tariff number	85366990
Country of origin	PL

PAI-4-FIX-5/6 YE - Test adapter



3035977

<https://www.phoenixcontact.com/us/products/3035977>

Technical data

Notes

General	Touch proof against unintentional direct contact according to DIN EN 50274 when plugged in
General	Do not plug in while the power is connected
General	Latching testing accessories, therefore only suitable for being plugged in once

Product properties

Product type	Test socket
Number of positions	1

Electrical properties

Maximum load current	10 A
Max. voltage	250 V

Connection data

Maximum load current	10 A
----------------------	------

Dimensions

Width	5.8 mm
Height	5.8 mm
Depth	45.3 mm
Diameter	5.8 mm
Pin diameter	2.4 mm

Material specifications

Color	yellow
Material	Copper
Flammability rating according to UL 94	V0
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Mechanical properties

Mechanical data

PAI-4-FIX-5/6 YE - Test adapter



3035977

<https://www.phoenixcontact.com/us/products/3035977>

Insertion/withdrawal cycles	1
-----------------------------	---

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Connection method	Plug-in connection
-------------------	--------------------

PAI-4-FIX-5/6 YE - Test adapter



3035977

<https://www.phoenixcontact.com/us/products/3035977>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3035977>



EAC

Approval ID: RU C-DE.BL08.B.00511

PAI-4-FIX-5/6 YE - Test adapter



3035977

<https://www.phoenixcontact.com/us/products/3035977>

Classifications

ECLASS

ECLASS-11.0	27141148
ECLASS-12.0	27141148
ECLASS-13.0	27250304

ETIM

ETIM 9.0	EC002555
----------	----------

UNSPSC

UNSPSC 21.0	20122000
-------------	----------

PAI-4-FIX-5/6 YE - Test adapter



3035977

<https://www.phoenixcontact.com/us/products/3035977>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e No hazardous substances above threshold values
------------	-----------------------------------------------------------------------------------------------------------

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com