

# E-WML 12 (25X19)R - Wire-wrap label



1199677

<https://www.phoenixcontact.com/us/products/1199677>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire-wrap label, Roll, white, unlabeled, can be labeled with: THERMOMARK E.WRAP, THERMOMARK E.300 (D)/600 (D), mounting type: adhesive, cable diameter range: 6.1 ... 12.1 mm, lettering field size: 25.4 x 19.1 mm, Number of individual labels: 2750

## Product description

The self-laminating wrap-around labels in the E-WML... product family are designed for automated processing with the THERMOMARK E.WRAP applicator. After the printing and applying process, the markers adhere to the cable at a permanently defined position and the protective laminate protects the markers against dirt and abrasion. As the labels wrap tightly around the wires, they do not create any additional volume, so the wires can also be pulled through cable ducts, for example.

## Your advantages

- For indoor and outdoor applications: high resistance to dirt and abrasion due to the protective laminate
- Firmly defined positioning of labels thanks to the adhesive system
- Broad diameter range with many different applications inside and outside the control cabinet
- The wrap-around labels do not create any additional volume, so the cable can also be pulled through cable ducts, for example
- Tight, bubble-free fit on the cable thanks to automatic winding
- For cylindrical objects, single wires, and cables

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1199677       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BG15          |
| Product key                          | BG2311        |
| GTIN                                 | 4063151262426 |
| Weight per piece (including packing) | 901.6 g       |
| Weight per piece (excluding packing) | 816.3 g       |
| Customs tariff number                | 39191012      |
| Country of origin                    | FR            |

# E-WML 12 (25X19)R - Wire-wrap label



1199677

<https://www.phoenixcontact.com/us/products/1199677>

## Technical data

### Product properties

|              |                   |
|--------------|-------------------|
| Product type | Conductor marking |
| Type         | Label             |

### Marking

|                                     |                            |
|-------------------------------------|----------------------------|
| Number of individual labels         | 2750                       |
| Number of individual labels per row | 1                          |
| Identification technology           | Thermal transfer for rolls |

### Dimensions

|        |         |
|--------|---------|
| Width  | 25.4 mm |
| Length | 57.2 mm |

### Material specifications

|                |               |
|----------------|---------------|
| RoHS compliant | yes           |
| Adhesive       | Acrylic       |
| Color          | white         |
| Material       | PVC           |
| Components     | Silicone-free |

### Cable/line

|                         |                    |
|-------------------------|--------------------|
| External cable diameter | 12.1 mm            |
|                         | 6.1 mm ... 12.1 mm |

### Environmental and real-life conditions

#### Scratch test for the determining scratch resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 1518-1:2019-10 (following) |
| Requirements  | ≥ 5 N                                 |
| Result        | Test passed                           |

#### Tesafilm test

|               |                                  |
|---------------|----------------------------------|
| Specification | DIN EN ISO 2409:2013 (following) |
| Result        | Test passed                      |

#### UV resistance

|                         |                                |
|-------------------------|--------------------------------|
| Specification           | ISO 4892-2:2013-03 (following) |
| Result                  | Test passed                    |
| Test duration           | 96 h                           |
| Specification           | IEC 60068-2-2:2007-07          |
| Result                  | Test passed                    |
| Duration                | 96 h                           |
| Temperature for testing | 100 °C                         |

# E-WML 12 (25X19)R - Wire-wrap label



1199677

<https://www.phoenixcontact.com/us/products/1199677>

## Temperature resistance

|                                |                                 |
|--------------------------------|---------------------------------|
| Specification                  | ANSI/UL 969-2018:03 (following) |
| Test duration                  | 240 h                           |
| Rating 100 °C (121 °C)         | Test passed                     |
| Specification                  | ISO 175:2010 (following)        |
| Test duration                  | 168 h                           |
| Diesel<br>[CAS No. 68476-34-6] | Test passed                     |
| IRM 901                        | Test passed                     |
| IRM 902                        | Test passed                     |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                   |
|---------------|-------------------|
| Specification | DIN 50018:2013-05 |
| Result        | Test passed       |
| Climate level | AHT 1.0 S         |
| Cycles        | 2                 |

## Salt spray test

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result        | Test passed               |
| Test duration | 96 h                      |

## Ambient conditions

|                                                     |                   |
|-----------------------------------------------------|-------------------|
| Ambient temperature (operation)                     | -40 °C ... 80 °C  |
| Ambient temperature (assembly)                      | + 15 °C ... 35 °C |
| Recommended ambient temperature (storage/transport) | 20 °C ... 25 °C   |
| Recommended humidity (storage/transport)            | 40 % ... 50 %     |
| Shelf life                                          | 2 years           |

## Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Mounting

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

# E-WML 12 (25X19)R - Wire-wrap label



1199677

<https://www.phoenixcontact.com/us/products/1199677>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27281102 |
| ECLASS-12.0 | 27281102 |
| ECLASS-13.0 | 27281102 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001530 |
|----------|----------|

# E-WML 12 (25X19)R - Wire-wrap label

1199677

<https://www.phoenixcontact.com/us/products/1199677>



## Accessories

### THERMOMARK E.300 D US - Thermal transfer printer

1287033

<https://www.phoenixcontact.com/us/products/1287033>



Thermal transfer printer with internal rewinder for printing all materials in roll format with a print resolution of 300 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

---

### THERMOMARK E.600 D US - Thermal transfer printer

1287040

<https://www.phoenixcontact.com/us/products/1287040>



Thermal transfer printer with internal rewinder for printing all materials in roll format with a print resolution of 600 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

# E-WML 12 (25X19)R - Wire-wrap label

1199677

<https://www.phoenixcontact.com/us/products/1199677>



## THERMOMARK E.WRAP - Applicator

1192931

<https://www.phoenixcontact.com/us/products/1192931>



Applicator for the efficient printing and applying of E-WML... wire-wrap labels on wires and cables in a single automated process step

---

## THERMOMARK E.WRAP SET US - Applicator set

1287056

<https://www.phoenixcontact.com/us/products/1287056>



Device set consisting of the E.WRAP applicator and the compatible THERMOMARK E.300 D BASIC printing system for printing and applying the E-WML... wire-wrap labels on wires and cables.

## E-WML 12 (25X19)R - Wire-wrap label

1199677

<https://www.phoenixcontact.com/us/products/1199677>



### TM-RIBBON 64 BK 103 - Ink ribbon

1255598

<https://www.phoenixcontact.com/us/products/1255598>



Ink ribbon, For the E-WML... product group in combination with the THERMOMARK E.WRAP applicator, length: 0.3 m, roll length: 300 m, width: 64 mm, color: black

---

### TM E.WRAP-PR - Pressure roller

1259200

<https://www.phoenixcontact.com/us/products/1259200>



Pressure roller for all E-WML... materials (material width of up to 60 mm/2.36")

# E-WML 12 (25X19)R - Wire-wrap label

1199677

<https://www.phoenixcontact.com/us/products/1199677>



## TM E.300/E.600-TEAR OFF PLATE - Demolition plate

1263118

<https://www.phoenixcontact.com/us/products/1263118>

Tear-off plate for all roll printers in the THERMOMARK E SERIES



---

## TM E.300/E.600-DISPENSING EDGE/L - Dispensing edge

1263116

<https://www.phoenixcontact.com/us/products/1263116>

Dispensing edge for processing all E-WML... materials when using the THERMOMARK E.WRAP





## E-WML 12 (25X19)R - Wire-wrap label

1199677

<https://www.phoenixcontact.com/us/products/1199677>



## TM E.300/E.600-FRONT COVER - Front plate

1285305

<https://www.phoenixcontact.com/us/products/1285305>

Front panel for all roll printers in the THERMOMARK E SERIES



---

## THERMOMARK ROLL-ERH - Media hub

5146448

<https://www.phoenixcontact.com/us/products/5146448>

External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm



# E-WML 12 (25X19)R - Wire-wrap label

1199677

<https://www.phoenixcontact.com/us/products/1199677>



## THERMOMARK-ERH 500 - Media hub

5146309

<https://www.phoenixcontact.com/us/products/5146309>



External media hub, for the THERMOMARK ROLL, for roll diameter of up to 500 mm

---

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)