

UKH 240 BU - High-current terminal block



0711852

<https://www.phoenixcontact.com/gb/products/0711852>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



High-current terminal block, nom. voltage: 1000 V, nominal current: 415 A, number of connections: 2, number of positions: 1, connection method: Screw connection, Rated cross section: 240 mm², cross section: 70 mm² - 240 mm², mounting type: NS 35/15, NS 32, color: blue

Your advantages

- Large-surface marking

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0711852 |
| Packing unit | 3 pc |
| Minimum order quantity | 3 pc |
| Sales key | BE1311 |
| Product key | BE1311 |
| GTIN | 4017918885120 |
| Weight per piece (including packing) | 471 g |
| Weight per piece (excluding packing) | 471 g |
| Customs tariff number | 85369010 |
| Country of origin | IN |

Technical data

Notes

General

| | |
|------|---|
| Note | For a reliable contact of multi stranded conductors it is recommended to untwist multi stranded conductors. |
|------|---|

Product properties

| | |
|-----------------------|-----------------------------|
| Product type | High current terminal block |
| Number of positions | 1 |
| Number of connections | 2 |
| Number of rows | 1 |
| Potentials | 1 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---|---------|
| Rated surge voltage | 8 kV |
| Maximum power dissipation for nominal condition | 13.78 W |

Connection data

| | |
|---------------------------------|---------------------|
| Number of connections per level | 2 |
| Nominal cross section | 240 mm ² |

Level 1 above 1 below 1

| | |
|---|--|
| Connection method | Screw connection |
| Screw thread | M10 |
| Note | Screws with hexagonal socket |
| Tightening torque | 25 ... 30 Nm |
| Stripping length | 40 mm |
| Internal cylindrical gage | B15 |
| Connection in acc. with standard | IEC 60947-7-1 |
| Conductor cross-section rigid | 70 mm ² ... 240 mm ² |
| Cross section AWG | 3/0 ... 350 kcmil (converted acc. to IEC) |
| Conductor cross-section flexible | 70 mm ² ... 240 mm ² |
| Conductor cross-section, flexible [AWG] | 3/0 ... 350 kcmil (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 70 mm ² ... 185 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 70 mm ² ... 185 mm ² |
| Cross-section with insertion bridge, rigid | 240 mm ² |
| Cross-section with insertion bridge, flexible | 185 mm ² |
| 2 conductors with same cross section, rigid | 35 mm ² ... 95 mm ² |
| 2 conductors with same cross section, flexible | 50 mm ² ... 95 mm ² |

UKH 240 BU - High-current terminal block



0711852

<https://www.phoenixcontact.com/gb/products/0711852>

| | |
|---|--|
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve | 35 mm ² ... 50 mm ² |
| Nominal cross section | 240 mm ² |
| Nominal current | 415 A |
| Maximum load current | 415 A (with 240 mm ² conductor cross-section) |
| Nominal voltage | 1000 V |
| Note | Note: Product releases, connection cross sections and notes on connecting aluminum cables can be found in the download area. |

Ex data

Rated data (ATEX/IECEx)

| | |
|-----------------------------------|--|
| Identification | Ⓔ II 2 GD Ex eb IIC Gb |
| Operating temperature range | -60 °C ... 110 °C |
| Ex-certified accessories | 1201947 VDE-ISS 8 |
| | 1201659 E/AL-NS 32 |
| | 1201662 E/AL-NS 35 |
| List of bridges | Insertion bridge / EB 2-36/UKH / 0201401 |
| | Insertion bridge / EB 3-36/UKH / 0201414 |
| Bridge data | 270 A (240 mm ²) |
| Ex temperature increase | 40 K (389 A/240 mm ²) |
| at bridging with insertion bridge | 690 V |
| Rated insulation voltage | 1000 V |
| output | (Permanent) |

Ex level General

| | |
|----------------------|---------|
| Rated voltage | 1100 V |
| Rated current | 350 A |
| Maximum load current | 350 A |
| Contact resistance | 0.03 mΩ |

Ex connection data General

| | |
|---|--|
| Stripping length | 40 mm |
| Torque range | 25 Nm ... 30 Nm |
| Nominal cross section | 240 mm ² |
| Rated cross section AWG | 500 kcmil |
| Connection capacity rigid | 70 mm ² ... 240 mm ² |
| Connection capacity AWG | 2/0 ... 500 kcmil |
| Connection capacity flexible | 70 mm ² ... 240 mm ² |
| Connection capacity AWG | 2/0 ... 500 kcmil |
| 2 conductors with same cross section, solid | 35 mm ² ... 95 mm ² |
| 2 conductors with the same cross-section AWG rigid | 2 ... 3/0 |
| 2 conductors with same cross section, stranded | 50 mm ² ... 95 mm ² |
| 2 conductors with the same cross-section AWG flexible | 1/0 ... 3/0 |


Dimensions

UKH 240 BU - High-current terminal block



0711852

<https://www.phoenixcontact.com/gb/products/0711852>

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 36 mm |
| Height | 100 mm |
| Depth | 123.6 mm |
| Depth on NS 32 | 129 mm |
| Depth on NS 35/15 | 131.5 mm |

Material specifications

| | |
|--|-----------------|
| Color | blue (RAL 5015) |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | I |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Electrical tests

Surge voltage test

| | |
|--|-------------|
| Result | Test passed |
| Short-time withstand current 240 mm ² | 28.8 kA |
| Result | Test passed |

Power-frequency withstand voltage

| | |
|-----------------------|-------------|
| Test voltage setpoint | 2.2 kV |
| Result | Test passed |

Mechanical properties

Mechanical data

| | |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

Mechanical tests

Mechanical strength

| | |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

Attachment on the carrier

| | |
|-------------------------|-------------|
| DIN rail/fixing support | NS 32/NS 35 |
| Result | Test passed |

Test for conductor damage and slackening

| | |
|--------------------------------|---|
| Rotation speed | 10 (+/- 2) rpm |
| Revolutions | 135 |
| Conductor cross-section/weight | 70 mm ² /10.4 kg 240 mm ² /20.0 kg |
| Result | Test passed |

Environmental and real-life conditions

Needle-flame test

| | |
|------------------|-------------|
| Time of exposure | 30 s |
| Result | Test passed |

Oscillation/broadband noise

| | |
|------------------------|--|
| Specification | DIN EN 50155 (VDE 0115-200):2022-06 |
| Spectrum | Long life test category 2, bogie-mounted |
| Frequency | $f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$ |
| ASD level | 6.12 (m/s ²) ² /Hz |
| Acceleration | 3.12g |
| Test duration per axis | 5 h |
| Test directions | X-, Y- and Z-axis |
| Result | Test passed |

Shocks

| | |
|--------------------------------|-------------------------------------|
| Specification | DIN EN 50155 (VDE 0115-200):2022-06 |
| Pulse shape | Half-sine |
| Acceleration | 5g |
| Shock duration | 30 ms |
| Number of shocks per direction | 3 |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |
| Result | Test passed |

Ambient conditions

| | |
|--|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Standards and regulations

UKH 240 BU - High-current terminal block



0711852

<https://www.phoenixcontact.com/gb/products/0711852>

| | |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

Mounting

| | |
|---------------|----------|
| Mounting type | NS 35/15 |
| | NS 32 |


UKH 240 BU - High-current terminal block

0711852


<https://www.phoenixcontact.com/gb/products/0711852>

Drawings

Dimensional drawing



Schematic diagram



Connecting aluminum cables. Further notes can be found in the download area

UKH 240 BU - High-current terminal block

0711852

<https://www.phoenixcontact.com/gb/products/0711852>



Circuit diagram



UKH 240 BU - High-current terminal block





0711852

<https://www.phoenixcontact.com/gb/products/0711852>


Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/0711852>

|  CSA Approval ID: 13631 | | | | |
|--|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| B | | | | |
| | 600 V | 400 A | 1/0 - 500 | - |
| C | | | | |
| | 600 V | 400 A | 1/0 - 500 | - |

|  cULus Recognized Approval ID: E60425 | | | | |
|--|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| B | | | | |
| | 600 V | 380 A | 2/0 - 500 | - |
| Multi-conductor connection | 600 V | 380 A | 2 - 3/0 | - |
| C | | | | |
| | 600 V | 380 A | 2/0 - 500 | - |
| Multi-conductor connection | 600 V | 380 A | 2 - 3/0 | - |

| DNV Approval ID: TAE00001CT | | | | |
|---------------------------------------|--|--|--|--|
|---------------------------------------|--|--|--|--|

|  ATEX Approval ID: KEMA99ATEX8332U | | | | |
|---|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| Type examination certificate | 1100 V | 350 A | - | 70 - 240 |

|  IECEX Approval ID: IECEx KEM 06.0030U | | | | |
|---|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 1100 V | 350 A | - | 70 - 240 |

|  CCC Approval ID: 2020322313000623 | | | | |
|---|--|--|--|--|
|---|--|--|--|--|

UKH 240 BU - High-current terminal block



0711852

<https://www.phoenixcontact.com/gb/products/0711852>



UKCA-EX

Approval ID: DEKRA 21UKEX0309U

UL Comp Hazloc CA US

Approval ID: UL US CA L 192998

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine | | | | |
| | 600 V | 380 A | 2/0 - 500 | - |

UKH 240 BU - High-current terminal block



0711852

<https://www.phoenixcontact.com/gb/products/0711852>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250101 |
| ECLASS-15.0 | 27250101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000897 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

UKH 240 BU - High-current terminal block



0711852

<https://www.phoenixcontact.com/gb/products/0711852>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk