

# ZB 6:UNBEDRUCKT - Zack marker strip



1051003

<https://www.phoenixcontact.com/us/products/1051003>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 6.2 mm, Number of individual labels: 10, text field height: 10.5 mm, text field width: 6.15 mm

## Your advantages

- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves

## Commercial data

Item number	1051003
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2112
Catalog page	Page 118 (C-3-2019)
GTIN	4017918015824
Weight per piece (including packing)	1.6 g
Weight per piece (excluding packing)	1.55 g
Customs tariff number	39269097
Country of origin	DE

# ZB 6:UNBEDRUCKT - Zack marker strip



1051003

<https://www.phoenixcontact.com/us/products/1051003>

## Technical data

### Notes

General	Can be labeled with CMS
---------	-------------------------

### Product properties

Product type	Terminal marking
Pitch	6.2 mm
Type	high

### Marking

Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10

### Dimensions

Width	6 mm
Pitch	6.2 mm

### Text field

Text field width	6.15 mm
Text field height	10.5 mm

### Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

### Environmental and real-life conditions

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

# ZB 6:UNBEDRUCKT - Zack marker strip



1051003


<https://www.phoenixcontact.com/us/products/1051003>

## Mounting

Mounting type	latching
---------------	----------

Drawings

Schematic diagram



# ZB 6:UNBEDRUCKT - Zack marker strip



1051003

<https://www.phoenixcontact.com/us/products/1051003>

## Classifications

### ECLASS

ECLASS-13.0

27281101

### ETIM

ETIM 9.0

EC000761

### UNSPSC

UNSPSC 21.0

39131500

# ZB 6:UNBEDRUCKT - Zack marker strip



1051003

<https://www.phoenixcontact.com/us/products/1051003>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.0 Climate Change

CO2e kg	0.012 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)