

THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

Product description

The THERMOMARK ROLL 2.0 prints markers in roll format for top quality terminal, wire, cable, equipment, and plant marking applications. You can easily create high-quality printed labels and markers.

Your advantages

- The THERMOMARK ROLL 2.0 prints marking material in roll format. For applications in terminal, wire, cable, equipment, and plant marking
- Printing of punched and continuous adhesive labels, insert labels, and shrink sleeves
- Fast, high-quality, and durable printing
- Easy and intuitive operation via touch color display
- Maintenance-free operation with proven thermal transfer printer technology
- Easy to control with the PROJECT COMPLETE software
- USB and Ethernet connections

Commercial data

Item number	1085260
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG01
Product key	BG1221
Catalog page	Page 40 (C-3-2019)
GTIN	4055626834764
Weight per piece (including packing)	6,370 g
Weight per piece (excluding packing)	6,289 g
Customs tariff number	84433210
Country of origin	DE

THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

Technical data

Product properties

Product type	Printing system
Scope of delivery	Ink ribbon, label roll, power cable, USB cable, operating instructions
	Power cable, USB cable, operating instructions, label roll, ink ribbon

Marking

Identification technology	Thermal transfer for rolls
---------------------------	----------------------------

Device properties

Print width	105 mm
Print resolution	300 dpi
Operating system	MS Windows Vista, MS Windows 7 (32/64-bit), MS Windows 8 (32/64-bit), MS Windows 8.1 (32/64-bit), MS Windows 10 (32/64-bit), Server 2008, Server 2008 R2, Server 2012, Server 2012 R2

Electrical properties

Supply

Supply voltage range	100 V AC ... 240 V AC (50 Hz ... 60 Hz)
----------------------	---

Interfaces

Interface	10/100 Mbps Ethernet, USB 2.0, RS-232
-----------	---------------------------------------

Dimensions

Width	240 mm
Height	189 mm
Length	320 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	10 °C ... 35 °C
---------------------------------	-----------------

THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1085260>



EAC

Approval ID: RU D-DE.GB09.B.00141



CCC

Approval ID: 2019010904194065



KC

Approval ID: R-R-YG3-TR20



EAC-RoHS

Approval ID: RU D-DE.HB49.B.00023



cULus Recognized

Approval ID: E140403

UAE-RoHS

Approval ID: 13537_E22-04-033555

THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

Classifications

ECLASS

ECLASS-11.0	19140104
ECLASS-12.0	19140104
ECLASS-13.0	19140104

ETIM

ETIM 9.0	EC001684
----------	----------

UNSPSC

UNSPSC 21.0	43212100
-------------	----------

THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

Environmental product compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 10; For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

Accessories

THERMOMARK ROLL-CUTTER - Cutter

5146422

<https://www.phoenixcontact.com/us/products/5146422>



Cutter for THERMOMARK ROLL and THERMOMARK ROLL 2.0, cutter width: 110 mm, suitable for: TML, SK, EML-RM, PMM, WMS, WMS-2 HF, WMS-OT HF, TMT continuous media, and EMT (EX15)R

THERMOMARK ROLL-CUTTER/P - Cutter

5146435

<https://www.phoenixcontact.com/us/products/5146435>



Perforation cutter, for the THERMOMARK ROLL and THERMOMARK ROLL 2.0, cutter width: 45 mm, suitable for: WMS continuous media up to 25.4 mm, WMS-2 continuous media up to 25.4 mm, WMS-OT HF continuous media, TMT continuous media, and EMT (EX15)R

THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

THERMOMARK-RIBBON 110 - Ink ribbon

5145384

<https://www.phoenixcontact.com/us/products/5145384>



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM..., length: 300 m, roll length: 300 m, width: 110 mm, color: black

THERMOMARK-RIBBON 110 BU - Ink ribbon

0829544

<https://www.phoenixcontact.com/us/products/0829544>



Ink ribbon, length: 300 m, roll length: 300 m, width: 110 mm, color: blue

THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

THERMOMARK-RIBBON 110 GN - Ink ribbon

0829542

<https://www.phoenixcontact.com/us/products/0829542>

Ink ribbon, length: 300 m, roll length: 300 m, width: 110 mm, color: green



THERMOMARK-RIBBON 110 RD - Ink ribbon

0829543

<https://www.phoenixcontact.com/us/products/0829543>

Ink ribbon, length: 300 m, roll length: 300 m, width: 110 mm, color: red



THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

THERMOMARK-RIBBON 110-EML-HT - Ink ribbon

0800342

<https://www.phoenixcontact.com/us/products/0800342>



Ink ribbon, for roll printer for printing product group EML-HT..., length: 300 m, roll length: 300 m, width: 110 mm, color: black

THERMOMARK-RIBBON 110-WMSU - Ink ribbon

0801358

<https://www.phoenixcontact.com/us/products/0801358>



Ink ribbon, For roll printer for printing product groups WMS..., WMS-2 HF..., and WMTB HF-HP, length: 300 m, roll length: 300 m, width: 110 mm, color: black

THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

THERMOMARK-RIBBON 110-WMSU WH - Ink ribbon

0801359

<https://www.phoenixcontact.com/us/products/0801359>



Ink ribbon, for roll printer for printing product group WMS... (black), length: 300 m, roll length: 300 m, width: 110 mm, color: white

THERMOMARK-RIBBON 110-WMTB HF - Ink ribbon

5148007

<https://www.phoenixcontact.com/us/products/5148007>



Ink ribbon, for roll printer for printing product groups WMTB HF..., WMS-2 HF..., TMT..., EMT..., EMLF..., PML-..., length: 300 m, roll length: 300 m, width: 110 mm, color: black

THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

THERMOMARK-RIBBON 64-WMSU - Ink ribbon

0801360

<https://www.phoenixcontact.com/us/products/0801360>



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., length: 300 m, roll length: 300 m, width: 64 mm, color: black

THERMOMARK-RIBBON 64-WMSU WH - Ink ribbon

0801361

<https://www.phoenixcontact.com/us/products/0801361>



Ink ribbon, for roll printer for printing product group WMS... (black), length: 300 m, roll length: 300 m, width: 64 mm, color: white

THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

TM-RIBBON 25 BK 102 - Ink ribbon

1053499

<https://www.phoenixcontact.com/us/products/1053499>



Ink ribbon, for printing WMS-OT/WMS-2 HF... materials, length: 300 m, roll length: 300 m, width: 25 mm, color: black

TM-RIBBON 110-TC/TR WH - Ink ribbon

1014402

<https://www.phoenixcontact.com/us/products/1014402>



Ink ribbon, for roll printer and THERMOMARK CARD for printing product groups US-EMLF..., US-PML..., EMLF..., PML..., and EMLP..., length: 240 m, width: 110 mm, color: white

THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

TR-PRESSURE ROLLER STANDARD - Pressure roller

0801802

<https://www.phoenixcontact.com/us/products/0801802>

Standard pressure roller



TR-PRESSURE ROLLER DR4-50 - Pressure roller

0801800

<https://www.phoenixcontact.com/us/products/0801800>

Pressure roller for continuous shrink sleeve



THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

TR-TEAR OFF PLATE - Demolition plate

0801803

<https://www.phoenixcontact.com/us/products/0801803>

Demolition plate



THERMOMARK ROLL-ERH - Media hub

5146448

<https://www.phoenixcontact.com/us/products/5146448>

External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm



THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

THERMOMARK-ERH 500 - Media hub

5146309

<https://www.phoenixcontact.com/us/products/5146309>



External media hub, for the THERMOMARK ROLL, for roll diameter of up to 500 mm

UM IA THERMOMARK ROLL - Manual

2910897

<https://www.phoenixcontact.com/us/products/2910897>

Manual



THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

THERMOMARK-CP - Accessories

5145371

<https://www.phoenixcontact.com/us/products/5145371>

Cleaning pen, for thermal transfer printers



TR-MARGIN STOP - Locking

0801810

<https://www.phoenixcontact.com/us/products/0801810>

Locking



THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

TL CASE - Transport case

0800613

<https://www.phoenixcontact.com/us/products/0800613>



Transport case for THERMOMARK printers, rounded profile case with aluminum frame, including the TL CASE TROLLY

TL CASE TROLLY - Cart for printer

0803337

<https://www.phoenixcontact.com/us/products/0803337>



Trolley for the transport cases for THERMOMARK LINE and THERMOMARK ROLL X1

THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

TC/TR-PACKAGE WITH FOAM - Original packaging

0801804

<https://www.phoenixcontact.com/us/products/0801804>

Original packaging for transportation



PROJECT COMPLETE - Software

1050453

<https://www.phoenixcontact.com/us/products/1050453>



Intuitive planning and marking software for configuring terminal strips and for professional marking of marking materials for terminal blocks, conductors, cables, devices, and systems. The software is available for download

THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

CLIP-PROJECT ADVANCED - Software

5146040

<https://www.phoenixcontact.com/us/products/5146040>



Multilingual software for convenient configuration of Phoenix Contact products on standard DIN rails.

CLIP-PROJECT PROFESSIONAL - Software

5146053

<https://www.phoenixcontact.com/us/products/5146053>



Multilingual software for terminal strip configuration. A marking module enables the professional marking of markers and labels for identifying terminal blocks, conductors and cables, and devices.

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com