

# ZB 18 CUS - Zack marker strip

0824947

<https://www.phoenixcontact.com/gb/products/0824947>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 18 mm, Number of individual labels: 5, text field height: 17.4 mm, text field width: 10.5 mm

## Your advantages

- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 0824947                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BG8112                         |
| Product key                          | BG8112                         |
| GTIN                                 | 4046356356343                  |
| Weight per piece (including packing) | 2.187 g                        |
| Weight per piece (excluding packing) | 2.187 g                        |
| Customs tariff number                | 49119900                       |
| Country of origin                    | PL                             |

# ZB 18 CUS - Zack marker strip



0824947

<https://www.phoenixcontact.com/gb/products/0824947>

## Technical data

### Product properties

|              |                 |
|--------------|-----------------|
| Product type | Terminal marker |
| Pitch        | 18 mm           |

### Marking

|                                     |      |
|-------------------------------------|------|
| Number of individual labels         | 5    |
| Number of individual labels per row | 5    |
| Number of marker strips             | 5    |
| Slot type                           | high |

### Dimensions

|        |          |
|--------|----------|
| Width  | 17.40 mm |
| Height | 10.50 mm |
| Depth  | 4.20 mm  |
| Pitch  | 18 mm    |

### Text field

|                   |         |
|-------------------|---------|
| Text field width  | 10.5 mm |
| Text field height | 17.4 mm |

### Material specifications

|  |                                |
|--|--------------------------------|
| Color                                  | white (RAL 9010)               |
| Material                               | PA                             |
| Flammability rating according to UL 94 | V2                             |
| Base element material                  | PA                             |
| Components                             | free from silicone and halogen |

### Environmental and real-life conditions

#### Ambient conditions

|   |                   |
|---|-------------------|
| Ambient temperature (operation)                     | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C             |
| Recommended humidity (storage/transport)            | 50 %              |

#### UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
|---------------|---------------------------------------|

#### Wipe resistance of inscriptions

|               |  |
|---------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03           |
|               | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

### Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

# ZB 18 CUS - Zack marker strip

0824947

<https://www.phoenixcontact.com/gb/products/0824947>



## Mounting

Mounting type

snap into tall marker groove

# ZB 18 CUS - Zack marker strip

0824947

<https://www.phoenixcontact.com/gb/products/0824947>

## Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

# ZB 18 CUS - Zack marker strip



0824947

<https://www.phoenixcontact.com/gb/products/0824947>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000761 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# ZB 18 CUS - Zack marker strip



0824947

<https://www.phoenixcontact.com/gb/products/0824947>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)