

ECOR-1-BSC2-RT/2X21 - Relay base

1027546

<https://www.phoenixcontact.com/gb/products/1027546>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

ECOR-1... relay base, for miniature power relays or miniature switching relays with 1 or 2 changeover contacts, bolt connection, for mounting on NS 35/7,5.



Commercial data

Item number	1027546
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	DKF312
Product key	DKF312
GTIN	4055626522210
Weight per piece (including packing)	35.297 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85366990
Country of origin	CN

Technical data

Notes

Notes on operation	Do not use to separate SELV / PELV circuits from other circuits, because safe isolation is not guaranteed.
Notes on operation	The outputs are not suitable for switching different outer conductors.
Notes on operation	The system installer must ensure the touch protection of the product (at voltages > 25 V AC/60 V DC). The product is a built-in device without protection against direct contact.
Notes on operation	At least a basic level of insulation is maintained against adjacent modules in the DIN rail direction. If the application has higher requirements on the insulation (reinforced insulation), then these must be realized through suitable measures (e.g. partition plates).

Product properties

Product type	Relay socket
Product family	ESSENTIAL edition
Operating mode	100% operating factor

Insulation characteristics: Air clearances and creepage distances between the power circuits

Overvoltage category	III
Pollution degree	2

Electrical properties

Nominal current I_N	10 A
Test voltage relay winding/relay contact	2 kV _{rms} (50 Hz, 1 min.)

Air clearances and creepage distances between the power circuits

Rated insulation voltage	250 V AC
Rated surge voltage	4 kV

Input data

Nominal input voltage U_N	≤ 230 V AC/DC
	≤ 230 V AC/DC

Connection data

Input side

Connection method	Bolt connection
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section rigid (2 conductors with same cross section)	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ² (without ferrule)
	0.2 mm ² ... 1.5 mm ² (with ferrule)
Conductor cross-section flexible (2 conductors with same cross section)	0.2 mm ² ... 2.5 mm ² (without ferrule)
	0.2 mm ² ... 1.5 mm ² (with ferrule)

ECOR-1-BSC2-RT/2X21 - Relay base



1027546

<https://www.phoenixcontact.com/gb/products/1027546>

Conductor cross-section AWG	14
Tightening torque	0.5 Nm ... 0.7 Nm

Output side

Connection method	Bolt connection
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section rigid (2 conductors with same cross section)	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ² (without ferrule)
	0.2 mm ² ... 1.5 mm ² (with ferrule)
Conductor cross-section flexible (2 conductors with same cross section)	0.2 mm ² ... 2.5 mm ² (without ferrule)
	0.2 mm ² ... 1.5 mm ² (with ferrule)
Conductor cross-section AWG	14
Tightening torque	0.5 Nm ... 0.7 Nm

Dimensions

Item dimensions

Width	15.8 mm
Height	71.5 mm
Depth (Retaining bracket)	58.1 mm (with retaining bracket)

Material specifications

Color	traffic gray B (RAL 7043)
-------	---------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Altitude	≤ 2000 m

Standards and regulations

Air clearances and creepage distances between the power circuits

Standards/regulations	DIN EN 50178
-----------------------	--------------

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

ECOR-1-BSC2-RT/2X21 - Relay base



1027546

<https://www.phoenixcontact.com/gb/products/1027546>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1027546>



cUL Recognized
Approval ID: FILE E 113228



UL Recognized
Approval ID: FILE E 113228



EAC
Approval ID: RU C-DE.**08.B.01419



cULus Recognized
Approval ID: E113228

ECOR-1-BSC2-RT/2X21 - Relay base



1027546

<https://www.phoenixcontact.com/gb/products/1027546>

Classifications

ECLASS

ECLASS-13.0	27371603
ECLASS-15.0	27371603

ETIM

ETIM 10.0	EC001456
-----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

ECOR-1-BSC2-RT/2X21 - Relay base



1027546

<https://www.phoenixcontact.com/gb/products/1027546>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	1.583 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk