

FOC-CRIMPSPLICE-PROTECT - Crimp splice protection



1019678

<https://www.phoenixcontact.com/gb/products/1019678>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp splice protection, design: Straight, degree of protection: IP20, connection method: Crimp connection, cable outlet: above and below, color: Bare metallic

Product description

Crimp splice protection in blister packaging

Your advantages

- No attenuating effects on the fusion splice
- Mechanical protection for fusion splices
- Telekom TS 0338/96 approval

Commercial data

Item number	1019678
Packing unit	12 pc
Minimum order quantity	12 pc
Sales key	ABNGAZ
Product key	ABNGAZ
GTIN	4055626701189
Weight per piece (including packing)	0.529 g
Weight per piece (excluding packing)	0.19 g
Customs tariff number	85367000
Country of origin	DE

FOC-CRIMPSPLICE-PROTECT - Crimp splice protection



1019678

<https://www.phoenixcontact.com/gb/products/1019678>

Technical data

Notes

Order information:	Splice protection for FDX 20 splice boxes
Assembly note	Processing with commercially-available presses

Product properties

Product type	Network distributor box
Housing type	Fiber optic
Cable outlet	above and below

Connection data

Connection technology

Connection method	Crimp connection
-------------------	------------------

Dimensions

Height	3 mm
Depth	1.2 mm
Length	30 mm

Material specifications

Color	Bare metallic
Material	Metal

Cable/line

Cable type	Fiberglass
External cable diameter	250 µm (Includes primary coating)

FO cable

Transmission medium	FO
---------------------	----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-40 °C ... 85 °C (according to DIN EN 61300-2)

Mounting

Mounting type	Crimp splice protection
Assembly note	Crimp splice protection clicks into the splice holder

FOC-CRIMPSPLICE-PROTECT - Crimp splice protection



1019678

<https://www.phoenixcontact.com/gb/products/1019678>

Classifications

ECLASS

ECLASS-13.0	19170192
ECLASS-15.0	19170192

ETIM

ETIM 10.0	EC003626
-----------	----------

UNSPSC

UNSPSC 21.0	26121650
-------------	----------

FOC-CRIMPSPLICE-PROTECT - Crimp splice protection



1019678

<https://www.phoenixcontact.com/gb/products/1019678>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk