

ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/gb/products/1089994>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



ECOR-2 relay base, for industrial relay with 2 or 4 changeover contacts, screw connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5

Commercial data

Item number	1089994
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	DKF312
Product key	DKF312
GTIN	4055626897837
Weight per piece (including packing)	68.75 g
Weight per piece (excluding packing)	68 g
Customs tariff number	85366990
Country of origin	CN

ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/gb/products/1089994>

Technical data

Notes

Notes on operation	Do not use to separate SELV / PELV circuits from other circuits, because safe isolation is not guaranteed.
Notes on operation	The outputs are not suitable for switching different outer conductors.
Notes on operation	The system installer must ensure the touch protection of the product (at voltages > 25 V AC/60 V DC). The product is a built-in device without protection against direct contact.
Notes on operation	At least a basic level of insulation is maintained against adjacent modules in the DIN rail direction. If the application has higher requirements on the insulation (reinforced insulation), then these must be realized through suitable measures (e.g. partition plates).

Product properties

Product type	Relay socket
Product family	ESSENTIAL edition
Operating mode	100% operating factor

Insulation characteristics: Air clearances and creepage distances between the power circuits

Overvoltage category	II
Pollution degree	2

Electrical properties

Test voltage relay winding/relay contact	2.5 kV _{rms} (50 Hz, 1 min.)
--	---------------------------------------

Air clearances and creepage distances between the power circuits

Rated insulation voltage	250 V AC
Rated surge voltage	2.5 kV

Input data

Nominal input voltage U _N	≤ 230 V AC/DC
	≤ 230 V AC/DC

Connection data

Input side

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ² (without ferrule) 0.2 mm ² ... 1.5 mm ² (with ferrule)
Conductor cross-section AWG	12
Tightening torque	0.5 Nm ... 0.7 Nm

ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/gb/products/1089994>

Output side

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ² (without ferrule) 0.2 mm ² ... 1.5 mm ² (with ferrule)
Conductor cross-section AWG	12
Tightening torque	0.5 Nm ... 0.7 Nm

Dimensions

Item dimensions

Width	27 mm
Height	75 mm
Depth (Retaining bracket)	84 mm (with retaining bracket)

Material specifications

Color	traffic gray B (RAL 7043)
-------	---------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20 (DIN EN 60529)
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Altitude	≤ 2000 m

Standards and regulations

Air clearances and creepage distances between the power circuits

Standards/regulations	DIN EN 50178
-----------------------	--------------

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/gb/products/1089994>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1089994>



cUL Recognized
Approval ID: FILE E 113228



UL Recognized
Approval ID: FILE E 113228



cULus Recognized
Approval ID: E113228

ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/gb/products/1089994>

Classifications

ECLASS

ECLASS-13.0	27371603
ECLASS-15.0	27371603

ETIM

ETIM 10.0	EC001456
-----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/gb/products/1089994>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	2.66 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk