

QPD W3PE1,5 6-10 M25 0,1 BKKTH - Panel feed-through



1103638

<https://www.phoenixcontact.com/gb/products/1103638>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Panel feed-through, number of positions: 3+PE, black, 1.5 mm², cable length: 0.1 m

Your advantages

- Innovative and time saving - QUICKON fast connection for time saving of up to 80 % for on-site connection
- Robust throughout: housing with IP68/IP69K and IK07 protection for a wide range of applications
- Safer connection with mechanical coding to protect against mismatching, and touch-proof protection in accordance with DIN EN 0105
- Efficient - by using panel feed-throughs, devices no longer need to be opened in order to connect cables

Commercial data

Item number	1103638
Packing unit	1 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Sales key	AF6ABB
Product key	AF6ABB
GTIN	4055626967776
Weight per piece (including packing)	54.3 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85444290
Country of origin	PL

QPD W3PE1,5 6-10 M25 0,1 BKKTH - Panel feed-through



1103638

<https://www.phoenixcontact.com/gb/products/1103638>

Technical data

Product properties

Product type	Panel feed-through
Product family	QPD
Type	QPD 4x2,5
Number of positions	4
Connection profile	3+PE
Special properties	Ring cable lug M4

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Connection data

Connection technology

Frequency of connections between conductors of the same cross section	max. 10
---	---------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	max. 50
-----------------------------	---------

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V0

Cable/line

Cable length	0.1 m
Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	VDE 0295 class 1 to 6/min. 0.15 mm
Cable cross section	1.5 mm ²

Environmental and real-life conditions

Ambient conditions

Degree of protection	Touch-proof when not plugged in (IP2X)
Impact strength	IK07

QPD W3PE1,5 6-10 M25 0,1 BKKTH - Panel feed-through





1103638

<https://www.phoenixcontact.com/gb/products/1103638>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1103638>

 UL Listed Approval ID: E468743				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	600 V	8 A	- 16	- 16

 cUL Listed Approval ID: E468743				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	600 V	8 A	- 16	-

QPD W3PE1,5 6-10 M25 0,1 BKKTH - Panel feed-through



1103638

<https://www.phoenixcontact.com/gb/products/1103638>

Classifications

ECLASS

ECLASS-13.0	27440602
ECLASS-15.0	27440602

ETIM

ETIM 10.0	EC002566
-----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

QPD W3PE1,5 6-10 M25 0,1 BKKTH - Panel feed-through



1103638

<https://www.phoenixcontact.com/gb/products/1103638>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk