

# PHT22-SSD-GN/PT10/GN - Selector switch



1108337

<https://www.phoenixcontact.com/gb/products/1108337>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Selector switch, illuminated, 22 mm, circular, 2 switch positions, green, self-locking, including an actuating head, module holder, a N/O contact module using push-in connection technology and a LED module

## Your advantages

- 22 mm selector switch set with Push-in connection
- 2 positions (0°/60°) – latching
- Depending on the set variant, incl. contact module(s) (N/O / N/C, 1- or 2-way) + 1 LED module – flexible in use
- With integrated lighting option for clear status display
- Quick mounting in the control cabinet/control panel

## Commercial data

Item number	1108337
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BE6122
Product key	BE6122
GTIN	4063151013127
Weight per piece (including packing)	51.5 g
Weight per piece (excluding packing)	51.5 g
Country of origin	CN

1108337

<https://www.phoenixcontact.com/gb/products/1108337>

## Technical data

### Product properties

Product type	Actuator
Insulation characteristics	
Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	5 W

### Connection data

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible [AWG]	20 ... 16 (converted acc. to IEC)
2 conductors with same cross section, rigid	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
2 conductors with the same cross-section AWG rigid	20 ... 16 (converted acc. to IEC)
2 conductors with same cross section, flexible	0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
2 conductors with the same cross-section AWG flexible	20 ... 16 (converted acc. to IEC)
2 conductors with the same cross section, flexible, with ferrule with plastic sleeve	0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Thermal continuous current $I_{th}$	10 A

### Dimensions

Width	30 mm
Height	46 mm

### Installation dimensions

Installation depth	47.9 mm
--------------------	---------

### Material specifications

Color	white
-------	-------

### Environmental and real-life conditions

#### Degree of protection (IP code)

Degree of protection	IP66
----------------------	------

#### Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-30 °C ... 85 °C
Permissible humidity (operation)	≤ 95 % ((room temperature 25°C) no condensation)

# PHT22-SSD-GN/PT10/GN - Selector switch



1108337

<https://www.phoenixcontact.com/gb/products/1108337>

## Standards and regulations

Standards/specifications	IEC 60947-5-1
	GB 14048.5
	UL 60947-5-1

## Mounting

Mounting type	Panel mount
Tightening torque	1 Nm ... 1.2 Nm


# PHT22-SSD-GN/PT10/GN - Selector switch

1108337

<https://www.phoenixcontact.com/gb/products/1108337>

## Drawings

Circuit diagram



# PHT22-SSD-GN/PT10/GN - Selector switch



1108337

<https://www.phoenixcontact.com/gb/products/1108337>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1108337>



**cULus Listed**

Approval ID: E172140



**CCC**

Approval ID: 2024010305697836

**Functional Safety**

Approval ID: R CN21G3UE 001

# PHT22-SSD-GN/PT10/GN - Selector switch



1108337

<https://www.phoenixcontact.com/gb/products/1108337>

## Classifications

### ECLASS

ECLASS-13.0	27371243
ECLASS-15.0	27371243

# PHT22-SSD-GN/PT10/GN - Selector switch



1108337

<https://www.phoenixcontact.com/gb/products/1108337>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)