

# PHT22-BZ-RD - Buzzer

1108842

<https://www.phoenixcontact.com/gb/products/1108842>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Buzzer, 22 mm, round, red, LED integrated, intermittent beep, operating voltage: AC/DC 24-240V, PT Push-in connection technology

## Your advantages

- 22 mm buzzer for clear acoustic signals
- Quick push-in mounting (tool-free)
- High sound pressure for reliable warnings
- Compact, robust design for industrial applications
- Ideal for warning and fault messages in the control cabinet

## Commercial data

Item number	1108842
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE6122
Product key	BE6122
GTIN	4063151017934
Weight per piece (including packing)	20.5 g
Weight per piece (excluding packing)	18.1 g
Customs tariff number	85318070
Country of origin	CN

## Technical data

### Product properties

Product type	Acoustic element
--------------	------------------

### Insulation characteristics

Degree of pollution	3
---------------------	---

### Electrical properties

Max. operating current $I_{max}$	85 mA
----------------------------------	-------

### Connection data

Connection method	Plug-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible [AWG]	20 ... 16 (converted acc. to IEC)
2 conductors with same cross section, rigid	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
2 conductors with the same cross-section AWG rigid	20 ... 16 (converted acc. to IEC)
2 conductors with same cross section, flexible	0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
2 conductors with the same cross-section AWG flexible	20 ... 16 (converted acc. to IEC)
2 conductors with the same cross section, flexible, with ferrule with plastic sleeve	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>

### Dimensions

Width	30 mm
Height	30 mm

### Installation dimensions

Installation depth	28.2 mm
--------------------	---------

### Material specifications

Color	red
-------	-----

### Environmental and real-life conditions

#### Degree of protection (IP code)

Degree of protection	IP40
----------------------	------

#### Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-30 °C ... 85 °C
Permissible humidity (operation)	≤ 95 % ((room temperature 25°C) no condensation)
Noise level	80 dB (10 cm)

### Standards and regulations

# PHT22-BZ-RD - Buzzer



1108842

<https://www.phoenixcontact.com/gb/products/1108842>

Standards/specifications	IEC 60947-5-1
	GB 14048.5
	UL 60947-5-1

## Mounting

Mounting type	Panel mount
---------------	-------------

# PHT22-BZ-RD - Buzzer


1108842

<https://www.phoenixcontact.com/gb/products/1108842>



## Drawings

Circuit diagram



# PHT22-BZ-RD - Buzzer



1108842

<https://www.phoenixcontact.com/gb/products/1108842>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1108842>



**cULus Listed**

Approval ID: E172140



**CCC**

Approval ID: 2024010305697836



**CCC**

Approval ID: 2025010305806583

**Functional Safety**

Approval ID: R CN21G3UE 001

# PHT22-BZ-RD - Buzzer



1108842

<https://www.phoenixcontact.com/gb/products/1108842>

## Classifications

### ECLASS

ECLASS-15.0	27371214
ECLASS-13.0	27371214

# PHT22-BZ-RD - Buzzer



1108842

<https://www.phoenixcontact.com/gb/products/1108842>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)