

# PHT22-PL-WH - LED light

1109034

<https://www.phoenixcontact.com/gb/products/1109034>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Indicator, 22 mm, round, white, LED integrated, AC/DC 24 V ... 240 V, PT Push-in connection



## Your advantages

- 22 mm indicator light with push-in mounting
- Large voltage range 24 ... 240 V AC/DC
- High visibility thanks to bright, uniform light
- Available in different colors
- Robust, touch-proof design for industrial applications

## Commercial data

Item number	1109034
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE6122
Product key	BE6122
GTIN	4063151018061
Weight per piece (including packing)	18.7 g
Weight per piece (excluding packing)	16.4 g
Customs tariff number	85318070
Country of origin	CN

## Technical data

### Product properties

Product type	LED display
--------------	-------------

### Insulation characteristics

Degree of pollution	3
---------------------	---

### Electrical properties

Rated surge voltage	4 kV
---------------------	------

### Connection data

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible [AWG]	20 ... 16 (converted acc. to IEC)
2 conductors with same cross section, rigid	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
2 conductors with the same cross-section AWG rigid	20 ... 16 (converted acc. to IEC)
2 conductors with same cross section, flexible	0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
2 conductors with the same cross-section AWG flexible	20 ... 16 (converted acc. to IEC)
2 conductors with the same cross section, flexible, with ferrule with plastic sleeve	0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Maximum total current	25 mA

### Dimensions

Width	30 mm
Height	30 mm

### Installation dimensions

Installation depth	28.2 mm
--------------------	---------

### Material specifications

Color	white
-------	-------

### Environmental and real-life conditions

#### Degree of protection (IP code)

Degree of protection	IP66
----------------------	------

#### Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-30 °C ... 85 °C
Permissible humidity (operation)	≤ 95 % ((room temperature 25°C) no condensation)

### Standards and regulations

# PHT22-PL-WH - LED light



1109034

<https://www.phoenixcontact.com/gb/products/1109034>

Standards/specifications	IEC 60947-5-1
	GB 14048.5
	UL 60947-5-1

## Mounting

Mounting type	Panel mount
---------------	-------------

# PHT22-PL-WH - LED light


1109034

<https://www.phoenixcontact.com/gb/products/1109034>



## Drawings

Circuit diagram



**1 LED**

# PHT22-PL-WH - LED light



1109034

<https://www.phoenixcontact.com/gb/products/1109034>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1109034>



**cULus Listed**

Approval ID: E172140



**CCC**

Approval ID: 2024010305697836



**CCC**

Approval ID: 2025010305806583

**Functional Safety**

Approval ID: R CN21G3UE 001

# PHT22-PL-WH - LED light

1109034

<https://www.phoenixcontact.com/gb/products/1109034>



## Classifications

### ECLASS

ECLASS-13.0	27371302
ECLASS-15.0	27371302

### ETIM

ETIM 10.0	EC000041
-----------	----------

# PHT22-PL-WH - LED light



1109034

<https://www.phoenixcontact.com/gb/products/1109034>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)