PHT22-PT10 - Contact module

1108991

https://www.phoenixcontact.com/gb/products/1108991

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Contact module, 1NO, push-in connection

Your advantages

- Contact module for 22 mm PHT operating elements
- Quick mounting – simply snap on
- N/O contact – ideal for start/release functions
- Reliable switching function for industrial applications
- Designed for modular combination – multiple contacts possible

Commercial data

Item number	1108991
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	BE6122
Product key	BE6122
GTIN	4063151017460
Weight per piece (including packing)	9.1 g
Weight per piece (excluding packing)	9.1 g
Customs tariff number	85365080
Country of origin	CN

Technical data

Product properties

Product type	Switch module

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	5 W

Connection data

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.5 mm² ... 2.5 mm²
Conductor cross-section flexible	0.5 mm² ... 1.5 mm²
Conductor cross-section, flexible [AWG]	20 ... 16 (converted acc. to IEC)
2 conductors with same cross section, rigid	0.5 mm² ... 2.5 mm²
2 conductors with the same cross-section AWG rigid	20 ... 16 (converted acc. to IEC)
2 conductors with same cross section, flexible	0.5 mm² ... 1.5 mm²
2 conductors with the same cross-section AWG flexible	20 ... 16 (converted acc. to IEC)
2 conductors with the same cross section, flexible, with ferrule with plastic sleeve	0.5 mm² ... 0.5 mm²
Thermal continuous current I_{th}	10 A

Environmental and real-life conditions

Degree of protection (IP code)

Degree of protection	IP20

Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-30 °C ... 85 °C
Permissible humidity (operation)	≤ 95 % ((room temperature 25°C) no condensation)

Standards and regulations

Standards/specifications	IEC 60947-5-1
	GB 14048.5
	UL 60947-5-1

Mounting

Mounting type	Panel mount

Drawings

Circuit diagram



Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/gb/products/1108991

cULus Listed
Approval ID: E172140

CCC
Approval ID: 2024010305697836

Functional Safety
Approval ID: R CN21G3UE 001

Classifications

ECLASS

ECLASS-13.0	27371302
ECLASS-15.0	27371302

ETIM

ETIM 10.0	EC000041

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk