

NBC-R4ACS/0,3-93B/R4ACS - Patch cable



1113825

<https://www.phoenixcontact.com/gb/products/1113825>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Patch cable, PROFINET CAT5 (100 Mbps), EtherCAT® (100 Mbps), 4-position, PVC/PVC, green RAL 6018, Plug straight RJ45 / IP20, on Plug straight RJ45 / IP20, cable length: 0.3 m

Your advantages

- PVC cable for flexible installations
- Perfect for industrial applications
- Worldwide approval with CE, UL, WEEE, and EAC
- Secure connection and disconnection with reliable locking clip protection
- Ideal EMC properties, thanks to 360° shielding
- Simultaneous power transmission with PoE++
- Resistant to shock and vibrations, thanks to robust molding
- High-speed data transmission with up to 100 Mbps (CAT5)



Commercial data

Item number	1113825
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ABNABA
Product key	ABNABA
GTIN	4063151036485
Weight per piece (including packing)	44 g
Weight per piece (excluding packing)	38.305 g
Customs tariff number	85444210

NBC-R4ACS/0,3-93B/R4ACS - Patch cable

1113825

<https://www.phoenixcontact.com/gb/products/1113825>



Country of origin	PL
-------------------	----

Technical data

Product properties

Product type	Data cable preassembled
Product family	RJ45 INDUSTRIAL PN4 CAT5
Number of positions	4
Shielded	yes

Interfaces

Signal type/category	PROFINET CAT5 (IEC 11801), 100 Mbps
	EtherCAT®, 100 Mbps

Electrical properties

Rated voltage (III/2)	72 V
Rated current	1.75 A
Insulation resistance	> 1 TΩ
Transmission speed	100 Mbps
Transmission characteristics (category)	CAT5

Dimensions

Width	14 mm
Height	14.8 mm
Length	44.2 mm

Connector

Connection 1

Type	RJ45 Plug, straight, 4-position, PROFINET, EtherCAT®
Number of positions	4
Signal type/category	PROFINET CAT5 (IEC 11801), 100 Mbps
	EtherCAT®, 100 Mbps
Insertion/withdrawal cycles	≥ 750
Insertion force	50 N (per signal contact)
Withdrawal force	30 N (per signal contact)
Overvoltage category	I
Degree of pollution	2
Material Contact	CuSn6
Material Contact surface	Ni/Au
Material Contact carrier	PC
Material Housing	PP
Color (Housing)	black
Flammability rating according to UL 94	V2
Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C

NBC-R4ACS/0,3-93B/R4ACS - Patch cable



1113825

<https://www.phoenixcontact.com/gb/products/1113825>

Connection 2

Type	RJ45 Plug, straight, 4-position, PROFINET, EtherCAT®
Number of positions	4
Signal type/category	PROFINET CAT5 (IEC 11801), 100 Mbps EtherCAT®, 100 Mbps
Insertion/withdrawal cycles	≥ 750
Insertion force	50 N (per signal contact)
Withdrawal force	30 N (per signal contact)
Overvoltage category	I
Degree of pollution	2
Material Contact	CuSn6
Material Contact surface	Ni/Au
Material Contact carrier	PC
Material Housing	PP
Color (Housing)	black
Flammability rating according to UL 94	V2
Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C

Cable/line

Cable length	0.3 m
--------------	-------

PROFINET PVC stranded CAT5 [93B]

Dimensional drawing	
UL AWM Style	21695 (80 °C / 600 V)
Number of positions	4
Shielded	yes
Cable type	PROFINET PVC stranded CAT5 [93B]
Conductor structure	1x4xAWG22/7, SF/TQ
AWG signal line	22
Conductor cross-section	4x 0.34 mm²
Wire diameter incl. insulation	1.5 mm ±0.1 mm
External cable diameter	6.50 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	green RAL 6018
Conductor material	Tin-plated Cu litz wires
Material wire insulation	PE

NBC-R4ACS/0,3-93B/R4ACS - Patch cable



1113825

<https://www.phoenixcontact.com/gb/products/1113825>

Single wire, color	white, yellow, blue, orange
Overall twist	Star quad
Optical shield covering	85 %
Insulation resistance	$\geq 5 \text{ G}\Omega\cdot\text{km}$
Loop resistance	$\leq 120.00 \text{ }\Omega/\text{km}$
Wave impedance	$100 \text{ }\Omega \pm 5 \text{ }\Omega$ (at 100 MHz)
Nominal voltage, cable	$\leq 600 \text{ V}$
Test voltage Core/Core	2000 V ((50 Hz/1 min))
Test voltage Core/Shield	2000.00 V ((50 Hz/1 min))
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Flame resistance	UL 1581, Section 1060 and UL 2556, Section 9.3 (FT1)
	UL 1685 (CSA FT 4)
	UL 1581, Section 1100 and UL 2556, Section 9.1 (HFT/FT2)
Resistance to oil	OIL RES I according to UL 2256
Other resistance	UV resistant (according to UL 1581, Section 1200)
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-10 °C ... 70 °C (Cable, flexible installation)

Standards and regulations

Standards/specifications	IEC 60603-7
--------------------------	-------------

NBC-R4ACS/0,3-93B/R4ACS - Patch cable



1113825

<https://www.phoenixcontact.com/gb/products/1113825>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1113825>

 UL Listed Approval ID: E335024-V1S7				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	57 V	1.75 A	-	-

 cUL Listed Approval ID: E335024-V1S7				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	57 V	1.75 A	-	-

NBC-R4ACS/0,3-93B/R4ACS - Patch cable



1113825

<https://www.phoenixcontact.com/gb/products/1113825>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

ETIM

ETIM 10.0	EC002599
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	4.619 kg CO2e
---------	---------------