

NS 35/ 7,5 PERF (18X5,2)2000MM - DIN rail perforated



1210019

<https://www.phoenixcontact.com/gb/products/1210019>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail perforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

Commercial data

Item number	1210019
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BE7244
Product key	BE7244
GTIN	4017918941970
Weight per piece (including packing)	640 g
Weight per piece (excluding packing)	640 g
Customs tariff number	72166190
Country of origin	DE

NS 35/ 7,5 PERF (18X5,2)2000MM - DIN rail perforated



1210019


<https://www.phoenixcontact.com/gb/products/1210019>

Technical data

Product properties

Product type	DIN rail
--------------	----------

Dimensions

Dimensional drawing	
Width	35 mm
Hole width	18 mm
Hole height	5.2 mm
Depth	7.5 mm
Length	2000 mm
Drill hole spacing	25 mm

Material specifications

Color	silver-colored
Material	Steel
Coating	galvanized, passivated with a thick layer

Standards and regulations

Connection in acc. with standard	IEC / EN
Tests	acc. to EN 60715

Electrical tests

Short-time withstand current	
Equivalent E-Cu cross-section	16 mm ²
Short-time current resistance 1s	1.92 kA



NS 35/ 7,5 PERF (18X5,2)2000MM - DIN rail perforated

1210019

<https://www.phoenixcontact.com/gb/products/1210019>

Drawings

Dimensional drawing



NS 35/ 7,5 PERF (18X5,2)2000MM - DIN rail perforated



1210019

<https://www.phoenixcontact.com/gb/products/1210019>

Classifications

ECLASS

ECLASS-13.0	27400602
ECLASS-15.0	27400602

ETIM

ETIM 10.0	EC001285
-----------	----------

UNSPSC

UNSPSC 21.0	39121700
-------------	----------

NS 35/ 7,5 PERF (18X5,2)2000MM - DIN rail perforated



1210019

<https://www.phoenixcontact.com/gb/products/1210019>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	1.449 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk