

PLT-EE-T3-60AC-R - Type 3 surge protection device



1249056

<https://www.phoenixcontact.com/gb/products/1249056>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Type 3 surge protection, consisting of protective plug and base element with screw connection, with integrated status indicator and remote signaling for single-phase power supply networks.
Nominal voltage: 60 V AC

Commercial data

Item number	1249056
Packing unit	5 pc
Minimum order quantity	5 pc
Note	Made to order (non-returnable)
Sales key	CLP312
Product key	CLP312
GTIN	4063151353322
Weight per piece (including packing)	94.32 g
Weight per piece (excluding packing)	94 g
Customs tariff number	85363030
Country of origin	DE

PLT-EE-T3-60AC-R - Type 3 surge protection device



1249056

<https://www.phoenixcontact.com/gb/products/1249056>

Technical data

Product properties

Product type	Device protection
IEC power supply system	TN-S
Type	DIN rail module, two-section, divisible
Number of positions	2
Surge protection fault message	Optical, remote indicator contact

Insulation characteristics

Overvoltage category	III
Pollution degree	2
IEC test classification	III
	T3
EN type	T3
Number of ports	One

Electrical properties

Indicator/remote signaling


Connection name	Remote fault indicator contact
Switching function	Changeover contact
Operating voltage	250 V AC
	125 V DC (200 mA DC)
Operating current	0.5 A AC
	0.5 A DC (75 V DC)

Connection data

Connection method	Screw connection
Screw thread	M3
Tightening torque	0.5 Nm
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section AWG	24 ... 12

Dimensions

Dimensional drawing



PLT-EE-T3-60AC-R - Type 3 surge protection device



1249056

<https://www.phoenixcontact.com/gb/products/1249056>

Width	17.7 mm
Height	93.4 mm
Depth	71.3 mm (incl. DIN rail 7.5 mm)
Horizontal pitch	1 Div.

Material specifications

Color	light gray (RAL 7035)
	traffic gray B (RAL 7043)
Flammability rating according to UL 94	V-0
CTI value of material	600
Insulating material	PA 6.6-FR 20 % GF
	PA 6.6-FR
Housing material	PA 6.6-FR 20 % GF
	PA 6.6-FR

Protective circuit

Mode of protection	L-N
	L-PE
	N-PE
Direction of action	1L-N & N-PE
Nominal voltage U_N	60 V AC (TN-S)
Nominal frequency f_N	50 Hz (60 Hz)
Maximum continuous operating voltage U_C	80 V AC
Rated load current I_L	16 A (at 63 °C)
Protective conductor current I_{PE}	$\leq 5 \mu A$
Standby power consumption P_C	$\leq 5.3 \text{ mVA}$ (at U_{REF})
	$\leq 8.4 \text{ mVA}$ (at U_C)
Reference test voltage U_{REF}	66 V AC
Nominal discharge current I_n (8/20) μs	2 kA
Combination wave U_{OC}	4 kV
Voltage protection level U_p (L-N)	$\leq 0.48 \text{ kV}$
Voltage protection level U_p (L-PE)	$\leq 0.8 \text{ kV}$
Voltage protection level U_p (N-PE)	$\leq 0.8 \text{ kV}$
TOV behavior at U_T (L-N)	120 V AC (120 min / withstand mode)
TOV behavior at U_T (L-PE)	120 V AC (120 min / withstand mode)
Response time t_A (L-N)	$\leq 25 \text{ ns}$
Response time t_A (L-PE)	$\leq 100 \text{ ns}$
Response time t_A (N-PE)	$\leq 100 \text{ ns}$
Short-circuit current rating I_{SCCR}	6 kA AC
Maximum backup fuse for through wiring	16 A (gG / B / C)
Max. backup fuse with branch wiring	16 A (gG / B / C)

Additional technical data

Residual voltage U_{res} (L-N)	$\leq 0.42 \text{ kV}$ (at 1 kA)
	$\leq 0.48 \text{ kV}$ (at 2 kA)

PLT-EE-T3-60AC-R - Type 3 surge protection device



1249056

<https://www.phoenixcontact.com/gb/products/1249056>

Residual voltage U_{res} (L-PE)	≤ 0.4 kV (at $U_{OC} = 2$ kV)
	≤ 0.55 kV (at 1 kA)
	≤ 0.6 kV (at 2 kA)
Residual voltage U_{res} (N-PE)	≤ 0.6 kV (at $U_{OC} = 2$ kV)
	≤ 0.55 kV (at 1 kA)
	≤ 0.6 kV (at 2 kA)
	≤ 0.6 kV (at $U_{OC} = 2$ kV)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m (operating voltage remote contact ≤ 250 V)
	≤ 6000 m (operating voltage remote contact ≤ 150 V)
Permissible humidity (operation)	5 % ... 95 %
Shock (operation)	30g (Half-sine / 11 ms / 3x $\pm X$, $\pm Y$, $\pm Z$)
Vibration (operation)	5g (5 ... 500 Hz / 2.5 h / X, Y, Z)

Standards and regulations

Standards/specifications	IEC 61643-11
Note	2011

EN 61643-11

Standards/specifications	EN 61643-11
Note	2012

Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------

PLT-EE-T3-60AC-R - Type 3 surge protection device




1249056

<https://www.phoenixcontact.com/gb/products/1249056>

Drawings

Dimensional drawing




PLT-EE-T3-60AC-R - Type 3 surge protection device



1249056


<https://www.phoenixcontact.com/gb/products/1249056>

Diagram



Nominal current depending on ambient temperature

Circuit diagram



PLT-EE-T3-60AC-R - Type 3 surge protection device



1249056

<https://www.phoenixcontact.com/gb/products/1249056>

Classifications

ECLASS

ECLASS-13.0	27171203
ECLASS-15.0	27171203

ETIM

ETIM 10.0	EC000942
-----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

PLT-EE-T3-60AC-R - Type 3 surge protection device



1249056

<https://www.phoenixcontact.com/gb/products/1249056>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk