

# MACX MCR-EX-AP-2T-2I-SP - Temperature measuring transducer



1290849

<https://www.phoenixcontact.com/gb/products/1290849>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ex i-Temperature transducer, input signals from resistance thermometers in 2, 3, or 4-conductor technology, thermocouples, and mV sources are converted into active 0 mA / 4 mA ... 20 mA non Ex i signals. number of channels: 2, Standard configuration, 5-way isolation, Push-in connection

## Commercial data

Item number	1290849
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DK121W
Product key	DK121W
GTIN	4063151523077
Weight per piece (including packing)	220.5 g
Weight per piece (excluding packing)	133.1 g
Customs tariff number	85437090
Country of origin	DE

# MACX MCR-EX-AP-2T-2I-SP - Temperature measuring transducer



1290849

<https://www.phoenixcontact.com/gb/products/1290849>

## Technical data

### Notes

Note on application	Accuracy, typically specified as a percentage of the basic measuring range at $U_N$ , 23°C
Notes on operation	Installation conditions influence the ambient temperature. Please refer to the operating instructions.
Notes on operation	Output behavior = 2.4 mA (0 mA ... 23 mA or "Hold last value" can be configured)
Notes on operation	Sensor set via software or DIP switches
Notes on operation	2-conductor comparison set via DIP switch ADJ
Note on application	The input variables can be set via the ISpac Wizard parameterization software or DIP switches.

### Product properties

Product type	Temperature transmitter
Product family	MACX Analog
No. of channels	2
Configuration	Software

### System properties

#### Functionality

Configuration	Software
---------------	----------

### Electrical properties

Electrical isolation	5-way isolation
Electrical isolation between input and output	yes
Temperature coefficient, typical	$\leq 0.1\%$ (10 K)
Reverse polarity protection	yes

#### Electrical isolation Input/output IEC/EN 60079-11

Standards/regulations	IEC/EN 60079-11
Rated insulation voltage	375 V <sub>PP</sub>

#### Electrical isolation Input/power supply IEC/EN 60079-11

Standards/regulations	IEC/EN 60079-11
Rated insulation voltage	375 V <sub>PP</sub>

#### Electrical isolation Input/error message output IEC/EN 60079-11

Standards/regulations	IEC/EN 60079-11
Rated insulation voltage	375 V <sub>PP</sub>

#### Electrical isolation Input/configuration interface IEC/EN 60079-11

Standards/regulations	IEC/EN 60079-11
Rated insulation voltage	375 V <sub>PP</sub>

# MACX MCR-EX-AP-2T-2I-SP - Temperature measuring transducer



1290849

<https://www.phoenixcontact.com/gb/products/1290849>

## Electrical isolation Output 1/output 2

Test voltage	350 V (50 Hz, 60 s)
--------------	---------------------

## Electrical isolation Output/supply

Test voltage	350 V (50 Hz, 60 s)
--------------	---------------------

## Electrical isolation Output/configuration interface

Test voltage	350 V (50 Hz, 60 s)
--------------	---------------------

## Electrical isolation Output/supply/error message output

Test voltage	350 V (50 Hz, 60 s)
--------------	---------------------

## Supply

Nominal supply voltage	24 V DC
Supply voltage range	18 V ... 31.2 V
Power dissipation	≤ 1.9 W
Power consumption	≤ 1.9 W

## Input data

### Measurement

Description of the input	Resistance thermometer
Sensor types (RTD) that can be used	Pt 100, Pt 250, Pt 500, Pt 1000, Pt 2000, Ni 100, Ni 500, Ni 1000, M50, M53, M100
Temperature measuring range	-200 °C ... 1100 °C (Range depending on the sensor type)
Connection technology	2-, 3-, 4-conductor
Max. permissible overall conductor resistance	50 Ω (per wire, 2-conductor circuit) 100 Ω (per wire, 3-, 4-conductor circuit)
Temperature measuring range	≥ 51 K (Range depending on the sensor type)

### Measurement

Description of the input	Thermocouple
Sensor types that can be used (TC)	B, E, J, K, N, R, S, T, L, U, XK
Temperature measuring range	-200 °C ... 1800 °C (Range depending on the sensor type)
Max. permissible overall conductor resistance	≤ 1000 Ω (per wire)
Temperature measuring range	≥ 36 K (Range depending on the sensor type)

### Measurement

Description of the input	Potentiometer
Connection technology	3-conductor
Linear resistance measuring range	50 Ω ... 500 Ω 0.5 kΩ ... 5 kΩ 1 kΩ ... 10 kΩ 10 kΩ ... 100 kΩ (with parallel 10 kΩ shunt, no wire-break monitoring)

# MACX MCR-EX-AP-2T-2I-SP - Temperature measuring transducer



1290849

<https://www.phoenixcontact.com/gb/products/1290849>

## Output data

Signal: Error message output

Maximum switching voltage	30 V
Max. switching current	100 mA

Signal: Current

Current output signal	0 mA ... 20 mA (configurable)
	4 mA ... 20 mA (configurable)
	0 mA ... 21 mA (Function area)
Load	0 Ω ... 600 Ω (per channel)

## Connection data

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 16

## Ex data

Ex installation (EPL)	Gc
Ex i circuits (EPL)	[Ga]
	[Da]
	[Ma]

## Safety data

Max. internal inductance $L_i$	negligible
Max. internal capacitance $C_i$	negligible
Max. output voltage $U_o$	6.5 V
Max. output current $I_o$	19.7 mA
Max. output power $P_o$	32 mW (linear characteristic curve)
Safety-related maximum voltage $U_m$	253 V AC
IIA (simple circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	700 mH / 1000 μF
IIB (simple circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	330 mH / 570 μF
IIC (simple circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	90 mH / 25 μF
I (simple circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	700 mH / 1000 μF

## Interfaces

Designation	Configuration interface
Note	Note on application All device functions and diagnostics
Connection method	4-pos. socket

# MACX MCR-EX-AP-2T-2I-SP - Temperature measuring transducer



1290849

<https://www.phoenixcontact.com/gb/products/1290849>

Type	RS-232-C
Software	ISpac Wizard 9199

## Signaling

Status display	Green LED (supply voltage)
	Red LED (line errors)

## Dimensions

Dimensional drawing	
Width	17.5 mm
Height	107.8 mm
Depth	113.7 mm
Depth NS 35/7,5	114.5 mm (Snapped onto DIN rail NS 35/7,5 in accordance with EN 60715)

## Material specifications

Flammability rating according to UL 94	V0
Housing material	PA 6.6

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20 (Terminal blocks)
	IP30 (Housing)
Ambient temperature (operation)	-20 °C ... 70 °C (Stand-alone device: any mounting position)
	-20 °C ... 40 °C (Group assembly: vertical DIN rail without circulating air)
	-20 °C ... 60 °C (Group assembly: vertical DIN rail with circulating air)
	-20 °C ... 50 °C (Group assembly: horizontal DIN rail without circulating air)
	-20 °C ... 70 °C (Group assembly: horizontal DIN rail with circulating air)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m
Permissible humidity (operation)	≤ 95 % (non-condensing)

## Approvals

ATEX

# MACX MCR-EX-AP-2T-2I-SP - Temperature measuring transducer



1290849

<https://www.phoenixcontact.com/gb/products/1290849>

Identification	⊕ II (1) G [Ex ia Ga] IIC
	⊕ II (1) D [Ex ia Da] IIIC
	⊕ II 3 (1) G Ex nA nC [ia Ga] IIC T4 Gc
	⊕ I (M1) [Ex ia Ma] I

## IECEEx

Identification	[Ex ia Ga] IIC
	[Ex ia Da] IIIC
	Ex nA nC [ia Ga] IIC T4 Gc
	[Ex ia Ma] I

## EMC data

Electromagnetic compatibility	Tested in accordance with the following standards and regulations: EN 61326-1 For industrial use, NAMUR NE 21
-------------------------------	---

## Standards and regulations

Electrical isolation	5-way isolation
----------------------	-----------------

## Mounting

Mounting type	NS 35/15, NS 35/7,5
Mounting position	vertical, horizontal


# MACX MCR-EX-AP-2T-2I-SP - Temperature measuring transducer

1290849

<https://www.phoenixcontact.com/gb/products/1290849>

## Drawings

Dimensional drawing




# MACX MCR-EX-AP-2T-2I-SP - Temperature measuring transducer

1290849

<https://www.phoenixcontact.com/gb/products/1290849>

Block diagram



# MACX MCR-EX-AP-2T-2I-SP - Temperature measuring transducer



1290849

<https://www.phoenixcontact.com/gb/products/1290849>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1290849>



**IECEX**

Approval ID: IECEX BVS 21.0035X



**ATEX**

Approval ID: BVS 21 ATEX E 033X

# MACX MCR-EX-AP-2T-2I-SP - Temperature measuring transducer



1290849

<https://www.phoenixcontact.com/gb/products/1290849>

## Classifications

### ECLASS

ECLASS-13.0	27210129
ECLASS-15.0	27210129

### ETIM

ETIM 10.0	EC002919
-----------	----------

### UNSPSC

UNSPSC 21.0	41112100
-------------	----------

# MACX MCR-EX-AP-2T-2I-SP - Temperature measuring transducer



1290849

<https://www.phoenixcontact.com/gb/products/1290849>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead titanium zirconium oxide(CAS: 12626-81-2)
	Lead(CAS: 7439-92-1)
SCIP	1d9c4574-f017-434a-b95c-e8665fc27c3b

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)