

SACC-CI-M12FSX-8CON-L180 TOR32 - Contact carrier



1413446

<https://www.phoenixcontact.com/gb/products/1413446>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Ethernet CAT6_A, 8-position, Socket, straight, M12, X-coding, THR solder connection, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate

Commercial data

Item number	1413446
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	ABQAGT
Product key	ABQAGT
GTIN	4046356999083
Weight per piece (including packing)	7.365 g
Weight per piece (excluding packing)	3.329 g
Customs tariff number	85366990
Country of origin	DE

SACC-CI-M12FSX-8CON-L180 TOR32 - Contact carrier



1413446

<https://www.phoenixcontact.com/gb/products/1413446>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Application	Data
Number of positions	8
Seal present	no
Shielded	yes
Coding	X
Thread type	M12

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	< 5 mΩ
Insulation resistance	> 100 MΩ
Nominal voltage U_N	50 V AC 60 V DC
Nominal current I_N	0.5 A
Transmission characteristics (category)	CAT6 _A

Connection data

Connection method	THR solder connection
-------------------	-----------------------

Interfaces

Signal type/category	Ethernet CAT6 _A
----------------------	----------------------------

Material specifications

Material Contact carrier	PA 6T/66
Material Contact	CuZn
Material Contact surface	Ni/Au
Flammability rating according to UL 94	V0

Connector

SACC-CI-M12FSX-8CON-L180 TOR32 - Contact carrier



1413446

<https://www.phoenixcontact.com/gb/products/1413446>

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	X

Cable/line

Signal type/category	Ethernet CAT6 _A
----------------------	----------------------------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (correctly plugged in and locked)
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 95 °C
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-109

Packaging specifications


Type of packaging	Belt
Delivery state	with assembly pad

SACC-CI-M12FSX-8CON-L180 TOR32 - Contact carrier

1413446

<https://www.phoenixcontact.com/gb/products/1413446>

Drawings



Pin assignment M12 connector, 8-pos., view socket side

SACC-CI-M12FSX-8CON-L180 TOR32 - Contact carrier





1413446

<https://www.phoenixcontact.com/gb/products/1413446>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1413446>

 cUL Recognized Approval ID: E335024-20120308				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	0.5 A	-	-

 UL Recognized Approval ID: E335024-20120308				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	0.5 A	-	-

SACC-CI-M12FSX-8CON-L180 TOR32 - Contact carrier



1413446

<https://www.phoenixcontact.com/gb/products/1413446>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CI-M12FSX-8CON-L180 TOR32 - Contact carrier



1413446

<https://www.phoenixcontact.com/gb/products/1413446>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk