

# SACC-CI-M12MSL-4FE-L180 THR SH T - Contact carrier



1421314

<https://www.phoenixcontact.com/gb/products/1421314>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Power, 5-position, Pin, straight, M12, L-coding, THR solder connection, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Your advantages

- For compact devices: transmit high power in a confined space
- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration, thanks to mechanical port screw connections with threaded fastening
- Additional gasket for the device when not plugged in

## Commercial data

Item number	1421314
Packing unit	60 pc
Minimum order quantity	60 pc
Sales key	ABQAGE
Product key	ABQAGE
GTIN	4055626280639
Weight per piece (including packing)	4.891 g
Weight per piece (excluding packing)	3.451 g
Customs tariff number	85366990
Country of origin	DE

# SACC-CI-M12MSL-4FE-L180 THR SH T - Contact carrier



1421314

<https://www.phoenixcontact.com/gb/products/1421314>

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Notes on operation	FE not connected to metal parts that can be touched, no protective function

### Product properties

Product type	Contact insert
Application	Power
Number of positions	5
Connection profile	4+FE
No. of power contacts	4
Seal present	yes
Shielded	yes
Coding	L
Thread type	M12

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage	1.5 kV
Nominal voltage $U_N$	63 V
Nominal current $I_N$	16 A

### Connection data

Connection method	THR solder connection
-------------------	-----------------------

### Interfaces

Signal type/category	Power
----------------------	-------

### Material specifications

Material Contact carrier	PA 4T
Material Contact	CuZn
Material Contact surface	Au
Material Seal	FKM
Flammability rating according to UL 94	V0

## Connector

# SACC-CI-M12MSL-4FE-L180 THR SH T - Contact carrier



1421314

<https://www.phoenixcontact.com/gb/products/1421314>

## Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Coding	L

## Cable/line

Signal type/category	Power
----------------------	-------

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67 (correctly plugged in and locked)
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 105 °C -40 °C ... 105 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

## Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-111

## Packaging specifications

Type of packaging	Tray
Delivery state	with assembly pad


# SACC-CI-M12MSL-4FE-L180 THR SH T - Contact carrier

1421314

<https://www.phoenixcontact.com/gb/products/1421314>

## Drawings

Schematic diagram



Pin assignment of M12 connector, 5-pos., L-coded, pin side view

# SACC-CI-M12MSL-4FE-L180 THR SH T - Contact carrier



1421314

<https://www.phoenixcontact.com/gb/products/1421314>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1421314>

 <b>cULus Recognized</b> Approval ID: E468743-20180113				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	63 V	16 A	-	-

# SACC-CI-M12MSL-4FE-L180 THR SH T - Contact carrier



1421314

<https://www.phoenixcontact.com/gb/products/1421314>

## Classifications

### ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

### ETIM

ETIM 10.0	EC003557
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-CI-M12MSL-4FE-L180 THR SH T - Contact carrier



1421314

<https://www.phoenixcontact.com/gb/products/1421314>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)