

# CUC-PPC-C2ZNI-SX/24FKP5 - Power connector



1421783

<https://www.phoenixcontact.com/gb/products/1421783>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power connector, design: Version 14, degree of protection: IP65/IP67, number of positions: 5, material: Metal, connection method: Spring-cage connection, connection cross section: AWG 18-13, cable outlet: straight, Universal

## Your advantages

- Fixed coding
- Increased temperature range
- Lockable
- One-part housing

## Commercial data

Item number	1421783
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ABNOHA
Product key	ABNOHA
GTIN	4055626280349
Weight per piece (including packing)	110.9 g
Weight per piece (excluding packing)	116.386 g
Customs tariff number	85366990
Country of origin	PL

1421783

<https://www.phoenixcontact.com/gb/products/1421783>

## Technical data

### Product properties

Product type	Data connector (cable side)
Type	Version 14
Number of positions	5
Connection profile	MSTB
Shielded	no
Cable outlet	straight

### Insulation characteristics

Overvoltage category	I
Degree of pollution	3

### Electrical properties

Rated voltage (II/2)	630 V
Rated voltage (III/2)	400 V
Rated voltage (III/3)	24 V
	250 V
Rated surge voltage (II/2)	4 kV
Rated surge voltage (III/2)	4 kV
Rated surge voltage (III/3)	4 kV
Rated current	16 A (at 20 °C)
	16 A
Nominal voltage $U_N$	24 V
Nominal current $I_N$	16 A
Transmission medium	Copper
Power transmission	PoE

### Connection data

#### Connection technology

Connection method	Spring-cage connection
Connection cross section AWG	18 ... 13
Conductor cross-section	0.75 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>

### Interfaces

Signal type/category	Universal
----------------------	-----------

### Dimensions

Width	31 mm
Height	36 mm
Length	67 mm

### Material specifications

# CUC-PPC-C2ZNI-SX/24FKP5 - Power connector



1421783

<https://www.phoenixcontact.com/gb/products/1421783>

Material	Metal
Flammability rating according to UL 94	V0
Seal material	NBR
Housing material	Metal
Housing surface material	nickel-plated
Cable seal material	TPE
Contact material	Copper alloy
Contact surface material	Gold over nickel
Contact carrier material	PA

## Cable/line

Signal type/category	Universal
External cable diameter	9 mm ... 13 mm
Stripping length of the individual wire	10 mm
Cable cross section	0.75 mm <sup>2</sup>

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

## Drawings

### Schematic diagram



Pin assignment PROFINET push-pull, power connector, 24 V, fixed coding

# CUC-PPC-C2ZNI-SX/24FKP5 - Power connector



1421783

<https://www.phoenixcontact.com/gb/products/1421783>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1421783>

 <b>cULus Recognized</b> Approval ID: E118976-20080903				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	24 V	16 A	- 14	-

# CUC-PPC-C2ZNI-SX/24FKP5 - Power connector



1421783

<https://www.phoenixcontact.com/gb/products/1421783>

## Classifications

### ECLASS

ECLASS-13.0	27440290
ECLASS-15.0	27440114

### ETIM

ETIM 10.0	EC002636
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1421783

<https://www.phoenixcontact.com/gb/products/1421783>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	2.461 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)