

VAL-SPP-T1-1500DC-PV-2+V-UT - Surge arrester



1784479

<https://www.phoenixcontact.com/gb/products/1784479>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surge arrester for 2-pos. insulated and grounded 1500 V DC PV systems, for DIN rail mounting, 3-pos. base element, three pluggable protective elements, two of them temperature monitored, status message on + and - plugs.

Your advantages

- Easy and safe installation with forward-thinking handling and safety features
- Reliable system protection with maximum performance and endurance
- Can be used in a wide range of applications due to the optimized design and broad portfolio
- Simple planning due to comprehensive digital data and selectors

Commercial data

Item number	1784479
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	CL11E1
Product key	CL11E1
GTIN	4067923402218
Weight per piece (including packing)	551 g
Weight per piece (excluding packing)	485.31 g
Customs tariff number	85354000
Country of origin	DE

1784479

<https://www.phoenixcontact.com/gb/products/1784479>

Technical data

Product properties

Product type	PV arrester
IEC test classification	PV I / II
EN type	PV T1 / T2
IEC power supply system	DC
Type	DIN rail module, two-section, divisible
Environment	Indoor
Installation location of the disconnect device	Internal
Accessibility	Accessible
End-of-life mode	OCFM (Open-Circuit Failure Mode)
Surge protection fault message	optical
Number of ports	One

Insulation characteristics

Overvoltage category	III
Pollution degree (Main circuit)	2

Electrical properties

Maximum power dissipation for nominal condition	≤ 150 mVA
-------------------------------------------------	-----------

Connection data

protection circuit (DC+, DC-, PE)

Connection method	Screw connection
Screw thread	M5
Stripping length	12 mm
Conductor cross-section rigid	1.5 mm ² ... 25 mm ²
Conductor cross-section flexible	1.5 mm ² ... 16 mm ²
Conductor cross-section AWG	15 ... 4
Conductor cross-section, flexible, with ferrule, without plastic sleeve	1.5 mm ² ... 16 mm ²
Conductor cross-section, flexible, with ferrule, with plastic sleeve	1.5 mm ² ... 16 mm ²
2 conductors with same cross section, rigid	1.5 mm ² ... 6 mm ²
2 conductors with same cross section, flexible	1.5 mm ² ... 6 mm ²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	1.5 mm ² ... 6 mm ²
2 conductors with the same cross section, flexible, with ferrule with plastic sleeve	1.5 mm ² ... 6 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	1.5 mm ² ... 6 mm ²
Drive size	PZSL 2 PZ/S 2
Tightening torque	2.5 Nm ... 3 Nm


VAL-SPP-T1-1500DC-PV-2+V-UT - Surge arrester



1784479

<https://www.phoenixcontact.com/gb/products/1784479>

Dimensions

Dimensional drawing	
Width	53.4 mm
Height	96.6 mm
Depth	95.5 mm (incl. DIN rail 7.5 mm)
Horizontal pitch	3 Div.

Material specifications

Color	gray (RAL 7042) light gray (RAL 7035)
Material Housing	PA 6.6-FR 20 % GF PBT
Flammability rating according to UL 94	V-0
Insulating material	PA 6.6-FR 20 % GF PBT

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Protective circuit

Mode of protection	(DC+) - (DC-) (DC+) - PE (DC-) - PE
Max. continuous voltage U_{CPV}	1500 V DC
Open-circuit voltage U_{OCSTC}	1250 V DC
Protective conductor current I_{PE}	$\leq 700 \mu\text{A AC}$ $\leq 100 \mu\text{A DC}$
Continuous current I_{CPV}	$\leq 100 \mu\text{A DC}$
Maximum power dissipation for nominal condition	$\leq 150 \text{ mVA}$
Nominal discharge current I_n (8/20) μs	20 kA
Max. discharge current I_{max} (8/20) μs	40 kA
Impulse discharge current	6.25 kA (3.1 As / 9.8 kJ/ Ω)
Total discharge current I_{Total} (8/20) μs	60 kA
Total discharge current I_{Total} (10/350) μs	12.5 kA
Short-circuit current rating I_{SCPV}	15000 A
Voltage protection level U_p	$\leq 4.5 \text{ kV}$
Residual voltage U_{res}	$\leq 4.5 \text{ kV (at } I_n)$ $\leq 4.5 \text{ kV (at } I_n)$

VAL-SPP-T1-1500DC-PV-2+V-UT - Surge arrester



1784479

<https://www.phoenixcontact.com/gb/products/1784479>

	$\leq 4.5 \text{ kV (at } I_n)$
	$\leq 4.5 \text{ kV (at } I_n)$
Response time t_A	$\leq 25 \text{ ns}$

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20C (under touch protection cover)
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Altitude	$\leq 4000 \text{ m (amsl)}$
Permissible humidity (operation)	5 % ... 95 %
Shock (operation)	25g (Half-sine / 11 ms / 3x $\pm X$, $\pm Y$, $\pm Z$)
Vibration (operation)	5g (5-500 Hz/2.5 h/XYZ)

Standards and regulations

Standards/specifications	IEC 61643-31
Note	2018
Standards/specifications	EN 61643-31
Note	2019 + AC: 2022

Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------


VAL-SPP-T1-1500DC-PV-2+V-UT - Surge arrester

1784479

<https://www.phoenixcontact.com/gb/products/1784479>

Drawings

Dimensional drawing




VAL-SPP-T1-1500DC-PV-2+V-UT - Surge arrester

1784479

<https://www.phoenixcontact.com/gb/products/1784479>



Circuit diagram



VAL-SPP-T1-1500DC-PV-2+V-UT - Surge arrester



1784479

<https://www.phoenixcontact.com/gb/products/1784479>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1784479>

DEKRA

Approval ID: 31-172928

VAL-SPP-T1-1500DC-PV-2+V-UT - Surge arrester



1784479

<https://www.phoenixcontact.com/gb/products/1784479>

Classifications

ECLASS

ECLASS-13.0	27171401
ECLASS-15.0	27171401

ETIM

ETIM 10.0	EC000381
-----------	----------

VAL-SPP-T1-1500DC-PV-2+V-UT - Surge arrester



1784479

<https://www.phoenixcontact.com/gb/products/1784479>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk