

# IL ETH BK DI8 DO4 2TX-PAC - Bus coupler



2703981

<https://www.phoenixcontact.com/gb/products/2703981>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline, Bus coupler, Modbus/TCP (UDP), RJ45 jack, Digital inputs: 8, 24 V DC, connection technology: 3-conductor, Digital outputs: 4, 24 V DC, 500 mA, connection technology: 3-conductor, transmission speed in the local bus: 500 kbps / 2 Mbps, degree of protection: IP20, including Inline connectors and marking fields

## Product description

The bus coupler with integrated I/Os is intended for use within a Modbus/TCP (UDP) network and represents the link to the Inline I/O system. Up to 61 Inline devices can be connected to the bus coupler. The bus coupler supports a maximum of 16 PCP devices.

## Your advantages

- 2 Ethernet ports (with integrated switch)
- Transmission speed of 10 Mbps and 100 Mbps
- Automatic detection of the transmission speed in the local bus (500 kbps or 2 Mbps)
- 8 digital inputs, 4 digital outputs (on-board)
- Firmware can be updated
- Data exchange via OPC server supported
- Software interface for access via TCP/IP: Device Driver Interface (DDI)
- Web-based management

## Commercial data

Item number	2703981
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DRI11B
Product key	DRI11B
GTIN	4046356041157
Weight per piece (including packing)	331.3 g
Weight per piece (excluding packing)	341.14 g
Customs tariff number	85176200
Country of origin	DE

# IL ETH BK DI8 DO4 2TX-PAC - Bus coupler




2703981

<https://www.phoenixcontact.com/gb/products/2703981>

## Technical data

### Dimensions

Dimensional drawing	
Width	80 mm
Height	119.8 mm
Depth	71.5 mm
Note on dimensions	Housing dimensions

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

#### Utilization restriction

CCcex note	Use in potentially explosive areas is not permitted in China.
------------	---

### Material specifications

Color (Housing)	green (RAL 6021)
-----------------	------------------

### Interfaces

Supported protocols	Modbus/TCP (UDP)
	SNMP
	HTTP
	TFTP
	FTP
	BootP
	DHCP

#### Modbus/TCP (UDP)

Number of interfaces	2
Connection method	RJ45 jack
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Ethernet in RJ45 twisted pair

#### Inline local bus

Number of interfaces	1
Connection method	Inline data jumper
Transmission speed	500 kbps / 2 Mbps (automatic detection, no combined system)

## System properties

### System limits

Number of supported devices	max. 63 (per station)
Number of local bus devices that can be connected	max. 61 (The on-board I/Os are two devices)
Number of devices with parameter channel	max. 16
Number of supported branch terminals with remote bus branch	0

### Programming data

Input address area	8 bit
Output address area	4 bit
Register length (bus)	16 bit
Register length (master)	512 Byte

## Input data

### Digital:

Input name	Digital inputs
Description of the input	EN 61131-2 type 1
Number of inputs	8
Connection method	Inline connector
Connection technology	3-conductor
Input voltage	24 V DC
Input voltage range "0" signal	-30 V DC ... 5 V DC
Input voltage range "1" signal	15 V DC ... 30 V DC
Nominal input voltage $U_{IN}$	24 V DC
Nominal input current at $U_{IN}$	typ. 3 mA
Current flow	Limited to 3 mA, maximum
Typical input current per channel	typ. 3 mA
Typical response time	approx. 500 $\mu$ s
Delay at signal change from 0 to 1	1.2 ms
Delay at signal change from 1 to 0	1.2 ms

## Output data

### Digital:

Output name	Digital outputs
Connection method	Inline connector
Connection technology	3-conductor
Number of outputs	4
Protective circuit	Short-circuit and overload protection; Freewheeling circuit in the output driver
Output voltage	24 V DC -1 V (At nominal current)
Max. current carrying capacity per output	max. 500 mA
Maximum output current per module	max. 2 A
Nominal output voltage	24 V DC

Output current when switched off	max. 10 $\mu$ A (When not loaded, a voltage can be measured even at an output that is not set.)
Nominal load, inductive	12 VA (1.2 H, 48 $\Omega$ )
Nominal load, lamp	12 W
Nominal load, ohmic	12 W
Reverse voltage resistance to short pulses	Reverse voltage proof
Behavior with overload	Auto restart
Behavior with inductive overload	Output can be destroyed
Behavior at voltage switch-off	The output follows the power supply without delay
Signal delay	typ. 1.2 ms
Overcurrent shut-down	min. 0.7 A

## Product properties

Product type	I/O component
Product family	Inline
Type	modular
Mounting position	any
Scope of supply	including Inline connectors and marking fields
No. of channels	12
Diagnostics messages	Short-circuit or overload of the digital outputs yes
	Sensor supply failure yes
	Failure of the actuator supply yes

## Insulation characteristics

Overvoltage category	II (IEC 60664-1, EN 60664-1)
Pollution degree	2 (IEC 60664-1, EN 60664-1)

## Electrical properties

Maximum power dissipation for nominal condition	6.3 W
---	-------

Potentials: Bus coupler supply  $U_{BK}$ ; Communications power  $U_L$  (7.5 V) and the analog supply  $U_{ANA}$  (24 V) are generated from the bus coupler supply.

Supply voltage	24 V DC (via Inline connector)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 0.98 A (with max. number of connected I/O terminal blocks)
	min. 80 mA (without connected I/O terminal blocks)

Potentials: Communications power ( $U_L$ )

Supply voltage	7.5 V DC
Power supply	max. 0.8 A DC

Potentials: Supply of analog modules ( $U_{ANA}$ )

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Power supply	max. 0.5 A DC

Potentials: Main circuit supply ( $U_M$ )

# IL ETH BK DI8 DO4 2TX-PAC - Bus coupler



2703981

<https://www.phoenixcontact.com/gb/products/2703981>

Supply voltage	24 V DC (via Inline connector)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Power supply	max. 8 A DC (sum of $U_M + U_S$ )
Current draw	max. 8 A DC min. 3 mA (without connected peripherals)

## Potentials: Segment circuit supply ( $U_S$ )

Supply voltage	24 V DC (via Inline connector)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Power supply	max. 8 A DC (sum of $U_M + U_S$ )
Current draw	max. 8 A DC min. 3 mA (without connected peripherals)

## Electrical isolation/isolation of the voltage ranges

Test voltage: Ethernet interface 1 / Ethernet interface 2	500 V AC, 50 Hz, 1 min
Test voltage: Ethernet interface 1 / logic ( $U_{BK}$ , $U_L$ , $U_{ANA}$ )	500 V AC, 50 Hz, 1 min
Test voltage: Ethernet interface 1 / I/O ( $U_M$ , $U_S$ )	500 V AC, 50 Hz, 1 min
Test voltage: Ethernet interface 1 / functional ground	500 V AC, 50 Hz, 1 min
Test voltage: Ethernet interface 2 / logic ( $U_{BK}$ , $U_L$ , $U_{ANA}$ )	500 V AC, 50 Hz, 1 min
Test voltage: Ethernet interface 2 / I/O ( $U_M$ , $U_S$ )	500 V AC, 50 Hz, 1 min
Test voltage: Ethernet interface 2 / functional ground	500 V AC, 50 Hz, 1 min
Test voltage: Communications power ( $U_{BK}$ , $U_L$ , $U_{ANA}$ ) / I/O ( $U_M$ , $U_S$ )	500 V AC, 50 Hz, 1 min
Test voltage: Communications power ( $U_{BK}$ , $U_L$ , $U_{ANA}$ ) / functional ground	500 V AC, 50 Hz, 1 min
Test voltage: I/O ( $U_M$ , $U_S$ ) / functional ground	500 V AC, 50 Hz, 1 min

## Connection data

### Connection technology

Connection name	Inline connector
-----------------	------------------

### Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-40 °C ... 85 °C

# IL ETH BK DI8 DO4 2TX-PAC - Bus coupler



2703981

<https://www.phoenixcontact.com/gb/products/2703981>

Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

## Mechanical test

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	5g
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	25g

## Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

# IL ETH BK DI8 DO4 2TX-PAC - Bus coupler


2703981

<https://www.phoenixcontact.com/gb/products/2703981>



## Drawings

Dimensional drawing




# IL ETH BK DI8 DO4 2TX-PAC - Bus coupler




2703981

<https://www.phoenixcontact.com/gb/products/2703981>

Dimensional drawing



Connection diagram



# IL ETH BK DI8 DO4 2TX-PAC - Bus coupler



2703981

<https://www.phoenixcontact.com/gb/products/2703981>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2703981>



**EAC**

Approval ID: TR TS\_S\_03508-21



**BV**

Approval ID: 20977/C1 BV



**RINA**

Approval ID: ELE121121XG

**DNV**

Approval ID: TAA00002CU



**cULus Recognized**

Approval ID: E140324



**BV**

Approval ID: 21725/C1 BV



**cULus Listed**

Approval ID: E199827

# IL ETH BK DI8 DO4 2TX-PAC - Bus coupler



2703981

<https://www.phoenixcontact.com/gb/products/2703981>

## Classifications

### ECLASS

ECLASS-13.0	27242608
ECLASS-15.0	27242608

### ETIM

ETIM 10.0	EC001604
-----------	----------

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------

# IL ETH BK DI8 DO4 2TX-PAC - Bus coupler



2703981

<https://www.phoenixcontact.com/gb/products/2703981>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	2fb1615a-a168-44ad-947e-20c70d64c7a5

### EF3.1 Climate Change

CO2e kg	10.21 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)