

# PR2-BSC2/4X21 - Relay base



2833563

<https://www.phoenixcontact.com/gb/products/2833563>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay base PR2-B, for industrial relay REL-IR with 2 or 4 changeover contacts, 2/2-level design, screw connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5

## Your advantages

- Relay retaining bracket with labeling field and ejection function
- Plug-in input/interference suppression modules

## Commercial data

Item number	2833563
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	DK6313
Product key	DK6313
GTIN	4017918933791
Weight per piece (including packing)	70 g
Weight per piece (excluding packing)	62.96 g
Customs tariff number	85366990
Country of origin	Information on the country of origin is provided with the delivery.

# PR2-BSC2/4X21 - Relay base



2833563

<https://www.phoenixcontact.com/gb/products/2833563>

## Technical data

### Product properties

Product type	Relay socket
--------------	--------------

### Electrical properties

Nominal voltage $U_N$	300 V AC/DC
Nominal current $I_N$	12 A

### Connection data

#### Input side

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (2 conductors with the same cross-section)
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (2 conductors with the same cross-section)
Conductor cross-section AWG	26 ... 14 26 ... 16 (2 conductors with the same cross-section)

#### Output side

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (2 conductors with the same cross-section)
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (2 conductors with the same cross-section)
Conductor cross-section AWG	26 ... 14 26 ... 16 (2 conductors with the same cross-section)

### Dimensions

Width	27 mm
Height	75 mm
Depth Retaining bracket	84 mm (EL2-P35)

### Material specifications

Color	green (RAL 6021)
-------	------------------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C
---------------------------------	------------------

# PR2-BSC2/4X21 - Relay base



2833563

<https://www.phoenixcontact.com/gb/products/2833563>

Ambient temperature (storage/transport)	-25 °C ... 85 °C
---	------------------

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

# PR2-BSC2/4X21 - Relay base

2833563

<https://www.phoenixcontact.com/gb/products/2833563>



## Classifications

### UNSPSC

UNSPSC 21.0	39122335
-------------	----------

# PR2-BSC2/4X21 - Relay base



2833563

<https://www.phoenixcontact.com/gb/products/2833563>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)