

# PT 2X1- 5DC-ST - Surge protection plug

2856061

<https://www.phoenixcontact.com/gb/products/2856061>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surge protection plug for the base element, coarse and fine protection for two signal wires with common reference potential, common mode voltage coarse protection to ground. Design: 5 V DC

## Your advantages

- Easy testing and documentation with CHECKMASTER 2 with pluggable protective modules
- Maximum ease of maintenance, thanks to the 2-piece design
- Easy selection for all possible demands in MCR applications with a complete product portfolio
- The signal is not influenced during maintenance work, thanks to the impedance-neutral insertion and removal of protective plugs

## Commercial data

Item number	2856061
Packing unit	10 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	CL2111
Product key	CL2111
GTIN	4017918599249
Weight per piece (including packing)	21.52 g
Weight per piece (excluding packing)	16.57 g
Customs tariff number	85363010
Country of origin	DE

# PT 2X1- 5DC-ST - Surge protection plug

2856061

<https://www.phoenixcontact.com/gb/products/2856061>

## Technical data

### Product properties

Product type	Surge protection for MCR technology
Product family	PLUGTRAB PT
IEC test classification	C1
	C2
	C3
	D1
VDE requirement class	C1
	C2
	C3
	D1
Type	Male
Arrester can be tested with CHECKMASTER from software version:	From SW rev. 1.00

### Insulation characteristics

Overvoltage category	III
Pollution degree	2


### Electrical properties

Nominal voltage $U_N$	5 V DC
-----------------------	--------

### Connection data

Connection method	Screw connection (in connection with the base element)
Screw thread	M3
Tightening torque	0.8 Nm
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

### Dimensions

Dimensional drawing	
Width	17.5 mm
Height	44.8 mm
Depth	51.7 mm
Horizontal pitch	1 Div.
Complete module width	17.7 mm
Complete module height	90 mm

# PT 2X1- 5DC-ST - Surge protection plug



2856061

<https://www.phoenixcontact.com/gb/products/2856061>

Complete module depth	65.5 mm
-----------------------	---------

## Material specifications

Color	black (RAL 9005) copper color
Flammability rating according to UL 94	V-0
Housing material	PA 6.6

## Mechanical properties

### Mechanical data

Open side panel	No
-----------------	----

## Protective circuit

Direction of action	Line-Line & Line-Signal Ground/Shield & optional Signal Ground/Shield-Earth Ground
Nominal voltage $U_N$	5 V DC
Maximum continuous operating voltage $U_C$	6 V DC 4 V AC
Rated current	300 mA (45 °C)
Operating effective current $I_C$ at $U_C$	$\leq 1$ mA
Protective conductor current $I_{PE}$	$\leq 1$ $\mu$ A (with PT 2X1+F-BE) $\leq 2$ mA (Directly grounded)
Nominal discharge current $I_n$ (8/20) $\mu$ s (line-ground)	10 kA
Pulse discharge current $I_{imp}$ (10/350) $\mu$ s	2.5 kA (per path)
Total discharge current $I_{Total}$ (8/20) $\mu$ s	20 kA
Max. discharge current $I_{max}$ (8/20) $\mu$ s maximum (line-earth)	10 kA
Nominal pulse current $I_{an}$ (10/1000) $\mu$ s (line-earth)	125 A
Output voltage limitation at 1 kV/ $\mu$ s (line-earth) spike	$\leq 14$ V $\leq 600$ V (with PT 2X1+F-BE)
Output voltage limitation at 1 kV/ $\mu$ s (line-earth) static	$\leq 10$ V
Residual voltage at $I_n$ (conductor-ground)	$\leq 10$ V
Residual voltage with $I_{an}$ (10/1000) $\mu$ s (line-earth)	$\leq 12$ V
Voltage protection level $U_p$ (line-earth)	$\leq 50$ V (C2 - 10 kV / 5 kA)
Response time $t_A$ (line-earth)	$\leq 1$ ns
Input attenuation aE, asym.	0.5 dB ( $\leq 200$ kHz)
Cut-off frequency $f_g$ (3 dB), asym. (PE) in 50 $\Omega$ system	typ. 1 MHz
Capacity (Core-Earth)	3 nF
Resistance per path	4.7 $\Omega$ (1-2/5-6/7-8/11-12)
Surge protection fault message	none
Max. required back-up fuse	315 mA (T)
Impulse durability (line-earth)	C2 - 10 kV / 5 kA D1 - 2.5 kA

## Environmental and real-life conditions

# PT 2X1- 5DC-ST - Surge protection plug



2856061

<https://www.phoenixcontact.com/gb/products/2856061>

## Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C

## Standards and regulations

VDE requirement class	C1
	C2
	C3
	D1

## Standards Information technology specification

Standards/regulations	IEC 61643-21
	DIN EN 61643-21
	UL 497B
	IEC 61643-21
	DIN EN 61643-21
UL 497B	

## Air clearances and creepage distances

Standards/regulations	VDE 0110-1 / IEC 60664-1
Standards/specifications	IEC 61643-21
Note	2000

## Mounting

Mounting type	on base element
---------------	-----------------


# PT 2X1- 5DC-ST - Surge protection plug

2856061

<https://www.phoenixcontact.com/gb/products/2856061>


## Drawings

Dimensional drawing



The figure shows the complete module consisting of a base element and connector

Circuit diagram



# PT 2X1- 5DC-ST - Surge protection plug



2856061

<https://www.phoenixcontact.com/gb/products/2856061>

## Classifications

### ECLASS

ECLASS-13.0

27171501

### ETIM

ETIM 9.0

EC001625

### UNSPSC

UNSPSC 21.0

39121600

# PT 2X1- 5DC-ST - Surge protection plug



2856061

<https://www.phoenixcontact.com/gb/products/2856061>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c7c764ee-5cd6-4a64-8e88-4ace77a3d978

### EF3.1 Climate Change

CO2e kg	0.896 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)