

PSM-ME-RS232/TTY-P - Interface converter



2744458

<https://www.phoenixcontact.com/gb/products/2744458>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Interface converter, for converting RS-232 (V.24) to TTY, with electrical isolation, 2 channels, rail-mountable

Product description

This converter converts a V.24 (RS-232) interface into a 20 mA TTY current loop interface bidirectionally. The interference immune TTY signal allows problem-free data transmission over distances of up to 1000 m using a twisted-pair and shielded 4-wire cable.

Your advantages

- Mounting on standard EN DIN rails
- Transmission distances of up to 1000 m in active TTY mode
- High-quality 3-way isolation up to 2 kV (VCC // RS-232 // TTY)
- In the case of variable cable lengths, the TTY connection on the field side can be established conveniently using plug-in screw terminal blocks
- Integrated surge protection with transient discharge to the DIN rail
- Conversion of RS-232 TxD/RxD full duplex data signals to the TTY current loop standard
- Semi-active, active or passive TTY mode, depending on pin assignment
- 24 V DC or AC power supply suitable for the control cabinet
- Active data transmission indicated by separate data indicators for the transmit and receive channels
- RS-232 connection via 9-pos. D-SUB and standard RS-232 cable
- Transmission speed of up to 19.2 kbps
- Shipbuilding approval in accordance with DNV GL

PSM-ME-RS232/TTY-P - Interface converter

2744458

<https://www.phoenixcontact.com/gb/products/2744458>



Commercial data

Item number	2744458
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DNC111
Product key	DNC111
GTIN	4017918171803
Weight per piece (including packing)	184 g
Weight per piece (excluding packing)	179.6 g
Customs tariff number	85176200
Country of origin	DE

PSM-ME-RS232/TTY-P - Interface converter



2744458

<https://www.phoenixcontact.com/gb/products/2744458>

Technical data

Notes

Note on application	Only for industrial use
Note on application	As things stand now, we are preparing the product so that, as of December 11, 2027, it will comply with the requirements of the EU Cyber Resilience Act (CRA) based on the information currently available regarding the CRA.
Utilization restriction	
CCCex note	Use in potentially explosive areas is not permitted in China.

Product properties

Product type	Interface converter
Application	RS-232
	TTY
MTBF	1989 Years (Telcordia standard, 25°C temperature, 21% operating cycle (5 days a week, 8 hours a day))
	410 Years (Telcordia standard, 40°C temperature, 34.25% operating cycle (5 days a week, 12 hours a day))

Electrical properties

Electrical isolation	VCC // V.24 (RS-232) // TTY
Maximum power dissipation for nominal condition	1.8 W
Test voltage data interface/power supply	2 kV _{rms} (50 Hz, 1 min.)
	2 kV AC
Test voltage data interfaces	2 kV AC

Supply

Supply voltage range	19.2 V AC/DC ... 28.8 V AC/DC
Nominal supply voltage	24 V AC/DC ±20 % (via pluggable COMBICON screw terminal block)
Typical current consumption	75 mA (24 V DC)
Protective circuit	Surge protection; Suppressor diode

Connection data

Supply

Tightening torque	0.56 Nm ... 0.79 Nm
-------------------	---------------------

Interfaces

Bit distortion	< 5 %
Bit delay	< 3 µs
Signal	Modbus
Transmission channels	2 (1/1), RxD, TxD, full duplex

Data: V.24 (RS-232) interface in acc. with ITU-T V.28, EIA/TIA-232, DIN 66259-1

PSM-ME-RS232/TTY-P - Interface converter



2744458

<https://www.phoenixcontact.com/gb/products/2744458>

Serial transmission speed	≤ 19.2 kbps
Connection method	D-SUB 9 plug
Pin assignment	DTE/DCE switchover via switch
Transmission length	15 m (shielded twisted pair)
Single-wire/terminal point, flexible	0.2 mm² ... 2.5 mm²
Max. AWG conductor cross-section, flexible	13
Min. AWG conductor cross-section, flexible	24
Protocols supported	transparent protocol

Data: TTY interface, CL2 in acc. with DIN 66348-1

Serial transmission speed	≤ 19.2 kbps
Connection method	Pluggable screw connection
Transmission length	1000 m (shielded twisted pair)
Single-wire/terminal point, flexible	0.2 mm² ... 2.5 mm²
Max. AWG conductor cross-section, flexible	13
Min. AWG conductor cross-section, flexible	24
Load/output load current output	≤ 500 Ω
Impedance	≤ 117 Ω (Output) 126 Ω (Input)
Output current	2x 20 mA ±10 % (Loop current)

Dimensions

Dimensional drawing	
Width	22.5 mm
Height	99 mm
Depth	118.6 mm

Material specifications

Color (Housing)	green (RAL 6021)
Material (Housing)	PA

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 55 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 5000 m (For restrictions, see the manufacturer's declaration for altitude operation)
Permissible humidity (operation)	10 % ... 95 % (non-condensing)

PSM-ME-RS232/TTY-P - Interface converter



2744458

<https://www.phoenixcontact.com/gb/products/2744458>

Approvals

CE

Certificate	CE-compliant
-------------	--------------

UL, USA/Canada

Identification	508 Recognized
	Class I, Div. 2, Groups A, B, C, D
	Class I, Zone 2, AEx nA IIC T4
	Class I, Zone 2, Ex nA IIC T4 Gc X

Corrosive gas test

Identification	ISA-S71.04-1985 G3 Harsh Group A
----------------	----------------------------------

Shipbuilding

Identification	DNV GL
----------------	--------

Shipbuilding data

Temperature	B
Humidity	A
Vibration	A
EMC	B
Enclosure	Required protection according to the Rules shall be provided upon installation on board

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise immunity	EN 61000-6-2:2005

Noise emission

Standards/regulations	EN 61000-6-4
-----------------------	--------------

Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

Electrostatic discharge

Contact discharge	± 6 kV (Test Level 3)
Discharge in air	± 8 kV (Test Level 3)
Comments	Criterion B

Electromagnetic HF field

Standards/regulations	EN 61000-4-3
-----------------------	--------------

Electromagnetic HF field

Frequency range	Test Level 3
Field intensity	10 V/m
Comments	Criterion A

Fast transients (burst)

PSM-ME-RS232/TTY-P - Interface converter



2744458

<https://www.phoenixcontact.com/gb/products/2744458>

Standards/regulations	EN 61000-4-4
-----------------------	--------------

Fast transients (burst)

Input	± 4 kV (5 kHz)
Signal	± 2 kV (5 kHz)
Comments	Criterion B

Surge current load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

Surge current load (surge)

Input	± 0.5 kV (2 Ω)
Signal	± 2 kV (42 Ω)
Comments	Criterion B

Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

Conducted interference

Comments	Criterion A
Voltage	10 V

Emitted interference

Standards/regulations	EN 55011
Comments	Class A, industrial applications

Criteria

Criterion A	Normal operating behavior within the specified limits.
Criterion B	Temporary impairment to operational behavior that is corrected by the device itself.

Mounting

Mounting type	DIN rail mounting
Mounting position	On horizontal DIN rail

PSM-ME-RS232/TTY-P - Interface converter


2744458

<https://www.phoenixcontact.com/gb/products/2744458>



Drawings


Dimensional drawing



Slim design

Application drawing

Electrical Isolation



Electrical isolation


PSM-ME-RS232/TTY-P - Interface converter

2744458

<https://www.phoenixcontact.com/gb/products/2744458>



Application drawing



Interface adaptation

A diagram of a mechanical assembly. A large, irregularly shaped block is shown. On the left side, a vertical wall is indicated by a line with diagonal hatching. A smaller, rectangular component is attached to the left side of the main block, resting against the wall. A thick black arrow labeled 'A' points downwards from the top of this smaller component. A thick black curved arrow labeled 'B' points from the right side of the main block towards the bottom-left, indicating a clockwise rotational force.

Aug 29, 2026, 2:33 PM Page 10 (13)

PSM-ME-RS232/TTY-P - Interface converter



2744458

<https://www.phoenixcontact.com/gb/products/2744458>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2744458>



cUL Recognized
Approval ID: E238705



UL Recognized
Approval ID: E238705



DNV GL
Approval ID: TAA00001KR_7

 cUL Recognized Approval ID: E199827				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	24 V	0.075 A	-	-



cUL Listed
Approval ID: E199827



UL Listed
Approval ID: E199827

PSM-ME-RS232/TTY-P - Interface converter



2744458

<https://www.phoenixcontact.com/gb/products/2744458>

Classifications

ECLASS

ECLASS-13.0	27242208
ECLASS-15.0	27242208

ETIM

ETIM 10.0	EC001423
-----------	----------

UNSPSC

UNSPSC 21.0	32151700
-------------	----------

PSM-ME-RS232/TTY-P - Interface converter



2744458

<https://www.phoenixcontact.com/gb/products/2744458>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	866dc614-eb99-4212-a3b5-c6b58345a1f7

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk