

# MINI-BAT/24DC/1.3AH - Battery module



2866417

<https://www.phoenixcontact.com/gb/products/2866417>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Battery module, lead AGM, VRLA technology, 24 V DC, 1.2 Ah.



## Product description

MINI-BAT – battery module with lead AGM technology for maximum buffer times.

## Your advantages

- Maximum buffer times

## Commercial data

Item number	2866417
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	CMUEV3
Product key	CMUEV3
GTIN	4046356152112
Weight per piece (including packing)	2,210 g
Weight per piece (excluding packing)	1,700 g
Customs tariff number	85072080
Country of origin	CN

# MINI-BAT/24DC/1.3AH - Battery module



2866417

<https://www.phoenixcontact.com/gb/products/2866417>

## Technical data

### Notes

#### General

Note on the battery	This product contains a battery with a limited shelf life that must be charged every few months. The product packaging indicates when the battery must be started up or recharged. The general shelf life can be found in the energy storage devices area under "Latest startup".
---------------------	---

### Input data

Input voltage	24 V DC
Buffer period	20 min (2 A) 5 min (5 A)

### Output data

Nominal output voltage	24 V DC
Output current $I_{\max}$	15 A
Output fuse	1x 15 A
Connection in parallel	5
Connection in series	no

#### Battery operation

Nominal output voltage	24 V DC
Nominal output current ( $I_N$ )	15 A

### Energy storage

End-of-charge voltage	27.6 V
Charging current	0.36 A
Nominal capacity	1.2 Ah
Service life	6 Years (20 °C)
Latest startup (battery only) - range	6 Months (0 °C ... 20 °C) 6 Months (20 °C ... 30 °C) 3 Months (30 °C ... 40 °C)
Battery technology	VRLA-AGM
Memory medium	Lead rechargeable battery module
Accumulator type	BB Battery BP1.2-12FR
Number of cells	1
Size designation	Block
Battery pack	yes
IQ technology	no
Suitable for fast charging	yes

### Product properties

Product type	Battery module
--------------	----------------

# MINI-BAT/24DC/1.3AH - Battery module



2866417

<https://www.phoenixcontact.com/gb/products/2866417>

Product family	Battery module (device with battery)
Application	for MINI DC-UPS
Disposal	Used batteries must not be thrown away with household waste, they should instead be disposed of in accordance with applicable national regulations.
IQ technology	no

## Insulation characteristics

Protection class	III
------------------	-----

## Dimensions

Width	52 mm
Height	130 mm
Depth	110 mm

## Installation dimensions

Installation distance right/left	0 mm / 0 mm
Installation distance top/bottom	50 mm / 50 mm

## Material specifications

Housing material	Metal
Type of housing	Steel sheet, zinc-plated

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 40 °C
Ambient temperature (storage/transport)	0 °C ... 40 °C
Max. permissible relative humidity (operation)	95 %

## Ex data

Suited for EX-applications	no
----------------------------	----

# MINI-BAT/24DC/1.3AH - Battery module



2866417

<https://www.phoenixcontact.com/gb/products/2866417>

## Drawings

### Block diagram



# MINI-BAT/24DC/1.3AH - Battery module



2866417

<https://www.phoenixcontact.com/gb/products/2866417>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2866417>



**EAC**

Approval ID: RU S-DE.BL08.W.00764



**EAC**

Approval ID: RU\*DE\*01.B.78948/21

# MINI-BAT/24DC/1.3AH - Battery module



2866417

<https://www.phoenixcontact.com/gb/products/2866417>

## Classifications

### ECLASS

ECLASS-13.0	27050403
ECLASS-15.0	27050403

### ETIM

ETIM 10.0	EC003893
-----------	----------

### UNSPSC

UNSPSC 21.0	26111700
-------------	----------

# MINI-BAT/24DC/1.3AH - Battery module



2866417

<https://www.phoenixcontact.com/gb/products/2866417>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-3
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

### EF3.1 Climate Change

CO2e kg	13.23 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)