

FL SWITCH 4808E-16FX LC-4GC - Industrial Ethernet Switch



2891073

<https://www.phoenixcontact.com/gb/products/2891073>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Rack-mount managed Ethernet switch meets IEC 61850-3 and IEEE 1613. Provides eight RJ45 ports at 10/100 Mbps, 16 LC MM fiber ports at 100 Mbps and four gigabit combo ports (10/100/1000 Mbps RJ45 connection; 1000 Mbps fiber optic connection requires 1000 Mbps SFP module).



Your advantages

- Network structure according to IEC 61850
- IEEE 1613

Commercial data

Item number	2891073
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DNN125
Product key	DNN125
GTIN	4046356764377
Weight per piece (including packing)	4,706 g
Weight per piece (excluding packing)	4,630 g
Customs tariff number	85176200
Country of origin	TW

FL SWITCH 4808E-16FX LC-4GC - Industrial Ethernet Switch



2891073

<https://www.phoenixcontact.com/gb/products/2891073>

Technical data

Dimensions

Width	442 mm
Height	44 mm
Depth	375 mm

Mounting

Mounting type	Rack mount, includes brackets
---------------	-------------------------------

Interfaces

Ethernet (RJ45)

Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	100 m
No. of channels	8 (RJ45 ports)

Fiber optic interface

Connection method	LC
Transmission speed	100 Mbps (Full duplex)
Transmission physics	multi-mode fiberglass
Transmission length	8 km (fiberglass with F-G 62.5/125 0.7 dB/km F1000) 3.3 km (fiberglass with F-G 62.5/125 2.6 dB/km F600) 9.6 km (fiberglass with F-G 50/125 0.7 dB/km F1200) 5.3 km (fiberglass with F-G 50/125 1.6 dB/km F800)
Wavelength	1300/1310 nm
No. of channels	16 (Multi mode)

Ethernet (RJ45/FO combo)

Connection method	SFP/RJ45
Note on the connection method	Auto negotiation and autocrossing (RJ45 interface)
Transmission speed	10/100/1000 Mbps
Transmission physics	Ethernet RJ45 (10/100/1000 Mbps) or SFP (1000 Mbps)
No. of channels	4

Product properties

Product type	Switch
Product family	Managed Switch 4000
Type	Block design
MTTF	8.3 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)

Switch functions

FL SWITCH 4808E-16FX LC-4GC - Industrial Ethernet Switch



2891073

<https://www.phoenixcontact.com/gb/products/2891073>

Basic functions	Store and forward switch, Extended Ring and IEEE redundancy, Multicast control, IGMP snooping, trunking, Port and Tagging VLANs, Port and IEEE 802.1x security, SNMP V3 and Https security, SNTP, web customization, user accounts
Redundancy	ERR (Extended ring redundancy)
Status and diagnostic indicators	LEDs: U _{S1} , U _{S2} (redundant voltage supply), link and activity per port

Security functions

Basic functions	Store and forward switch, Extended Ring and IEEE redundancy, Multicast control, IGMP snooping, trunking, Port and Tagging VLANs, Port and IEEE 802.1x security, SNMP V3 and Https security, SNTP, web customization, user accounts
-----------------	--

Electrical properties

Current consumption	553 mA (115 V AC from FL SWITCH 4800E-P5)
Transmission medium	Copper FO

Supply

Power supply connection	From FL SWITCH 4800E-P...
Inrush current	19 A (48 V DC from FL SWITCH 4800E-P1) 18.7 A (115 V AC from FL SWITCH 4800E-P5)
Current consumption	553 mA (115 V AC from FL SWITCH 4800E-P5)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Air pressure (operation)	57 kPa ... 108 kPa (up to 4850 m above mean sea level)
Air pressure (storage/transport)	57 kPa ... 108 kPa (up to 4850 m above mean sea level)

EMC data

Noise immunity	IEC 61850-3, IEEE 1613, EN 61000-6-2: 2005
----------------	--

Noise emission

Standards/regulations	EN 61000-6-4
-----------------------	--------------

System properties

Functionality

Basic functions	Store and forward switch, Extended Ring and IEEE redundancy, Multicast control, IGMP snooping, trunking, Port and Tagging VLANs, Port and IEEE 802.1x security, SNMP V3 and Https security, SNTP, web customization, user accounts
-----------------	--

FL SWITCH 4808E-16FX LC-4GC - Industrial Ethernet Switch



2891073

<https://www.phoenixcontact.com/gb/products/2891073>

Signaling

Status display

LEDs: U_{S1}, U_{S2} (redundant voltage supply), link and activity per port

FL SWITCH 4808E-16FX LC-4GC - Industrial Ethernet Switch



2891073

<https://www.phoenixcontact.com/gb/products/2891073>

Classifications

UNSPSC

UNSPSC 21.0	43222612
-------------	----------

FL SWITCH 4808E-16FX LC-4GC - Industrial Ethernet Switch



2891073

<https://www.phoenixcontact.com/gb/products/2891073>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	15(a), 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk