

FL SFP FX - Media module

2891081

<https://www.phoenixcontact.com/gb/products/2891081>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The small form-factor plug-in module provides a fiber optic interface with a data transmission speed of 100 Mbps with a wavelength of 1310 nm (long).

Product description

Developed according to IEC 61850-3 (Ambient conditions) DDI, Digital DiagnosticMonitoring Interface

Your advantages

- Network structure according to IEC 61850
- IEEE 1613
- MSA compliant



Commercial data

Item number	2891081
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DNN612
Product key	DNN612

FL SFP FX - Media module

2891081

<https://www.phoenixcontact.com/gb/products/2891081>



GTIN	4046356800952
Weight per piece (including packing)	29.7 g
Weight per piece (excluding packing)	29.7 g
Customs tariff number	85176200
Country of origin	TW

Technical data

Dimensions

Width	13.7 mm
Height	8.95 mm
Length	56.5 mm

Notes

Note on application	Only for industrial use
Note on application	As things stand now, we are preparing the product so that, as of December 11, 2027, it will comply with the requirements of the EU Cyber Resilience Act (CRA) based on the information currently available regarding the CRA.

Material specifications

Color (Housing)	white aluminium (RAL 9006)
Housing material	Metal

Mounting

Mounting type	Plug-in mounting (SFP port)
---------------	-----------------------------

Interfaces

Ethernet FO

Connection method	1 LC socket at the SFP module, 100 Mbps
Transmission speed	100 Mbps
Transmit capacity, minimum	-19 dBm
Transmit capacity, maximum	-12 dBm
Minimum receiver sensitivity	-30 dBm
Maximum receiver sensitivity	-3 dBm
Transmission physics	multi-mode fiberglass
Wavelength	1310 nm
Signal LEDs	depending on the Factoryline device
No. of channels	1 (LC multi-mode)

Product properties

Product type	SFP module
Type	Factoryline devices with SFP slot
MTTF	372 Years (Telcordia standard, 25°C temperature, 21% operating cycle (5 days a week, 8 hours a day))
Format	SFP (Small Form-factor Pluggable)

Signaling

Status display	via a Factoryline device
----------------	--------------------------

Electrical properties

FL SFP FX - Media module



2891081

<https://www.phoenixcontact.com/gb/products/2891081>

Maximum power dissipation for nominal condition	0.66 W (when installed)
Transmission medium	Multi-mode fiberglass

Supply

Supply voltage	3.3 V (via Factoryline switch)
Power supply connection	via SFP slot

Connection data

Connection method	To insert in SFP slot
-------------------	-----------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C (non-condensing)
Ambient temperature (storage/transport)	-40 °C ... 85 °C (non-condensing)
Permissible humidity (operation)	30 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	30 % ... 95 % (non-condensing)
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz
Air pressure (operation)	86 kPa ... 108 kPa (1500 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (3500 m above sea level)

Standards and regulations

Standard designation	Ambient conditions
Standards/specifications	IEC 61850-3

FL SFP FX - Media module



2891081

<https://www.phoenixcontact.com/gb/products/2891081>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2891081>



DNV GL

Approval ID: TAA00000YV



LR

Approval ID: LR22250919TA



NK

Approval ID: TA24215M



BV

Approval ID: 48146_B1 BV

BSH

Approval ID: Nr. 966



RINA

Approval ID: ELE014724XG001

ABS

Approval ID: 21_2066186_1_PDA



cULus Recognized

Approval ID: E140403

ABS

Approval ID: 26-0501235-PDA

FL SFP FX - Media module

2891081

<https://www.phoenixcontact.com/gb/products/2891081>



Classifications

ECLASS

ECLASS-13.0	19179090
ECLASS-15.0	19179090

ETIM

ETIM 10.0	EC002608
-----------	----------

UNSPSC

UNSPSC 21.0	43222600
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead 7439-92-1(CAS: n/a)
SCIP	aef054ae-5c82-4e70-bccd-335bd44f47fe