

# RIF-0-BPT/21 - Relay base



2900958

<https://www.phoenixcontact.com/gb/products/2900958>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay base RIF-0..., for miniature power relay with 1 changeover contact or solid-state relays of the same design, Push-in connection, for mounting on NS 35/7,5

## Commercial data

Item number	2900958
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	DK6521
Product key	DK6521
GTIN	4046356733014
Weight per piece (including packing)	21.432 g
Weight per piece (excluding packing)	20 g
Customs tariff number	85366990
Country of origin	CN

# RIF-0-BPT/21 - Relay base

2900958

<https://www.phoenixcontact.com/gb/products/2900958>



## Technical data

### Product properties

Product type	Relay socket
Product family	RIFLINE complete
Set comprises	2903368 RIF-0-RPT-24DC/21AU
	2903369 RIF-0-RPT-12DC/21AU
	2903370 RIF-0-RPT-24DC/21
	2903371 RIF-0-RPT-12DC/21
	1550107 RIF-0-RPT-24DC/21/MS

### Electrical properties

Nominal voltage $U_N$	250 V AC/DC (Contact side)
Nominal current $I_N$	max. 8 A (Depends on application/assembly)
Protective circuit	Freewheeling diode

### Input data

Input voltage range	12 V DC ... 24 V DC
---------------------	---------------------

### Connection data

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (Ferrule with plastic sleeve)
Conductor cross-section AWG	24 ... 16

### Dimensions

#### Item dimensions

Width	6.2 mm
Height	93 mm
Depth	78 mm

### Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94 (Housing)	V2 (Housing)

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (Depends on application/assembly)
Ambient temperature (storage/transport)	-40 °C ... 85 °C

### Approvals

# RIF-0-BPT/21 - Relay base

2900958

<https://www.phoenixcontact.com/gb/products/2900958>



## Corrosive gas test


Identification	ISA-S71.04. G3 Harsh Group
	EN 60068-2-60

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

Drawings

Circuit diagram



# RIF-0-BPT/21 - Relay base



2900958

<https://www.phoenixcontact.com/gb/products/2900958>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2900958>



**CSA**

Approval ID: 76787



**UL Recognized**

Approval ID: FILE E 113228



**EAC**

Approval ID: RU D-DE.B\*00573/18

**DNV**

Approval ID: TAA000018V

# RIF-0-BPT/21 - Relay base

2900958

<https://www.phoenixcontact.com/gb/products/2900958>



## Classifications

### ECLASS

ECLASS-13.0	27371603
ECLASS-15.0	27371603

### ETIM

ETIM 10.0	EC001456
-----------	----------

### UNSPSC

UNSPSC 21.0	39122300
-------------	----------

# RIF-0-BPT/21 - Relay base



2900958

<https://www.phoenixcontact.com/gb/products/2900958>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	24c06b55-f1a6-4d06-9929-5f63500f22be

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)