

# PLC-OPT- 24DC/TTL - Solid-state relay module



2900363

<https://www.phoenixcontact.com/gb/products/2900363>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PLC-INTERFACE for TTL signal, consisting of PLC-O.../TTL basic terminal block with push-in connection and integrated solid-state relay, for mounting on DIN rail NS 35/7,5, 1 N/O contact, input: 24 V DC, output: TTL (5 V DC)

## Your advantages

- 6.2 mm narrow design width
- Resistant to vibrations and shocks
- Screw and spring-cage connection
- Switching power TTL (5 V), fan out = 1
- Status indicator
- Integrated protection circuit
- Bridging options

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 2900363                        |
| Packing unit                         | 10 pc                          |
| Minimum order quantity               | 10 pc                          |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | DK62A3                         |
| Product key                          | DK62A3                         |
| GTIN                                 | 4046356508995                  |
| Weight per piece (including packing) | 28.96 g                        |
| Weight per piece (excluding packing) | 30.15 g                        |
| Customs tariff number                | 85364190                       |
| Country of origin                    | DE                             |

# PLC-OPT- 24DC/TTL - Solid-state relay module



2900363

<https://www.phoenixcontact.com/gb/products/2900363>

## Technical data

### Product properties

|                |                          |
|----------------|--------------------------|
| Product type   | Solid-state relay module |
| Product family | PLC-INTERFACE            |
| Application    | TTL signal at output     |
| Operating mode | 100% operating factor    |

Insulation characteristics: Air clearances and creepage distances between the power circuits

|                      |                  |
|----------------------|------------------|
| Insulation           | Basic insulation |
| Overvoltage category | III              |
| Pollution degree     | 2                |

Data management status

|                              |            |
|------------------------------|------------|
| Date of last data management | 01.04.2026 |
|------------------------------|------------|

### Electrical properties

|   |   |
|---|---|
| Maximum power dissipation for nominal condition | 0.08 W  |
| Test voltage (Input/output)                     | 2.5 kV <sub>rms</sub> (50 Hz, 1 min., input/output) |

Air clearances and creepage distances between the power circuits

|                          |          |
|--------------------------|----------|
| Rated insulation voltage | 250 V DC |
| Rated surge voltage      | 4 kV     |

### Input data

|  |   |
|--|---|
| Rated actuating voltage $U_C$                        | 24 V DC   |
| Voltage range with reference to $U_C$                | 0.8 ... 1.2   |
| Rated actuating current $I_C$                        | 3.4 mA  |
| Switching threshold "0" signal in reference to $U_N$ | < 0.4   |
| Switching threshold "1" signal in reference to $U_N$ | > 0.8   |
| Typical input current at $U_N$                       | 3.4 mA  |
| Typical response time                                | 35 $\mu$ s  |
| Typical turn-off time                                | 35 $\mu$ s  |
| Operating voltage display                            | Yellow LED  |
| Protective circuit                                   | Reverse polarity protection; Parallel polarity protection diode<br>Surge protection |
| Surge voltage protection                             | > 33 V  |
| Transmission frequency                               | 1 kHz   |

### Output data

|  |                |
|--|----------------|
| Designation                                | Output data    |
| Contact switching type                     | 1 N/O contact  |
| Design of digital output                   | electronic     |
| Contact connection type                    | Signal contact |
| Rated control circuit supply voltage $U_S$ | 5 V DC         |

# PLC-OPT- 24DC/TTL - Solid-state relay module



2900363

<https://www.phoenixcontact.com/gb/products/2900363>

|  |   |
|--|---|
| Voltage range with reference to $U_S$            | 0.9 ... 1.2   |
| Output voltage range                             | 4.5 V DC ... 6 V DC   |
| Limiting continuous current                      | 50 mA (a TTL load (Fan out = 1))  |
| Fan out  | 1   |
| Surge voltage protection                         | > 8 V   |
| Voltage drop at max. limiting continuous current | < 80 mV   |
| Output circuit                                   | 3-conductor, ground-referenced  |
| Protective circuit                               | Reverse polarity protection; Parallel polarity protection diode<br>Surge protection |

## Connection data

|                                  |   |
|----------------------------------|---|
| Connection method                | Push-in connection  |
| Stripping length                 | 10 mm   |
| Conductor cross-section rigid    | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>  |
| Conductor cross-section flexible | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup><br>0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (Single ferrule)<br>2x 0.5 mm <sup>2</sup> ... 1 mm <sup>2</sup> (TWIN ferrule) |
| Conductor cross-section AWG      | 26 ... 14   |

## Dimensions

### Item dimensions

|        |        |
|--------|--------|
| Width  | 6.2 mm |
| Height | 80 mm  |
| Depth  | 94 mm  |

## Material specifications

|  |                 |
|--|-----------------|
| Color  | gray (RAL 7042) |
| Flammability rating according to UL 94 (Housing) | V0 (Housing)    |

## Environmental and real-life conditions

### Ambient conditions

|   |                  |
|---|------------------|
| Degree of protection                    | IP20             |
| Ambient temperature (operation)         | -25 °C ... 60 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

## Approvals

### Corrosive gas test

|                |   |
|----------------|---|
| Identification | ISA-S71.04. G3 Harsh Group<br>EN 60068-2-60 |
|----------------|---|

## Standards and regulations

### Air clearances and creepage distances between the power circuits

|                       |               |
|-----------------------|---------------|
| Standards/regulations | IEC 60947-5-1 |
|-----------------------|---------------|

# PLC-OPT- 24DC/TTL - Solid-state relay module



2900363

<https://www.phoenixcontact.com/gb/products/2900363>

## Mounting

|                   |                           |
|-------------------|---------------------------|
| Mounting type     | DIN rail mounting         |
| Assembly note     | in rows with zero spacing |
| Mounting position | any                       |

# PLC-OPT- 24DC/TTL - Solid-state relay module




2900363

<https://www.phoenixcontact.com/gb/products/2900363>

## Drawings

Circuit diagram



# PLC-OPT- 24DC/TTL - Solid-state relay module



2900363

<https://www.phoenixcontact.com/gb/products/2900363>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2900363>



**cULus Listed**

Approval ID: E140324



**cULus Listed**

Approval ID: E140324



**cULus Listed**

Approval ID: E140324

# PLC-OPT- 24DC/TTL - Solid-state relay module



2900363

<https://www.phoenixcontact.com/gb/products/2900363>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27371604 |
| ECLASS-15.0 | 27371604 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001504 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39122300 |
|-------------|----------|

## Environmental product compliance

### EU RoHS

|   |              |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 52675edb-44e4-4d8f-a53b-c86465c0b2ad |

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.821 kg CO2e |
|---------|---------------|