

# VAL-MS-EE-T1/T2-1+1-335 - Lightning/surge arrester type 1/2



2910553

<https://www.phoenixcontact.com/gb/products/2910553>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Universal varistor-based plug-in lightning/surge arrester for 1-phase power supply networks with separate N and PE (3-conductor system: L1, N, PE).

## Commercial data

Item number	2910553
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	CLP121
Product key	CLP121
GTIN	4055626462356
Weight per piece (including packing)	342.5 g
Weight per piece (excluding packing)	342.5 g
Customs tariff number	85363030
Country of origin	DE

# VAL-MS-EE-T1/T2-1+1-335 - Lightning/surge arrester type 1/2

2910553

<https://www.phoenixcontact.com/gb/products/2910553>

## Technical data

### Product properties

Product type	Arrester combination
IEC test classification	I / II
	T1 / T2
EN type	T1 / T2
IEC power supply system	TT
	TN-S
Type	DIN rail module, two-section, divisible
Number of positions	2
Surge protection fault message	optical
Number of ports	One

### Insulation characteristics

Overvoltage category	III
Pollution degree	2


### Electrical properties

Nominal frequency $f_N$	50 Hz (60 Hz)
-------------------------	---------------

### Connection data

Connection method	Screw connection
Screw thread	M5
Tightening torque	3 Nm (1.5 mm <sup>2</sup> ... 16 mm <sup>2</sup> )
	4.5 Nm (25 mm <sup>2</sup> ... 35 mm <sup>2</sup> )
Stripping length	16 mm
Conductor cross-section flexible	1.5 mm <sup>2</sup> ... 25 mm <sup>2</sup>
Conductor cross-section rigid	1.5 mm <sup>2</sup> ... 35 mm <sup>2</sup>
Conductor cross-section AWG	15 ... 2
Connection method	Biconnect terminal blocks
Conductor cross-section flexible	1.5 mm <sup>2</sup> ... 16 mm <sup>2</sup>

### Dimensions

Dimensional drawing	
Width	35.6 mm
Height	89.8 mm
Depth	77.5 mm (incl. DIN rail 7.5 mm)
Horizontal pitch	2 Div.

# VAL-MS-EE-T1/T2-1+1-335 - Lightning/surge arrester type 1/2



2910553

<https://www.phoenixcontact.com/gb/products/2910553>

## Material specifications

Color	traffic gray B (RAL 7043)
Flammability rating according to UL 94	V-0
CTI value of material	600
Insulating material	PA 6.6/PBT
Material group	I
Housing material	PA 6.6
	PBT

## Mechanical properties

### Mechanical data

Open side panel	No
-----------------	----

## Protective circuit

Mode of protection	L-N
	L-PE
	N-PE
Direction of action	1L-N & N-PE
Nominal voltage $U_N$	240 V AC (TN-S)
	240 V AC (TT)
Nominal frequency $f_N$	50 Hz (60 Hz)
Maximum continuous operating voltage $U_C$ (L-N)	335 V AC
Maximum continuous operating voltage $U_C$ (L-PE)	335 V AC
Maximum continuous operating voltage $U_C$ (N-PE)	264 V AC
Rated load current $I_L$	80 A
Protective conductor current $I_{PE}$	$\leq 5 \mu A$
Standby power consumption $P_C$	$\leq 270 \text{ mVA}$
Nominal discharge current $I_n$ (8/20) $\mu s$ (L-N)	12.5 kA
Nominal discharge current $I_n$ (8/20) $\mu s$ (L-PE)	12.5 kA
Nominal discharge current $I_n$ (8/20) $\mu s$ (N-PE)	50 kA
Maximum discharge current $I_{max}$ (8/20) $\mu s$	50 kA
Impulse discharge current (10/350) $\mu s$ (L-N), charge	6.25 As
Impulse discharge current (10/350) $\mu s$ (L-N), specific energy	39 kJ/ $\Omega$
Impulse discharge current (10/350) $\mu s$ (L-N), peak current value $I_{imp}$	12.5 kA
Impulse discharge current (10/350) $\mu s$ (L-PE), charge	6.25 As
Impulse discharge current (10/350) $\mu s$ (L-PE), specific energy	39 kJ/ $\Omega$
Impulse discharge current (10/350) $\mu s$ (L-PE), peak current value $I_{imp}$	12.5 kA
Impulse discharge current (10/350) $\mu s$ (N-PE), charge	25 As
Impulse discharge current (10/350) $\mu s$ (N-PE), specific energy	625 kJ/ $\Omega$
Impulse discharge current (10/350) $\mu s$ (N-PE), peak current value $I_{imp}$	50 kA
Total discharge current $I_{Total}$ (8/20) $\mu s$	50 kA

# VAL-MS-EE-T1/T2-1+1-335 - Lightning/surge arrester type 1/2



2910553

<https://www.phoenixcontact.com/gb/products/2910553>

Total discharge current $I_{Total}$ (10/350) $\mu$ s	25 kA
Follow current interrupt rating $I_{fi}$ (N-PE)	100 A
Short-circuit current rating $I_{SCCR}$	25 kA
Voltage protection level $U_p$ (L-N)	$\leq 1.2$ kV
	$\leq 1.6$ kV (30 kA - 8/20 $\mu$ s)
Voltage protection level $U_p$ (L-PE)	$\leq 2$ kV
Voltage protection level $U_p$ (N-PE)	$\leq 1.7$ kV
Residual voltage $U_{res}$ (L-N)	$\leq 1.2$ kV (at $I_n$ )
	$\leq 1.1$ kV (at 10 kA)
	$\leq 1$ kV (at 5 kA)
	$\leq 0.9$ kV (at 3 kA)
Residual voltage $U_{res}$ (L-PE)	$\leq 2$ kV (at $I_n$ )
	$\leq 1.5$ kV (at 10 kA)
	$\leq 1.2$ kV (at 5 kA)
	$\leq 1.1$ kV (at 3 kA)
Residual voltage $U_{res}$ (N-PE)	$\leq 0.6$ kV (at $I_n$ )
	$\leq 0.5$ kV (at 10 kA)
	$\leq 0.5$ kV (at 5 kA)
	$\leq 0.4$ kV (at 3 kA)
TOV behavior at $U_T$ (L-N)	415 V AC (5 s / withstand mode)
	457 V AC (120 min / safe failure mode)
TOV behavior at $U_T$ (N-PE)	1200 V AC (200 ms / withstand mode)
Response time $t_A$ (L-N)	$\leq 25$ ns
Response time $t_A$ (L-PE)	$\leq 100$ ns
Response time $t_A$ (N-PE)	$\leq 100$ ns
Max. backup fuse with V-type through wiring	80 A (gG - 16 mm <sup>2</sup> )
Max. backup fuse with branch wiring	160 A (gG)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20 (only when all terminal points are used)
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	$\leq 2000$ m (amsl)
Permissible humidity (operation)	5 % ... 95 %
Shock (operation)	30g (Half-sine / 11 ms / 3x $\pm$ X, $\pm$ Y, $\pm$ Z)
Vibration (operation)	7.5g (10 ... 500 Hz / 2.5 h / X, Y, Z)

## Standards and regulations

Standards/specifications	IEC 61643-11
Note	2011
Standards/specifications	EN 61643-11
Note	2012

# VAL-MS-EE-T1/T2-1+1-335 - Lightning/surge arrester type 1/2



2910553

<https://www.phoenixcontact.com/gb/products/2910553>

## Mounting

Mounting type

DIN rail: 35 mm


# VAL-MS-EE-T1/T2-1+1-335 - Lightning/surge arrester type 1/2

2910553


<https://www.phoenixcontact.com/gb/products/2910553>

## Drawings

Dimensional drawing



Circuit diagram



# VAL-MS-EE-T1/T2-1+1-335 - Lightning/surge arrester type 1/2



2910553

<https://www.phoenixcontact.com/gb/products/2910553>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2910553>

### UAE-RoHS

Approval ID: 23-10-88705

# VAL-MS-EE-T1/T2-1+1-335 - Lightning/surge arrester type 1/2



2910553

<https://www.phoenixcontact.com/gb/products/2910553>

## Classifications

### ECLASS

ECLASS-13.0	27171201
ECLASS-15.0	27171201

### ETIM

ETIM 10.0	EC000381
-----------	----------

### UNSPSC

UNSPSC 21.0	39121600
-------------	----------

# VAL-MS-EE-T1/T2-1+1-335 - Lightning/surge arrester type 1/2



2910553

<https://www.phoenixcontact.com/gb/products/2910553>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	7.326 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)