# REL-MR-120AC/21-21/MS - Single relay

2987969

https://www.phoenixcontact.com/gb/products/2987969

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.




Plug-in miniature relay, with power contact, 2 changeover contacts, test button, mechanical switching position indicator, status LED, coil voltage 120 V AC

## Your advantages

- With detectable manual operation
- Mechanical switch position indicator
- DC types with integrated freewheeling diode
- Switching current of up to 16 A
- Integrated status LED

## Commercial data

| | |
|---|---|
| Item number | 2987969 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | DK6937 |
| Product key | DK6937 |
| GTIN | 4046356480970 |
| Weight per piece (including packing) | 18.43 g |
| Weight per piece (excluding packing) | 17.48 g |
| Customs tariff number | 85364900 |
| Country of origin | CN |

# Technical data

## Product properties

| | |
|---|---|
| Product type | Single relay |
| Set comprises | 2909775 RIF-1-RPT-LV-120AC/2X21MS |
| Mechanical service life | 5x $10^6$ cycles |

Data management status

| | |
|---|---|
| Date of last data management | 01.04.2026 |

## Electrical properties

| | |
|---|---|
| Service life electrical | see diagram |
| Maximum power dissipation for nominal condition | 0.84 W |
| Test voltage (Winding/contact) | 5 kV AC (50 Hz, 1 min.) |
| Test voltage (Contact/contact) | 2.5 kV AC (50 Hz, 1 min.) |
| Test voltage (open contact) | 1 kV (50 Hz, 1 min.) |

## Input data

Coil side

| | |
|---|---|
| Nominal input voltage $U_N$ | 120 V AC |
| Input voltage range | 93.6 V AC ... 174 V AC |
| Mains frequency | 50/60 Hz |
| Drive and function | monostable |
| Drive (polarity) | non-polarized |
| Typical input current at $U_N$ | 7 mA |
| Typical response time | 3 ms ... 12 ms (depending on phase relation) |
| Typical release time range | 2 ms ... 8 ms (depending on phase relation) |

## Output data

Switching

| | |
|---|---|
| Contact switching type | 2 changeover contacts |
| Type of switch contact | Single contact |
| Contact material | AgNi |
| Maximum switching voltage | 250 V AC/DC |
| Minimum switching voltage | 12 V (at 10 mA) |
| Limiting continuous current | 8 A |
| Maximum inrush current | 16 A (20 ms) |
| Min. switching current | 10 mA (at 12 V) |
| Interrupting rating (ohmic load) max. | 2000 VA (for 250 V AC) |
| Switching capacity | 1 A (at 24 V, DC13) |
| | 1.5 A (at 24 V, AC15) |
| | 1.5 A (at 120 V, AC15) |
| | 1.5 A (at 240 V, AC15) |

| | |
|---|---|
| Motor load according to UL 508 | 1/4 HP, 120 V AC (N/O contact) |
| | 1/2 HP, 240 V AC (N/O contact) |
| | 1/4 HP, 120 V AC (N/C contact) |
| | 1/3 HP, 240 V AC (N/C contact) |

## Connection data

| | |
|---|---|
| Connection method | Plug / solder connection |

## Dimensions

Item dimensions

| | |
|---|---|
| Width | 12.7 mm |
| Height | 29 mm |
| Depth | 25 mm |

## Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 70 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

## Approvals

Corrosive gas test


| | |
|---|---|
| Identification | ISA-S71.04. G3 Harsh Group |
| | EN 60068-2-60 |

## Standards and regulations


| | |
|---|---|
| Standards/regulations | EN 61810-1 |
| | VDE 0435-201 |
| | EN 50178 |

## Drawings

Dimensional drawing





Diagram




1 DC coils, 0 A contact current
2 DC coils, 8 A contact current
3 AC coils, 0 A contact current
4 AC coils, 8 A contact current

Operating voltage range

Diagram





1 AC, ohmic load

2 DC, ohmic load, contacts in series

3 DC, ohmic load


Interrupting rating

Diagram





Electrical service life

Diagram




Service life reduction factor with various cos phi

Diagram




Permissible humidity for operation and storage.
The maximum permissible ambient temperature as specified in the data sheet must be observed.

Area A: Ice buildup at ambient temperatures ≤ 0°C must be prevented
Area B: Condensation at ambient temperatures > 0°C must be prevented

On 30 full days that are naturally distributed across an entire year, a humidity level of 95% is permissible at an ambient temperature ≤ 25°C.

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/gb/products/2987969

**cUL Recognized**
Approval ID: FILE E 195083

**UL Recognized**
Approval ID: FILE E 195083

**VDE Zeichengenehmigung**
Approval ID: 40027210

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27371601 |
| ECLASS-15.0 | 27371601 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC001437 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39122300 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(c)-I |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 1.018 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk