

PT 4-PE/L/HESILED 24 (5X20) - Fuse modular terminal block



3002603

<https://www.phoenixcontact.com/gb/products/3002603>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse modular terminal block, fuse type: Glass / ceramics / ..., fuse type: G / 5 x 20, nom. voltage: 24 V, nominal current: 6.3 A, connection method: Push-in connection, Rated cross section: 4 mm², cross section: 0.2 mm²- 6 mm², connection method: Push-in connection, cross section: 0.2 mm²- 6 mm², mounting type: NS 35/7,5, NS 35/15, color: black

Your advantages

- Convenient testing of fuses with test pick-offs on both sides
- The compact design and front connection enable wiring in a confined space
- The Push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system and by easy and tool-free wiring of conductors with ferrules or solid conductors
- Quick identification of faulty fuses, thanks to LED status indicator
- The easily accessible fuse inserts are easy to use or replace
- In addition to the testing option in the double function shaft, all terminal blocks provide an additional test pick-off

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3002603 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BE2236 |
| Product key | BE2236 |
| GTIN | 4055626369686 |
| Weight per piece (including packing) | 35 g |
| Weight per piece (excluding packing) | 35 g |
| Customs tariff number | 85369095 |
| Country of origin | IN |

PT 4-PE/L/HESILED 24 (5X20) - Fuse modular terminal block



3002603

<https://www.phoenixcontact.com/gb/products/3002603>

Technical data

Notes

| | |
|--------------------|---|
| Order information: | Fuse-link not supplied as standard |
| General | The current is determined by the fuse used, the voltage by the selected LED. If the fuse is faulty, the downstream circuit will not be disconnected. |
| General | |
| Note | The current is determined by the fuse used, the voltage by the fuse or selected light indicator. |

Product properties

| | |
|-----------------------|---------------------|
| Product type | Fuse terminal block |
| Number of connections | 5 |
| Number of rows | 3 |
| Potentials | 3 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---|--|
| Fuse type | Glass / ceramics / ... |
| Rated surge voltage | 6 kV |
| Maximum power dissipation for nominal condition | 1.02 W |
| Fuse | G / 5 x 20 |
| LED voltage range | 12 V AC/DC ... 30 V AC/DC |
| LED current range | 0.31 mA ... 0.95 mA |
| Maximum power dissipation | max. 1.6 W (with single arrangement of the fuse terminal block in the event of overload) max. 1.6 W (With interconnected arrangement of several fuse terminal blocks in the event of overload) max. 4 W (with single arrangement of the fuse terminal block in the event of a short-circuit) max. 2.5 W (With interconnected arrangement of several fuse terminal blocks in the event of a short-circuit) |

Input data

| | |
|-------------------|---------------------------|
| LED voltage range | 12 V AC/DC ... 30 V AC/DC |
|-------------------|---------------------------|

Connection data

| | |
|---------------------------------|-------------------|
| Grounding foot | Yes |
| Number of connections per level | 2 |
| Nominal cross section | 4 mm ² |

PT 4-PE/L/HESILED 24 (5X20) - Fuse modular terminal block



3002603

<https://www.phoenixcontact.com/gb/products/3002603>

Level 1+2

| | |
|---|---|
| Connection method | Push-in connection |
| Stripping length | 10 mm ... 12 mm |
| Internal cylindrical gage | A4 |
| Connection in acc. with standard | IEC 60947-7-1/IEC 60947-7-2 |
| Conductor cross-section rigid | 0.2 mm ² ... 6 mm ² |
| Cross section AWG | 24 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible | 0.2 mm ² ... 6 mm ² |
| Conductor cross-section, flexible [AWG] | 24 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible ultrasound-compressed | 0.34 mm ² ... 6 mm ² |
| Conductor cross-section, flexible [AWG] ultrasound-compressed | 22 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.25 mm ² ... 4 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.25 mm ² ... 4 mm ² |
| Nominal cross section | 4 mm ² |
| Nominal current | 6.3 A |
| Maximum load current | 6.3 A (with 6 mm ² conductor cross-section, rigid) |
| Nominal voltage | 24 V |

Level 3

| | |
|---|--|
| Connection method | Push-in connection |
| Stripping length | 10 mm ... 12 mm |
| Connection in acc. with standard | IEC 60947-7-3 |
| Conductor cross-section rigid | 0.2 mm ² ... 6 mm ² |
| Cross section AWG | 24 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section, flexible [AWG] | 24 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.25 mm ² ... 4 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.25 mm ² ... 4 mm ² |

Level 1+2 Connection cross sections directly pluggable

| | |
|---|---|
| Conductor cross-section rigid | 0.5 mm ² ... 6 mm ² |
| Conductor cross-section, rigid [AWG] | 20 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.5 mm ² ... 4 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.5 mm ² ... 4 mm ² |

Level 3 Connection cross sections directly pluggable

| | |
|---|---|
| Conductor cross-section rigid | 0.5 mm ² ... 6 mm ² |
| Conductor cross-section, rigid [AWG] | 20 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.5 mm ² ... 4 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.5 mm ² ... 4 mm ² |

Ex data

Rated data (ATEX/IECEx)

| | |
|----------------|-----------------------|
| Identification | Ⓔ II 3 G Ex ec IIC Gc |
|----------------|-----------------------|

PT 4-PE/L/HESILED 24 (5X20) - Fuse modular terminal block



3002603

<https://www.phoenixcontact.com/gb/products/3002603>

| | |
|--|-------------------------------------|
| Operating temperature range | -60 °C ... 130 °C |
| Ex-certified accessories | 3002619 D-PT 4-PE/L/HESI |
| | 1205066 SZS 1,0X4,0 VDE |
| | 3022276 CLIPFIX 35-5 |
| | 3022218 CLIPFIX 35 |
| List of bridges | Plug-in bridge / FBS 2-6 / 3030336 |
| | Plug-in bridge / FBS 3-6 / 3030242 |
| | Plug-in bridge / FBS 4-6 / 3030255 |
| | Plug-in bridge / FBS 5-6 / 3030349 |
| | Plug-in bridge / FBS 10-6 / 3030271 |
| Plug-in bridge / FBS 20-6 / 3030365 | |
| Bridge data | 19 A / 4 mm ² |
| for bridging with bridge | 275 V |
| - At bridging between non-adjacent terminal blocks | 275 V |
| - At cut-to-length bridging with cover | 275 V |
| Rated insulation voltage | 250 V |
| output | (Permanent) |

Ex level General

| | |
|---------------|-------|
| Rated voltage | 275 V |
|---------------|-------|

Ex connection data General

| | |
|------------------------------|---|
| Nominal cross section | 4 mm ² |
| Rated cross section AWG | 12 |
| Connection capacity rigid | 0.2 mm ² ... 6 mm ² |
| Connection capacity AWG | 24 ... 10 |
| Connection capacity flexible | 0.2 mm ² ... 4 mm ² |
| Connection capacity AWG | 24 ... 12 |
| output | (Permanent) |

Ex level Level 2

| | |
|----------------------|--------------------------------|
| Rated current | 29 A (4 mm ²) |
| Maximum load current | 32 A (6 mm ²) |
| Contact resistance | 0.9 mΩ |
| Temperature increase | 40 K (29 A/4 mm ²) |
| output | (Permanent) |

Ex level Level 3

| | |
|----------------------|----------------------------|
| Rated current | 6.3 A (4 mm ²) |
| Maximum load current | 6.3 A (6 mm ²) |
| Contact resistance | 5 mΩ |

Dimensions

| | |
|--------|----------|
| Width | 6.2 mm |
| Height | 119.5 mm |
| Depth | 82.6 mm |

PT 4-PE/L/HESILED 24 (5X20) - Fuse modular terminal block



3002603

<https://www.phoenixcontact.com/gb/products/3002603>

| | |
|--------------------|---------|
| Depth on NS 35/7,5 | 84.1 mm |
| Depth on NS 35/15 | 91.6 mm |

Material specifications

| | |
|--|------------------|
| Color | black (RAL 9005) |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | I |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Mechanical properties

Mechanical data

| | |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

Environmental and real-life conditions

Oscillation/broadband noise

| | |
|------------------------|--|
| Specification | DIN EN 50155 (VDE 0115-200):2008-03 |
| Spectrum | Long life test category 1, class B, body mounted |
| Frequency | $f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$ |
| ASD level | $0.964 \text{ (m/s}^2\text{)}^2\text{/Hz}$ |
| Acceleration | 0.58g |
| Test duration per axis | 5 h |
| Test directions | X-, Y- and Z-axis |
| Result | Test passed |

Shocks

| | |
|--------------------------------|-------------------------------------|
| Specification | DIN EN 50155 (VDE 0115-200):2008-03 |
| Pulse shape | Half-sine |
| Acceleration | 5g |
| Shock duration | 30 ms |
| Number of shocks per direction | 3 |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |
| Result | Test passed |

Ambient conditions

| | |
|---------------------------------|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; |
|---------------------------------|--|

PT 4-PE/L/HESILED 24 (5X20) - Fuse modular terminal block



3002603

<https://www.phoenixcontact.com/gb/products/3002603>

| | |
|--|---|
| | for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Standards and regulations

| | |
|----------------------------------|-----------------------------|
| Connection in acc. with standard | IEC 60947-7-1/IEC 60947-7-2 |
| | IEC 60947-7-3 |

Mounting

| | |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
| | NS 35/15 |

PT 4-PE/L/HESILED 24 (5X20) - Fuse modular terminal block

3002603

<https://www.phoenixcontact.com/gb/products/3002603>

Drawings

Application drawing



Fuse terminal blocks in interconnected arrangement,
block consisting of 5 fuse terminal blocks

PT 4-PE/L/HESILED 24 (5X20) - Fuse modular terminal block

3002603

<https://www.phoenixcontact.com/gb/products/3002603>

Application drawing



Fuse terminal block in single arrangement,
block consisting of one fuse terminal block and 4 feed-through terminal blocks

PT 4-PE/L/HESILED 24 (5X20) - Fuse modular terminal block

3002603

<https://www.phoenixcontact.com/gb/products/3002603>

Circuit diagram



PT 4-PE/L/HESILED 24 (5X20) - Fuse modular terminal block





3002603


<https://www.phoenixcontact.com/gb/products/3002603>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3002603>

 **CSA**
Approval ID: 158887

 **EAC**
Approval ID: RU C-DE.BL08.B.00644


 **cULus Recognized**
Approval ID: E60425

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|---------------|-----------------------|-----------------------|-------------------|----------------------|
| B | | | | |
| upper level | 300 V | 6.3 A | 24 - 10 | - |
| lower level | 300 V | 20 A | 24 - 10 | - |
| PE connection | 300 V | - | 24 - 10 | - |
| C | | | | |
| upper level | 300 V | 6.3 A | 24 - 10 | - |
| lower level | 300 V | 20 A | 24 - 10 | - |
| PE connection | 300 V | - | 24 - 10 | - |
| D | | | | |
| | 600 V | 5 A | 24 - 10 | - |

 **CSA**
Approval ID: 13631

 **cUL Recognized**
Approval ID: E192998

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|------------------------------|-----------------------|-----------------------|-------------------|----------------------|
| keine | | | | |
| Feed-through | 275 V | 20 A | 24 - 10 | 24 - 10 |
| depending on the LED display | 275 V | 6.3 A | 24 - 10 | 24 - 10 |

 **IECEx**
Approval ID: IECExKIWA17.0025U

 **UL Recognized**
Approval ID: E192998

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|--|-----------------------|-----------------------|-------------------|----------------------|
|--|-----------------------|-----------------------|-------------------|----------------------|

PT 4-PE/L/HESILED 24 (5X20) - Fuse modular terminal block



3002603

<https://www.phoenixcontact.com/gb/products/3002603>

| | | | | |
|------------------------------|-------|-------|---------|---|
| keine | | | | |
| Feed-through | 275 V | 20 A | 24 - 10 | - |
| depending on the LED display | 275 V | 6.3 A | 24 - 10 | - |



CCC

Approval ID: 2020322313000626



ATEX

Approval ID: KIWA17ATEX0045U



UKCA-EX

Approval ID: CSAE 21UKEX3605U



EAC Ex

Approval ID: KZ 7500525010101950

PT 4-PE/L/HESILED 24 (5X20) - Fuse modular terminal block



3002603

<https://www.phoenixcontact.com/gb/products/3002603>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250113 |
| ECLASS-15.0 | 27250113 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000899 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

PT 4-PE/L/HESILED 24 (5X20) - Fuse modular terminal block



3002603

<https://www.phoenixcontact.com/gb/products/3002603>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk