

# RB ST 10-(2,5/4) - Reducing bridge

3030873

<https://www.phoenixcontact.com/gb/products/3030873>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Reducing bridge, pitch: 10 mm, number of positions: 2, nominal current: 45 A, length: 36 mm, color: red

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3030873       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BE2Z2X        |
| Product key                          | BE2Z2X        |
| GTIN                                 | 4017918821364 |
| Weight per piece (including packing) | 4.75 g        |
| Weight per piece (excluding packing) | 4.521 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | PL            |

# RB ST 10-(2,5/4) - Reducing bridge



3030873

<https://www.phoenixcontact.com/gb/products/3030873>

## Technical data

### Product properties

|                     |                 |
|---------------------|-----------------|
| Product type        | Reducing bridge |
| Number of positions | 2               |
| Pitch               | 10 mm           |

### Electrical properties

|                      |   |
|----------------------|---|
| Maximum load current | 45 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.) |
|----------------------|---|

### Connection data

|                      |   |
|----------------------|---|
| Maximum load current | 45 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.) |
|----------------------|---|

### Dimensions

|        |         |
|--------|---------|
| Width  | 15 mm   |
| Height | 36.3 mm |
| Depth  | 3 mm    |
| Length | 36.3 mm |
| Pitch  | 10 mm   |

### Material specifications

|  |                |
|--|----------------|
| Color                                  | red (RAL 3001) |
| Material                               | Copper         |
| Flammability rating according to UL 94 | V0             |
| Insulating material                    | PA             |

### Environmental and real-life conditions

#### Ambient conditions

|  |   |
|--|---|
| Ambient temperature (operation)          | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)       |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C   |
| Ambient temperature (actuation)          | -5 °C ... 70 °C ( )   |
| Permissible humidity (storage/transport) | 30 % ... 70 %   |

### Mounting

|               |                  |
|---------------|------------------|
| Mounting type | Plug-in mounting |
|---------------|------------------|

# RB ST 10-(2,5/4) - Reducing bridge



3030873

<https://www.phoenixcontact.com/gb/products/3030873>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250303 |
| ECLASS-15.0 | 27250303 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000489 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# RB ST 10-(2,5/4) - Reducing bridge



3030873

<https://www.phoenixcontact.com/gb/products/3030873>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.047 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)