

TB 2,5-L/LB-PV I - Multi-level terminal block



3000901

<https://www.phoenixcontact.com/gb/products/3000901>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Multi-level terminal block, With equipotential bonding between the upper and lower level, with potential distribution, upper level bridgeable, nom. voltage: 500 V, nominal current: 21 A, connection method: Screw connection, 1st and 2nd level, Rated cross section: 2.5 mm², cross section: 0.5 mm² - 4 mm², mounting type: NS 35/7,5, NS 35/15, NS 32, color: dark gray

Commercial data

Item number	3000901
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BEK214
Product key	BEK214
GTIN	4046356857758
Weight per piece (including packing)	12.475 g
Weight per piece (excluding packing)	11 g
Customs tariff number	85369010
Country of origin	CN

TB 2,5-L/LB-PV I - Multi-level terminal block



3000901

<https://www.phoenixcontact.com/gb/products/3000901>

Technical data

Product properties

Product type	Multi-level terminal block
Product family	TB
Number of positions	2
Number of connections	4
Number of rows	2

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	0.77 W

Connection data

Number of connections per level	2
Nominal cross section	2.5 mm ²
Rated cross section AWG	12

1st and 2nd level

Connection method	Screw connection
Screw thread	M2,5
Tightening torque	0.4 ... 0.5 Nm
Stripping length	8 mm
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	0.5 mm ² ... 4 mm ²
Cross section AWG	20 ... 12 (converted acc. to IEC)
Conductor cross-section flexible	0.5 mm ² ... 2.5 mm ²
Conductor cross-section, flexible [AWG]	20 ... 14 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.5 mm ² ... 2.5 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.5 mm ² ... 1.5 mm ²
Cross-section with insertion bridge, rigid	0.5 mm ² ... 2.5 mm ²
Cross-section with insertion bridge, flexible	0.5 mm ² ... 2.5 mm ²
Cross-section with insertion bridge, flexible, with ferrule without plastic sleeve	0.5 mm ² (1.5 mm ²)
Cross-section with insertion bridge, flexible, with ferrule with plastic sleeve	0.5 mm ² ... 1.5 mm ²
2 conductors with same cross section, rigid	0.5 mm ² ... 1.5 mm ²
2 conductors with the same cross-section AWG rigid	20 ... 14 (converted acc. to IEC)
2 conductors with same cross section, flexible	0.5 mm ² ... 1.5 mm ²
2 conductors with the same cross-section AWG flexible	20 ... 14 (converted acc. to IEC)
2 conductors with same cross section, flexible, with ferrule	0.5 mm ² ... 1 mm ²

TB 2,5-L/LB-PV I - Multi-level terminal block



3000901

<https://www.phoenixcontact.com/gb/products/3000901>

without plastic sleeve	
Nominal cross section	2.5 mm ²
Nominal current	21 A (with a 2.5 mm ² conductor cross-section)
Maximum load current	32 A (with 4 mm ² conductor cross-section)
Nominal voltage	500 V

Dimensions

Width	5.2 mm
Height	56 mm
Depth on NS 32	67 mm
Depth on NS 35/7,5	62 mm
Depth on NS 35/15	69.5 mm

Material specifications

Color	traffic gray B (RAL 7043)
Flammability rating according to UL 94	V0
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Electrical tests

Surge voltage test

Test voltage setpoint	7.3 kV
Result	Test passed

Temperature-rise test

Requirement temperature-rise test	Increase in temperature ≤ 45 K
Result	Test passed
Short-time withstand current 2.5 mm ²	0.3 kA
Short-time withstand current 4 mm ²	0.48 kA
Result	Test passed

Power-frequency withstand voltage

Test voltage setpoint	1.89 kV
Result	Test passed

Mechanical tests

TB 2,5-L/LB-PV I - Multi-level terminal block



3000901

<https://www.phoenixcontact.com/gb/products/3000901>

Mechanical strength

Result	Test passed
--------	-------------

Attachment on the carrier

DIN rail/fixing support	NS 32/NS 35
Test force setpoint	1 N
Result	Test passed

Test for conductor damage and slackening

Rotation speed	10 rpm
Revolutions	135
Conductor cross-section/weight	0.5 mm ² / 0.3 kg
	2.5 mm ² / 0.7 kg
	4 mm ² / 0.9 kg
Result	Test passed

Environmental and real-life conditions

Needle-flame test

Time of exposure	30 s
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15
	NS 32

TB 2,5-L/LB-PV I - Multi-level terminal block


3000901

<https://www.phoenixcontact.com/gb/products/3000901>



Drawings

Circuit diagram



TB 2,5-L/LB-PV I - Multi-level terminal block



3000901

<https://www.phoenixcontact.com/gb/products/3000901>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3000901>



EAC

Approval ID: KZ7500651131219505



cULus Recognized

Approval ID: E60425

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	300 V	20 A	20 - 12	-
C				
	300 V	20 A	20 - 12	-
D				
	600 V	5 A	20 - 12	-

TB 2,5-L/LB-PV I - Multi-level terminal block



3000901

<https://www.phoenixcontact.com/gb/products/3000901>

Classifications

ECLASS

ECLASS-13.0	27250102
ECLASS-15.0	27250102

ETIM

ETIM 10.0	EC000897
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

TB 2,5-L/LB-PV I - Multi-level terminal block



3000901

<https://www.phoenixcontact.com/gb/products/3000901>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.189 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk