


UT 6-QUATTRO/2P-F - Screw flange

3060843

<https://www.phoenixcontact.com/gb/products/3060843>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Screw flange, mounting type: NS 35/7,5, NS 35/15, color: gray



Commercial data

Item number	3060843
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE114Z
Product key	BE114Z
GTIN	4046356608176
Weight per piece (including packing)	13 g
Weight per piece (excluding packing)	13 g
Customs tariff number	85369010
Country of origin	CN

UT 6-QUATTRO/2P-F - Screw flange



3060843

<https://www.phoenixcontact.com/gb/products/3060843>

Technical data

Product properties

Product type	Flange
Product family	UT

Connection data

Screw thread	M2,5
Tightening torque	0.4 ... 0.5 Nm
Conductor cross-section flexible ultrasound-compressed	0.34 mm ² ... 10 mm ²
Conductor cross-section, flexible [AWG] ultrasound-compressed	22 ... 8 (converted acc. to IEC)

Dimensions

Width	8.2 mm
Height	86.5 mm
Depth on NS 35/7,5	60 mm
Depth on NS 35/15	67.5 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	125 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	27,5 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Environmental and real-life conditions

Ambient conditions

Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

UT 6-QUATTRO/2P-F - Screw flange

3060843

<https://www.phoenixcontact.com/gb/products/3060843>



Mounting type	NS 35/7,5
	NS 35/15

UT 6-QUATTRO/2P-F - Screw flange



3060843

<https://www.phoenixcontact.com/gb/products/3060843>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3060843>



EAC

Approval ID: KZ7500651131219505

UT 6-QUATTRO/2P-F - Screw flange



3060843

<https://www.phoenixcontact.com/gb/products/3060843>

Classifications

ECLASS

ECLASS-13.0	27250302
ECLASS-15.0	27250302

ETIM

ETIM 10.0	EC001041
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UT 6-QUATTRO/2P-F - Screw flange



3060843

<https://www.phoenixcontact.com/gb/products/3060843>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.069 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk