

# CP-H 2,5-4L-Z-PE - Connector housing



3012324

<https://www.phoenixcontact.com/gb/products/3012324>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector housing, with securing pins, connection method: Crimp connection, depth: 31.7 mm, width: 5.2 mm, height: 31.6 mm, color: gray

## Your advantages

- With PE marking
- Can be labeled at each terminal point
- Four feed-through levels
- Design width of just 5.2 mm

## Commercial data

Item number	3012324
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE2144
Product key	BE2144
GTIN	4046356811279
Weight per piece (including packing)	1.977 g
Weight per piece (excluding packing)	1.966 g
Customs tariff number	85472000
Country of origin	PL

# CP-H 2,5-4L-Z-PE - Connector housing



3012324

<https://www.phoenixcontact.com/gb/products/3012324>

## Technical data

### Product properties

Product type	Plug
--------------	------

### Connection data

Connection method	Crimp connection
-------------------	------------------

### Dimensions

Width	5.2 mm
Height	31.6 mm
Depth	31.7 mm

### Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed


### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C (max. operating temperature see derating curve)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

## Drawings

Diagram



# CP-H 2,5-4L-Z-PE - Connector housing



3012324

<https://www.phoenixcontact.com/gb/products/3012324>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3012324>

 <b>VDE Gutachten mit Fertigungsüberwachung</b> Approval ID: 40042533				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	250 V	10 A	-	0.5 - 2.5

 <b>EAC</b> Approval ID: KZ7500651131219505	
---	--

# CP-H 2,5-4L-Z-PE - Connector housing



3012324

<https://www.phoenixcontact.com/gb/products/3012324>

## Classifications

### ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

### ETIM

ETIM 10.0	EC000437
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# CP-H 2,5-4L-Z-PE - Connector housing



3012324

<https://www.phoenixcontact.com/gb/products/3012324>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.012 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)