

PSBJ-URTK 6 GY - Test plug strip



3026612

<https://www.phoenixcontact.com/gb/products/3026612>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug strip, number of positions: 1, color: gray

Your advantages

- The test socket PSBJ... is used in place of the normal bridge screw and ensures the voltage pick-off on a bridged group of terminals
- The test sockets are tailored to the special applications encountered in the power supply industry

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3026612 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE1Z3X |
| Product key | BE1Z3X |
| GTIN | 4017918359973 |
| Weight per piece (including packing) | 2.5 g |
| Weight per piece (excluding packing) | 2.486 g |
| Customs tariff number | 85366990 |
| Country of origin | PL |

PSBJ-URTK 6 GY - Test plug strip

3026612

<https://www.phoenixcontact.com/gb/products/3026612>

Technical data


Product properties

| | |
|---------------------|-------------|
| Product type | Test socket |
| Number of positions | 1 |

Connection data

| | |
|-------------------|------------------|
| Connection method | Screw connection |
|-------------------|------------------|

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 6 mm |
| Height | 6 mm |
| Depth on NS 35/7,5 | 15 mm |
| Pin diameter | 4.1 mm |

Material specifications

| | |
|--|-----------------|
| Color | gray (RAL 7042) |
| Material | Brass |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Calorimetric heat release NFPA 130 (ASTM E 1354) | 28 MJ/kg |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Environmental and real-life conditions

Ambient conditions


| | |
|--|---|
| Ambient temperature (operation) | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

PSBJ-URTK 6 GY - Test plug strip

3026612

<https://www.phoenixcontact.com/gb/products/3026612>

Drawings



PSBJ-URTK 6 GY - Test plug strip



3026612

<https://www.phoenixcontact.com/gb/products/3026612>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250304 |
| ECLASS-15.0 | 27250304 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002555 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 20122000 |
|-------------|----------|

PSBJ-URTK 6 GY - Test plug strip



3026612

<https://www.phoenixcontact.com/gb/products/3026612>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 0.02 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk