


TB 10-TWIN I - Multi-conductor terminal block



3062812

<https://www.phoenixcontact.com/gb/products/3062812>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Multi-conductor terminal block, nom. voltage: 800 V, nominal current: 57 A, number of connections: 3, number of positions: 1, connection method: Screw connection, Rated cross section: 10 mm², cross section: 1.5 mm² - 16 mm², mounting type: NS 35/7,5, NS 35/15, NS 32, color: dark gray

Commercial data

Item number	3062812
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BEK212
Product key	BEK212
GTIN	4046356634878
Weight per piece (including packing)	25.13 g
Weight per piece (excluding packing)	24 g
Customs tariff number	85369010
Country of origin	CN

TB 10-TWIN I - Multi-conductor terminal block



3062812

<https://www.phoenixcontact.com/gb/products/3062812>

Technical data

Notes

General

Note	The max. load current must not be exceeded by the total current of all connected conductors.
------	--

Product properties

Product type	Multi-conductor terminal block
Product family	TB
Number of positions	1
Number of connections	3
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	1.82 W

Connection data

Number of connections per level	3
Nominal cross section	10 mm ²
Rated cross section AWG	6
Connection method	Screw connection
Screw thread	M4
Tightening torque	1.4 ... 1.5 Nm
Stripping length	11 mm
Internal cylindrical gage	A5 B5
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	1.5 mm ² ... 16 mm ²
Cross section AWG	14 ... 6 (converted acc. to IEC)
Conductor cross-section flexible	1.5 mm ² ... 10 mm ²
Conductor cross-section, flexible [AWG]	14 ... 8 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	1.5 mm ² ... 10 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	1.5 mm ² ... 6 mm ²
2 conductors with same cross section, rigid	1 mm ² ... 6 mm ²
2 conductors with the same cross-section AWG rigid	16 ... 8 (converted acc. to IEC)
2 conductors with same cross section, flexible	1 mm ² ... 6 mm ²
2 conductors with the same cross-section AWG flexible	16 ... 8 (converted acc. to IEC)

TB 10-TWIN I - Multi-conductor terminal block



3062812

<https://www.phoenixcontact.com/gb/products/3062812>

2 conductors with same cross section, flexible, with ferrule without plastic sleeve	1 mm ² ... 4 mm ²
Nominal cross section	10 mm ²
Nominal current	57 A
Maximum load current	57 A (with 16 mm ² conductor cross-section)
Nominal voltage	800 V

Dimensions

Width	10.2 mm
End cover width	1.8 mm
Height	56.5 mm
Depth on NS 32	64 mm
Depth on NS 35/7,5	59 mm
Depth on NS 35/15	66.5 mm

Material specifications

Color	traffic gray B (RAL 7043)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Electrical tests

Surge voltage test

Test voltage setpoint	9.8 kV
Result	Test passed

Temperature-rise test

Requirement temperature-rise test	Increase in temperature ≤ 45 K
Result	Test passed
Short-time withstand current 10 mm ²	1.2 kA
Result	Test passed

Power-frequency withstand voltage

Test voltage setpoint	2 kV
Result	Test passed

TB 10-TWIN I - Multi-conductor terminal block



3062812

<https://www.phoenixcontact.com/gb/products/3062812>

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Mechanical tests

Mechanical strength

Result	Test passed
--------	-------------

Attachment on the carrier

DIN rail/fixing support	NS 32/NS 35
Test force setpoint	5 N
Result	Test passed

Test for conductor damage and slackening

Rotation speed	10 rpm
Revolutions	135
Conductor cross-section/weight	1.5 mm ² / 0.4 kg
	10 mm ² / 2 kg
	16 mm ² / 2.9 kg
Result	Test passed

Environmental and real-life conditions

Needle-flame test

Time of exposure	30 s
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15
	NS 32

TB 10-TWIN I - Multi-conductor terminal block



3062812

<https://www.phoenixcontact.com/gb/products/3062812>

Drawings

Circuit diagram



TB 10-TWIN I - Multi-conductor terminal block



3062812

<https://www.phoenixcontact.com/gb/products/3062812>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3062812>



EAC

Approval ID: KZ7500651131219505



cULus Recognized

Approval ID: E60425

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	300 V	65 A	16 - 6	-
C				
	300 V	65 A	16 - 6	-

TB 10-TWIN I - Multi-conductor terminal block



3062812

<https://www.phoenixcontact.com/gb/products/3062812>

Classifications

ECLASS

ECLASS-13.0	27250101
ECLASS-15.0	27250101

ETIM

ETIM 10.0	EC000897
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

TB 10-TWIN I - Multi-conductor terminal block



3062812

<https://www.phoenixcontact.com/gb/products/3062812>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk