

D-ST 2,5-TWIN OG - End cover



3036754

<https://www.phoenixcontact.com/gb/products/3036754>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

End cover, depth: 29 mm, width: 2.2 mm, height: 60.5 mm, color: orange



Commercial data

Item number	3036754
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE2Z1X
Product key	BE2Z1X
GTIN	4017918615093
Weight per piece (including packing)	2.437 g
Weight per piece (excluding packing)	2.2 g
Customs tariff number	85389099
Country of origin	DE

D-ST 2,5-TWIN OG - End cover



3036754

<https://www.phoenixcontact.com/gb/products/3036754>

Technical data

Product properties

Product type	End cover
--------------	-----------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Material specifications

Color	orange (RAL 2003)
Material	PA
Flammability rating according to UL 94	V0
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Dimensions

Width	2.2 mm
Height	60.5 mm
Depth	29 mm

D-ST 2,5-TWIN OG - End cover



3036754

<https://www.phoenixcontact.com/gb/products/3036754>

Classifications

ECLASS

ECLASS-13.0

27250301

ETIM

ETIM 9.0

EC000886

UNSPSC

UNSPSC 21.0

39121400

D-ST 2,5-TWIN OG - End cover



3036754

<https://www.phoenixcontact.com/gb/products/3036754>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.049 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk