

# TBIO 2,5 I - Sensor/actuator terminal block



3246749

<https://www.phoenixcontact.com/gb/products/3246749>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator terminal block, upper level bridgeable for signal feed-through, lower levels with insertion bridges for potential distribution, nom. voltage: 250 V, Thermal continuous current  $I_{th}$ : 20 A, number of connections: 3, number of positions: 3, connection method: Screw connection, Rated cross section: 2.5 mm<sup>2</sup>, cross section: 0.2 mm<sup>2</sup> - 4 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, color: dark gray

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3246749       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BEK217        |
| Product key                          | BEK217        |
| GTIN                                 | 4046356689489 |
| Weight per piece (including packing) | 10.789 g      |
| Weight per piece (excluding packing) | 10.789 g      |
| Customs tariff number                | 85369010      |
| Country of origin                    | PL            |

# TBIO 2,5 I - Sensor/actuator terminal block



3246749

<https://www.phoenixcontact.com/gb/products/3246749>

## Technical data

### Product properties

|                       |                                |
|-----------------------|--------------------------------|
| Product type          | Sensor/actuator terminal block |
| Number of positions   | 3                              |
| Number of connections | 3                              |
| Number of rows        | 3                              |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
|----------------------|-----|

### Electrical properties

|   |        |
|---|--------|
| Rated surge voltage                             | 4 kV   |
| Maximum power dissipation for nominal condition | 0.77 W |

### Connection data

|   |  |
|---|--|
| Number of connections per level   | 2  |
| Nominal cross section   | 2.5 mm <sup>2</sup>                          |
| Rated cross section AWG   | 12   |
| Connection method   | Screw connection                             |
| Screw thread  | M2,5   |
| Tightening torque   | 0.4 ... 0.5 Nm                               |
| Stripping length  | 8 mm   |
| Internal cylindrical gage   | A1<br>B2                                     |
| Connection in acc. with standard  | IEC 60947-7-1                                |
| Conductor cross-section rigid   | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>    |
| Cross section AWG   | 24 ... 12 (converted acc. to IEC)            |
| Conductor cross-section flexible  | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>  |
| Conductor cross-section, flexible [AWG]   | 24 ... 14 (converted acc. to IEC)            |
| Conductor cross-section flexible (ferrule without plastic sleeve)                   | 0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Flexible conductor cross-section (ferrule with plastic sleeve)                      | 0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Cross-section with insertion bridge, rigid  | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>    |
| Cross-section with insertion bridge, flexible                                       | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>  |
| Cross-section with insertion bridge, flexible, with ferrule without plastic sleeve  | 0.25 mm <sup>2</sup> (2.5 mm <sup>2</sup> )  |
| Cross-section with insertion bridge, flexible, with ferrule with plastic sleeve     | 0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| 2 conductors with same cross section, rigid   | 0.2 mm <sup>2</sup> ... 1 mm <sup>2</sup>    |
| 2 conductors with the same cross-section AWG rigid                                  | 24 ... 16 (converted acc. to IEC)            |
| 2 conductors with same cross section, flexible                                      | 0.2 mm <sup>2</sup> ... 1 mm <sup>2</sup>    |
| 2 conductors with the same cross-section AWG flexible                               | 24 ... 16 (converted acc. to IEC)            |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve | 0.25 mm <sup>2</sup> ... 1 mm <sup>2</sup>   |
| Nominal cross section   | 2.5 mm <sup>2</sup>                          |

# TBIO 2,5 I - Sensor/actuator terminal block



3246749

<https://www.phoenixcontact.com/gb/products/3246749>

|                                     |   |
|-------------------------------------|---|
| Thermal continuous current $I_{th}$ | 20 A (with a 2.5 mm <sup>2</sup> conductor cross-section) |
| Maximum load current                | 20 A (with 4 mm <sup>2</sup> conductor cross-section)     |
| Nominal voltage                     | 250 V   |

## Dimensions

|                    |         |
|--------------------|---------|
| Width              | 6.2 mm  |
| Height             | 55 mm   |
| Depth on NS 35/7,5 | 55.3 mm |
| Depth on NS 35/15  | 62.8 mm |

## Material specifications

|  |                           |
|--|---------------------------|
| Color  | traffic gray B (RAL 7043) |
| Flammability rating according to UL 94                           | V0                        |
| Insulating material group  | I                         |
| Insulating material  | PA                        |
| Static insulating material application in cold                   | -60 °C                    |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C                    |
| Fire protection for rail vehicles (DIN EN 45545-2) R22           | HL 1 - HL 3               |
| Fire protection for rail vehicles (DIN EN 45545-2) R23           | HL 1 - HL 3               |
| Fire protection for rail vehicles (DIN EN 45545-2) R24           | HL 1 - HL 3               |
| Fire protection for rail vehicles (DIN EN 45545-2) R26           | HL 1 - HL 3               |
| Surface flammability NFPA 130 (ASTM E 162)                       | passed                    |
| Specific optical density of smoke NFPA 130 (ASTM E 662)          | passed                    |
| Smoke gas toxicity NFPA 130 (SMP 800C)                           | passed                    |

## Electrical tests

### Surge voltage test

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 4.8 kV      |
| Result                | Test passed |

### Temperature-rise test

|  |                                     |
|--|-------------------------------------|
| Requirement temperature-rise test                | Increase in temperature $\leq 45$ K |
| Result   | Test passed                         |
| Short-time withstand current 2.5 mm <sup>2</sup> | 0.3 kA                              |
| Result   | Test passed                         |

### Power-frequency withstand voltage

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 1.5 kV      |
| Result                | Test passed |

## Mechanical tests

### Mechanical strength

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

### Attachment on the carrier

# TBIO 2,5 I - Sensor/actuator terminal block



3246749

<https://www.phoenixcontact.com/gb/products/3246749>

|                         |             |
|-------------------------|-------------|
| DIN rail/fixing support | NS 35       |
| Result                  | Test passed |

## Test for conductor damage and slackening

|                                |                              |
|--------------------------------|------------------------------|
| Rotation speed                 | 10 rpm                       |
| Revolutions                    | 135                          |
| Conductor cross-section/weight | 0.2 mm <sup>2</sup> / 0.2 kg |
|                                | 2.5 mm <sup>2</sup> / 0.7 kg |
|                                | 4 mm <sup>2</sup> / 0.9 kg   |
| Result                         | Test passed                  |

## Environmental and real-life conditions

### Needle-flame test

|                  |             |
|------------------|-------------|
| Time of exposure | 30 s        |
| Result           | Test passed |

### Oscillation/broadband noise

|                        |  |
|------------------------|--|
| Specification          | EN 50155:2021-07                               |
| Spectrum               | Long life test category 2, bogie-mounted       |
| Frequency              | $f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$ |
| ASD level              | 6.12 (m/s <sup>2</sup> ) <sup>2</sup> /Hz      |
| Acceleration           | 3.06g  |
| Test duration per axis | 5 h  |
| Test directions        | X-, Y- and Z-axis                              |
| Result                 | Test passed                                    |

### Shocks

|                                |                                     |
|--------------------------------|-------------------------------------|
| Specification                  | DIN EN 50155 (VDE 0115-200):2008-03 |
| Pulse shape                    | Half-sine                           |
| Acceleration                   | 30g                                 |
| Shock duration                 | 18 ms                               |
| Number of shocks per direction | 3                                   |
| Test directions                | X-, Y- and Z-axis (pos. and neg.)   |
| Result                         | Test passed                         |

### Ambient conditions

|  |  |
|--|--|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)  |
| Ambient temperature (assembly)           | -5 °C ... 70 °C  |
| Ambient temperature (actuation)          | -5 °C ... 70 °C  |
| Permissible humidity (operation)         | 20 % ... 90 %  |
| Permissible humidity (storage/transport) | 30 % ... 70 %  |

## Standards and regulations

# TBIO 2,5 I - Sensor/actuator terminal block



3246749

<https://www.phoenixcontact.com/gb/products/3246749>

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |

# TBIO 2,5 I - Sensor/actuator terminal block


3246749

<https://www.phoenixcontact.com/gb/products/3246749>



## Drawings

Circuit diagram



# TBIO 2,5 I - Sensor/actuator terminal block



3246749

<https://www.phoenixcontact.com/gb/products/3246749>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3246749>



**EAC**

Approval ID: KZ7500651131219505



**cULus Recognized**

Approval ID: E60425

|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| B |                       |                       |                   |                             |
|   | 300 V                 | 15 A                  | 20 - 12           | -                           |
| C |                       |                       |                   |                             |
|   | 300 V                 | 15 A                  | 20 - 12           | -                           |

# TBIO 2,5 I - Sensor/actuator terminal block



3246749

<https://www.phoenixcontact.com/gb/products/3246749>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250112 |
| ECLASS-15.0 | 27250112 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000900 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# TBIO 2,5 I - Sensor/actuator terminal block



3246749

<https://www.phoenixcontact.com/gb/products/3246749>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.135 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)