

# NS 35/ 7,5 V2A UNPERF 2000MM VPE 10 - DIN rail, unperforated



0843100

<https://www.phoenixcontact.com/pc/products/0843100>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Stainless steel V2A, uncoated, Standard profile, color: silver-colored

## Commercial data

Item number	0843100
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	BE7238
GTIN	4046356948982
Weight per piece (including packing)	695 g
Weight per piece (excluding packing)	695 g
Customs tariff number	72224050
Country of origin	DE

# NS 35/ 7,5 V2A UNPERF 2000MM VPE 10 - DIN rail, unperforated



0843100

<https://www.phoenixcontact.com/pc/products/0843100>

## Technical data

### Product properties

Product type	DIN rail
--------------	----------

### Dimensions

Dimensional drawing	
Width	35 mm
Depth	7.5 mm
Length	2000 mm

### Material specifications

Color	silver-colored
Material	Stainless steel V2A
Coating	uncoated

### Standards and regulations

Connection in acc. with standard	IEC / EN
Tests	acc. to EN 60715

### Electrical tests

Short-time withstand current	
Equivalent E-Cu cross-section	16 mm <sup>2</sup>
Short-time current resistance 1s	1.92 kA

# NS 35/ 7,5 V2A UNPERF 2000MM VPE 10 - DIN rail, unperforated



0843100

<https://www.phoenixcontact.com/pc/products/0843100>

## Drawings

Dimensional drawing



# NS 35/ 7,5 V2A UNPERF 2000MM VPE 10 - DIN rail, unperforated



0843100

<https://www.phoenixcontact.com/pc/products/0843100>

## Classifications

### ECLASS

ECLASS-15.0	27400602
ECLASS-13.0	27400602

### ETIM

ETIM 10.0	EC001285
-----------	----------

### UNSPSC

UNSPSC 21.0	39121700
-------------	----------

# NS 35/ 7,5 V2A UNPERF 2000MM VPE 10 - DIN rail, unperforated



0843100

<https://www.phoenixcontact.com/pc/products/0843100>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	4.786 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachmarktstraße 8  
D-32825 Blomberg  
+49 (0) 5235-3 00  
[info@phoenixcontact.com](mailto:info@phoenixcontact.com)