

SACC-DSI-MSB-5CON-L180/SH GNX - Device connector rear mounting



1239822

<https://www.phoenixcontact.com/pc/products/1239822>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 5-position, Pin, straight, M12-SPEEDCON, B-coding, Solder pins, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Easy PCB assembly: one-piece connectors for wave soldering
- All standard pin assignments and codings for signal, data, and power transmission with a uniform design-in design
- For high transmission reliability: optional shield connection to the housing by means of shield contact

Commercial data

Item number	1239822
Packing unit	20 pc
Minimum order quantity	20 pc
Product key	ABQEGB
GTIN	4063151431839
Weight per piece (including packing)	14.465 g
Weight per piece (excluding packing)	13.22 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSI-MSB-5CON-L180/SH GNX - Device connector rear mounting



1239822

<https://www.phoenixcontact.com/pc/products/1239822>

Technical data

Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	---

Product properties

Product type	Circular connectors (device side)
Number of positions	5
Shielded	yes
Coding	B
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Dimensions

Length of the solder pin	6 mm
	6 mm

Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Insulating body	PA 6.6
Material Contact	CuZn
Material Contact surface	Au
Material Seal	NBR
Flammability rating according to UL 94	V0

Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	60 V
Nominal current I_N	4 A

Connection data

Conductor connection	
Connection method	Solder pins
Contact connection type	Pin

Mechanical properties

SACC-DSI-MSB-5CON-L180/SH GNX - Device connector rear mounting



1239822

<https://www.phoenixcontact.com/pc/products/1239822>

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Connector

Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON
Coding	B

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (When plugged in)
	IP65 (When plugged in)
	IP65/IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

SACC-DSI-MSB-5CON-L180/SH GNX - Device connector rear mounting

1239822

<https://www.phoenixcontact.com/pc/products/1239822>

Drawings

Schematic diagram



Pin assignment M12 male connector, 5-pos., B-coded, male side

SACC-DSI-MSB-5CON-L180/SH GNX - Device connector rear mounting



1239822

<https://www.phoenixcontact.com/pc/products/1239822>

Classifications

ECLASS

ECLASS-13.0	27440110
-------------	----------

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SACC-DSI-MSB-5CON-L180/SH GNX - Device connector rear mounting



1239822

<https://www.phoenixcontact.com/pc/products/1239822>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com