

# SACC-DSIV-FS-8CON-L180-10G SCOX - Device connector rear mounting



1237426

<https://www.phoenixcontact.com/pc/products/1237426>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M12 flush-type socket, front mounting

Device connector rear mounting, 8-position, Socket, straight, M12-SPEEDCON, X-coding, THR solder connection, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Commercial data

Item number	1237426
Packing unit	20 pc
Minimum order quantity	20 pc
Product key	ABQAIA
GTIN	4063151430474
Weight per piece (including packing)	11.135 g
Weight per piece (excluding packing)	9.734 g
Customs tariff number	85366990
Country of origin	DE

# SACC-DSIV-FS-8CON-L180-10G SCOX - Device connector rear mounting



1237426

<https://www.phoenixcontact.com/pc/products/1237426>

## Technical data

### Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	---

### Product properties

Product type	Circular connectors (device side)
Number of positions	8
Shielded	no
Coding	X
Thread type	M12

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Insulating body	PA 6.6
Material Contact	Cu alloy
Material Contact surface	Au
Material Seal	NBR
Flammability rating according to UL 94	HB

### Electrical properties

Contact resistance	< 5 mΩ
Insulation resistance	> 100 MΩ
Nominal voltage $U_N$	60 V
Nominal current $I_N$	4 A

### Connection data

#### Conductor connection

Connection method	THR solder connection
Contact connection type	Socket

### Connector

#### Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON

# SACC-DSIV-FS-8CON-L180-10G SCOX - Device connector rear mounting



1237426

<https://www.phoenixcontact.com/pc/products/1237426>

Coding	X
--------	---

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket)

## Standards and regulations


Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

# SACC-DSIV-FS-8CON-L180-10G SCOX - Device connector rear mounting

1237426

<https://www.phoenixcontact.com/pc/products/1237426>

## Drawings



M12 socket pin assignment, 8-pos, view of socket side

# SACC-DSIV-FS-8CON-L180-10G SCOX - Device connector rear mounting



1237426

<https://www.phoenixcontact.com/pc/products/1237426>

## Classifications

### ECLASS

ECLASS-13.0	27440110
-------------	----------

### ETIM

ETIM 9.0	EC001262
----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SACC-DSIV-FS-8CON-L180-10G SCOX - Device connector rear mounting



1237426

<https://www.phoenixcontact.com/pc/products/1237426>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstraße 8  
D-32825 Blomberg  
+49 (0) 5235-3 00  
[info@phoenixcontact.com](mailto:info@phoenixcontact.com)