

# ME-TBUS-A MC 1,5-2 - DIN rail bus connector



1351974

<https://www.phoenixcontact.com/pc/products/1351974>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail bus connector adapter (2-pos.) for connection of MACX MCR-EX-AP ... devices on the right side to the MACX MCR-PTB(-SP) power module with DIN rail bus connector ME 17,5 TBUS 1,5/5-ST-3,81 GY for bridging the supply voltage.

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1351974       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Product key                          | DK111Z        |
| GTIN                                 | 4063151671563 |
| Weight per piece (including packing) | 12.2 g        |
| Weight per piece (excluding packing) | 12.2 g        |
| Customs tariff number                | 85366990      |
| Country of origin                    | PL            |

# ME-TBUS-A MC 1,5-2 - DIN rail bus connector



1351974

<https://www.phoenixcontact.com/pc/products/1351974>

## Technical data

### Product properties

|              |                        |
|--------------|------------------------|
| Product type | DIN rail bus connector |
|--------------|------------------------|

### Electrical properties

|                       |       |
|-----------------------|-------|
| Nominal voltage $U_N$ | 160 V |
| Nominal current $I_N$ | 8 A   |

### Connection data

|                     |        |
|---------------------|--------|
| Connection method   | Female |
| Number of positions | 2      |

### Material specifications

|  |                       |
|--|-----------------------|
| Color                                  | light gray (RAL 7035) |
| Flammability rating according to UL 94 | V0                    |

### Dimensions

|        |          |
|--------|----------|
| Width  | 19.84 mm |
| Height | 11.1 mm  |
| Depth  | 32.2 mm  |

### Environmental and real-life conditions

#### Ambient conditions

|   |                   |
|---|-------------------|
| Ambient temperature (operation)         | -40 °C ... 100 °C |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C  |

# ME-TBUS-A MC 1,5-2 - DIN rail bus connector



1351974

<https://www.phoenixcontact.com/pc/products/1351974>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460201 |
| ECLASS-15.0 | 27460201 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002637 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# ME-TBUS-A MC 1,5-2 - DIN rail bus connector



1351974

<https://www.phoenixcontact.com/pc/products/1351974>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachmarktstraße 8  
D-32825 Blomberg  
+49 (0) 5235-3 00  
[info@phoenixcontact.com](mailto:info@phoenixcontact.com)