

# FL SWITCH EP4208-4SFP-LV - Industrial Ethernet Switch



1732183

<https://www.phoenixcontact.com/us/products/1732183>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Managed Switch EP4000 series, 8 RJ45 ports 10/100/1000 Mbps, 4 SFP ports 100/1000 Mbps, degree of protection: IP40, Ambient temperature (operation): -40 °C ... 85 °C, Supply voltage range: 12 V DC ... 48 V DC

## Product description

Developed according to IEC 61850-3 (Ambient conditions)

## Your advantages

- Network structure according to IEC 61850
- IEEE 1613
- Layer 2 managed switch

## Commercial data

Item number	1732183
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN36
Product key	DNN514
GTIN	4067923290143
Weight per piece (including packing)	2,002 g
Weight per piece (excluding packing)	1,421 g
Customs tariff number	85176200
Country of origin	TW

# FL SWITCH EP4208-4SFP-LV - Industrial Ethernet Switch



1732183

<https://www.phoenixcontact.com/us/products/1732183>

## Technical data

### Dimensions

Width	72 mm
Height	170 mm
Depth	140 mm

### Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Material specifications

Color (Housing)	anthracite gray (RAL 7016)
Housing material	Metal

### Mounting

Mounting type	DIN rail mounting
---------------	-------------------

### Interfaces

#### Ethernet

Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100/1000 Mbps
Transmission physics	Copper
Transmission length	100 m (per segment)
No. of channels	8 (RJ45 ports)

#### Ethernet (SFP)

Connection method	SFP
Transmission speed	100/1000 Mbps (full duplex)
Transmission physics	Depending on the SFP module
No. of channels	4 (SFP ports)

### Output data

Digital:

Output name	Alarm relay output: 30 V DC, 0.6 A maximum
-------------	--

### Product properties

Product type	Switch
Product family	Managed Switch EP4000
MTBF	240.1 Years (Telcordia standard, 25 °C temperature, 50% stress)
	20.2 Years (MIL-HDBK-217F standard, temperature 25°C)

# FL SWITCH EP4208-4SFP-LV - Industrial Ethernet Switch



1732183

<https://www.phoenixcontact.com/us/products/1732183>

	514 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
--	--

## Switch functions

Signal contact control voltage	30 V DC
Signal contact control current	0.6 A
MAC address table	16k
Redundancy	RSTP (Rapid Spanning Tree, IEEE 802.1w)
	STP
	MSTP
Status and diagnostic indicators	LEDs: POWER, ERROR, Link status

## Electrical properties

Local diagnostics	US1, US2 Supply voltage Green LED
	Alarm Alarm signal LED red
Maximum power dissipation for nominal condition	20 W (max.)

## Supply

Supply voltage (DC)	24 V DC (redundant)
Supply voltage range	12 V DC ... 48 V DC

## Function

Signal contact control voltage	30 V DC
Signal contact control current	0.6 A

## Connection data

### Power supply

Connection method	Screw connection
-------------------	------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP40
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)

## Standards and regulations

Standard designation	Ambient conditions
Standards/specifications	IEC 61850-3
	IEEE 1613

## Approvals

### Conformity/Approvals

Conformance	CE-compliant
-------------	--------------

# FL SWITCH EP4208-4SFP-LV - Industrial Ethernet Switch



1732183

<https://www.phoenixcontact.com/us/products/1732183>

## EMC data

Noise immunity

IEC 61850-3, IEEE 1613

## Signaling

Status display

LEDs: POWER, ERROR, Link status

# FL SWITCH EP4208-4SFP-LV - Industrial Ethernet Switch



1732183

<https://www.phoenixcontact.com/us/products/1732183>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1732183>



**cULus Listed**

Approval ID: E238705-20170725

# FL SWITCH EP4208-4SFP-LV - Industrial Ethernet Switch



1732183

<https://www.phoenixcontact.com/us/products/1732183>

## Classifications

### ECLASS

ECLASS-13.0	19170401
ECLASS-15.0	19170401

### ETIM

ETIM 10.0	EC000734
-----------	----------

# FL SWITCH EP4208-4SFP-LV - Industrial Ethernet Switch



1732183

<https://www.phoenixcontact.com/us/products/1732183>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	15(a), 6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)