

FL SFP-10G-SR - Media module

1145046

<https://www.phoenixcontact.com/us/products/1145046>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

10 Gigabit SFP module for transmission up to 300 m with a wavelength of 850 nm.



Commercial data

Item number	1145046
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN22
Product key	DNN614
GTIN	4063151131692
Weight per piece (including packing)	41 g
Weight per piece (excluding packing)	17 g
Customs tariff number	85176200
Country of origin	TW

FL SFP-10G-SR - Media module



1145046

<https://www.phoenixcontact.com/us/products/1145046>

Technical data

Dimensions

Width	14.69 mm
Height	13 mm
Length	55.9 mm

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Material specifications

Color (Housing)	white aluminium (RAL 9006)
-----------------	----------------------------

Mounting

Mounting type	Plug-in mounting (SFP port)
---------------	-----------------------------

Interfaces

Fiber optic interface

Connection method	LC duplex
Transmission speed	10 Gbps
Transmission physics	FO
Transmission length	300 m
No. of channels	1 (LC multi-mode)

Product properties

Product type	SFP module
Format	SFP (Small Form-factor Pluggable)

Signaling

Status display	via a Factoryline device
----------------	--------------------------

Electrical properties

Maximum power dissipation for nominal condition	0.6 W
Transmission medium	FO

Supply

Supply voltage	3.3 V (via Factoryline switch)
Power supply connection	via SFP slot

Connection data

Connection method	To insert in SFP slot
-------------------	-----------------------

Environmental and real-life conditions

FL SFP-10G-SR - Media module



1145046

<https://www.phoenixcontact.com/us/products/1145046>

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (non-condensing)
Ambient temperature (storage/transport)	-40 °C ... 85 °C (non-condensing)

FL SFP-10G-SR - Media module



1145046

<https://www.phoenixcontact.com/us/products/1145046>

Classifications

ECLASS

ECLASS-13.0	19179090
ECLASS-15.0	19179090

ETIM

ETIM 10.0	EC002608
-----------	----------

FL SFP-10G-SR - Media module



1145046

<https://www.phoenixcontact.com/us/products/1145046>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com