

# USK 10 - Feed-through modular terminal block



0261014

<https://www.phoenixcontact.com/us/products/0261014>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through modular terminal block, nom. voltage: 750 V, nominal current: 61 A, number of connections: 2, connection method: Screw connection, mounting type: NS 35/7,5, NS 35/15, color: gray

## Commercial data

Item number	0261014
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	BE05
Product key	BE511X
GTIN	4017918000073
Weight per piece (including packing)	15.7 g
Weight per piece (excluding packing)	15.7 g
Customs tariff number	85369010
Country of origin	US

# USK 10 - Feed-through modular terminal block



0261014

<https://www.phoenixcontact.com/us/products/0261014>

## Technical data

### Product properties

Number of connections	2
Number of rows	1
Potentials	2

### Connection data

Connection method	Screw connection
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup>
Conductor cross-section, flexible [AWG]	24 ... 8 (converted acc. to IEC)
Nominal current	61 A
Nominal voltage	750 V

### Dimensions

Width	8.2 mm
-------	--------

### Material specifications

Color	gray
-------	------

### Mechanical properties

#### Mechanical data

Open side panel	Yes
-----------------	-----

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

### Mounting

Mounting type	NS 35/7,5
	NS 35/15

# USK 10 - Feed-through modular terminal block



0261014

<https://www.phoenixcontact.com/us/products/0261014>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)